


# Super-Size AkroBins®

heavy duty bins, totes, containers & small parts storage

- Large-capacity storage to improve organization
- Molded of high-impact polypropylene and unaffected by weak acids or alkalis
- Sturdy, one-piece construction is water, rust and corrosion-proof
- Guaranteed not to crack or break under normal load conditions as stated in the 1-year limited warranty
- Products made of polypropylene block copolymer are autoclavable up to 250° F
- Available in three vibrant colors – Red, Yellow and Blue

## features



Anti-slide stop prevents stacked bins from shifting forward



Easy to carry with large handle molded onto back of bin



Reinforced side ribs add strength and prevent spreading when stacked



Large label area on front of bin



## accessories



**Window Insert** optimizes interior space and keeps contents visible



**Lengthwise Dividers** keep items separated in the bin

**Exclusively from Akro-Mils**  
**WIDTH DIVIDERS**  
**Create Extra Storage!**



**Widthwise Dividers** create extra storage compartments

## Super-Size AkroBins

### New Ways to Super-Size & Organize


- Provide additional options to efficiently organize large items and improve workflow
- Heavy-duty bins securely stack atop each other or can sit on shelving, carts or dollies



**30284 Super-Size AkroBins**  
23 7/8" x 8 1/4" x 7"



Super-Size AkroBins	Outside Dimensions Inches			Inside Dimensions Inches				Max. Cap. per Bin	Stacking Cap./= Qty. Stacked	Ctn. Qty.	Width	Length	Accessories		Windows	
	L	W	H	L	W	H	X						Dividers*	Qty. W	Qty. L	Windows
30280	20	12 $\frac{3}{8}$	6	16 $\frac{7}{8}$	10 $\frac{1}{16}$	5 $\frac{3}{8}$	15 $\frac{1}{2}$	200 lbs.	40 lb./10	4	-	40280 (3)	-	2	21280	2
30281	20	12 $\frac{3}{8}$	8	16 $\frac{7}{8}$	10 $\frac{1}{16}$	7 $\frac{3}{8}$	15 $\frac{1}{2}$	200 lbs.	50 lb./7	3	-	40281 (3)	-	3	21281	3
30282	20	12 $\frac{3}{8}$	12	16 $\frac{7}{8}$	10 $\frac{1}{16}$	11 $\frac{3}{8}$	15 $\frac{1}{2}$	200 lbs.	60 lb./5	2	-	40282 (3)	-	1	21282	2
30283	20	18 $\frac{3}{8}$	12	16 $\frac{7}{8}$	16 $\frac{1}{16}$	11 $\frac{3}{8}$	15 $\frac{1}{2}$	300 lbs.	150 lb./5	1	-	40283 (3)	-	1	21283	1
30284	23 $\frac{3}{8}$	8 $\frac{1}{4}$	7	20 $\frac{3}{4}$	6 $\frac{3}{8}$	6 $\frac{3}{8}$	19 $\frac{3}{8}$	200 lbs.	150 lb./5	1	41284 (2)	40286 (3)	2	4	21284	4
30286	23 $\frac{3}{8}$	11	7	20 $\frac{3}{4}$	9 $\frac{3}{8}$	6 $\frac{3}{8}$	19 $\frac{3}{8}$	200 lbs.	150 lb./5	4	41286 (2)	40286 (3)	2	4	21286	4
30287	23 $\frac{3}{8}$	11	10	20 $\frac{3}{4}$	9	9 $\frac{3}{8}$	19 $\frac{3}{8}$	300 lbs.	150 lb./5	4	41287 (2)	40287 (3)	6	6	21287	4
30288	23 $\frac{3}{8}$	16 $\frac{1}{2}$	11	20 $\frac{3}{4}$	14 $\frac{3}{8}$	10 $\frac{3}{8}$	19 $\frac{3}{8}$	300 lbs.	150 lb./5	1	41288 (2)	40287 (3)	6	6	21288	1
30289	23 $\frac{3}{8}$	18 $\frac{1}{4}$	12	20 $\frac{3}{4}$	16	11 $\frac{3}{8}$	19 $\frac{3}{4}$	300 lbs.	150 lb./5	1	41289 (2)	40289 (3)	2	1	21289	1
30290	29 $\frac{1}{4}$	18 $\frac{3}{8}$	12	26 $\frac{1}{8}$	16 $\frac{3}{16}$	11 $\frac{3}{8}$	24 $\frac{3}{8}$	300 lbs.	150 lb./5	1	-	40290 (3)	-	1	21283	1
30292	29 $\frac{1}{4}$	11	10	26 $\frac{3}{4}$	9	9 $\frac{3}{8}$	25 $\frac{3}{16}$	300 lbs.	150 lb./5	4	41287 (2)	40292 (3)	6	6	21287	4
30293	29 $\frac{1}{4}$	16 $\frac{1}{2}$	11	26 $\frac{3}{4}$	14 $\frac{3}{8}$	10 $\frac{3}{8}$	25 $\frac{3}{16}$	300 lbs.	150 lb./5	1	41288 (2)	40292 (3)	6	6	21288	1



One color per carton: Specify Red, Blue, or Yellow. Not recommended to hang on rack or panel systems. Order in carton quantities. \* ( ) = Max. # of dividers per bin.

### Super-Size AkroBin Carts



Model No.	Descriptions	L	W	H	Capacity lbs.	No. of Handles	Ctn. Qty.
R214CS1841	Transports six 30283 Bins	41	18	48	900	2	1
R214CS1859	Transports nine 30283 Bins	59	18	48	1350	2	1
R214CS1878	Transports twelve 30283 Bins	78	18	48	1500	2	1
R214CS2841	Transports six 30290 Bins	41	27 $\frac{1}{2}$	48	900	2	1
R214CS2859	Transports nine 30290 Bins	59	27 $\frac{1}{2}$	48	1350	2	1
R214CS2878	Transports twelve 30290 Bins	78	27 $\frac{1}{2}$	48	1500	2	1
R216CS2236	Transports sixteen 30284 Bins, six 30286 Bins, six 30287 Bins, four 30288 Bins	35 $\frac{1}{2}$	22 $\frac{3}{8}$	35	900	1	1
R216CS2836	Transports six 30292 Bins, four 30293 Bins	35 $\frac{1}{2}$	28 $\frac{3}{8}$	35	900	1	1
R216CS2239	Transports four 30289 Bins	35 $\frac{1}{2}$	22 $\frac{3}{8}$	39	900	1	1

Optional security bar available for all sizes. Bins sold separately.

### Super-Size AkroBin Dollies

Model No.	Descriptions	L	W	H	Casters	Capacity lbs.	Ctn. Qty.
RU843HR2018	Compatible with Model 30280, 30281, 30282 & 30283 Bins - Fits 1 wide	17 $\frac{1}{16}$	18 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843HR2918	Compatible with Model 30290 Bins - Fits 1 wide	26 $\frac{1}{16}$	18 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP2122	Compatible with Model 30286 & 30287 Bins - Fits 2 wide	20 $\frac{7}{8}$	21 $\frac{1}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP2227	Compatible with Model 30292 Bins - Fits 2 wide	21 $\frac{7}{8}$	26 $\frac{1}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP1721	Compatible with Model 30284 Bins - Fits 2 wide Compatible with Model 30288 Bins - Fits 1 wide	16 $\frac{1}{2}$	20 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP1727	Compatible with Model 30293 Bins - Fits 1 wide	16 $\frac{1}{2}$	26 $\frac{1}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP1821	Compatible with Model 30289 Bins - Fits 1 wide	18 $\frac{1}{2}$	20 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1

Bins sold separately.



## products related products

Increase the benefits of your Super-Size AkroBins with:

- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42
- Shelf Cart ..... pg. 47

### Window Inserts

Optimize interior space and keep contents visible



## Carts & Dollies

### AkroBin Carts

Easy organization of bulky parts in 4, 6, 9, 12 and 16 bin configurations!

- Super-Size AkroBins (sold separately) store and organize large, bulky items
- Heavy-duty frames with capacity from 900 - 1,500 lbs.



### AkroBin Solid Steel Dollies

Available for efficient parts transport

# Stak-N-Store Bins

heavy duty bins, totes, containers & small parts storage

- The perfect way to organize heavy, bulky items
- Bins stack to form tall, stable storage arrangements on floors or standard industrial shelving
- 75 lb. weight capacity
- Color: Gray, Red and Blue
- 13017 is also available in White




## features



Large radius corners and curved upper lip add strength



Side ribs add stability when stacked



Wide hopper front allows easy access to bulky items



Large comfort grip handles

## related products

Add mobility to your Stak-N-Store Bins with:

- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42
- Solid Steel Dollies ..... pg. 50
- VERSA/Deck ..... pg. 53
- Platform Trucks ..... pgs. 54-57




### Secure Stacking


- Stack bins together to form vertical storage and picking systems




### Solid Steel Dollies

- Available for efficient, easy load transport



Stak-N-Store Bins	Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Capacity Cu. Ft.	Ctn. Qty.
		L	W	H	L	W	H	X		
	13014	17½	10¾	12½	15%	8	12¼	13½	.98	4
	13017	15¼	19¾	12½	13%	17½	12¼	11½	1.7	3
	13018	17½	16½	12½	15%	13¾	12¼	13½	1.6	2

One color per carton. Specify Red, Blue or Gray. 13017 also available in White. Order in carton quantities.

Steel Dolly	Model No.	Inches			Ctn. Qty.	Capacity	Casters	Bin Compatibility
		L	W	H				
	RU843HR1617	16¾	15¾	4½	1	900 lbs.	3" Polyolefin	13018
	RU843HR1519	19¼	14¾	4½	1	900 lbs.	3" Polyolefin	13017




# Nest & Stack Totes

heavy duty bins, totes, containers & small parts storage

- Extremely durable industrial-grade totes
- Ideal for shipping, transfer and storage applications
- NSTs stack with or without lids for storage and shipping, nest when empty
- Strong, high impact polypropylene will not rust, corrode or bend out of shape even when fully loaded
- Heavy-duty construction provides a longer service life resulting in lower replacement costs than other “budget-priced” totes
- Easy to clean, smooth surfaces are resistant to most solvents and chemicals
- NSTs are manufactured from FDA-sanctioned materials
- Optional lids protect contents from dust and damage
- Available in 9 sizes and 3 colors: Red, Blue and Gray



## features



Smooth surfaces are easy to clean



Comfortable grip makes handling easy



Textured bottoms provide a no-slip grip on conveyor belts



Ribs under the lip will prevent jamming when nested

## products related products

Add mobility to your Nest & Stack Totes with:

- Carts ..... pgs. 45-47
- Dollies..... pgs. 49-50
- Wire Shelving Systems ..... pgs. 36-39



### Dollies


- Available to transport containers – see pgs. 49-50



## accessories





**Clear Plastic Label Holders** attach easily to NSTs, with or without the lid in place. Holders accommodate labels up to 3¾" x 5"



**Lids snap tight** to protect contents. See lids chart for matching lid size below

### Label Holders

Model No.	Pkg. Qty.	Label Size (In.)
35010	6	3¾ x 5
35011	6	3 x 5



Nest & Stack Totes (NSTs)	Outside Dimensions Inches				Inside Dimensions Inches					NST Ctn. Qty.	Cu. Ft.	Lid Model	Ctn. Qty.
	Model No.	L	W	H	A	B	C	D	E				
35180	18	11	6	10	16	15¼	9%	5%	6	0.5	35181	6	
35185	18	11	9	10	16	15%	9%	8%	6	0.76	35181	6	
35190	19½	15½	10	14½	17	16	13¼	9%	6	1.2	35191	6	
35195	19½	15½	13	14½	17	15%	13%	12%	6	1.7	35191	6	
35200	19½	13½	8	12%	17½	16%	11½	7%	6	0.8	35201	6	
35225	23½	19½	10	18¼	20%	19%	16%	9%	3	2	35231	3	
35230	23½	19½	13	18%	20%	19½	16%	12%	3	2.6	35231	3	
35240*	23½	15½	12	14¼	20%	19%	13	11%	3	1.7	35241	3	
35300*	29½	19½	15	18¼	26%	25%	16%	14%	3	3.7	35301	3	

One color per carton. Specify color: Red, Blue or Gray. Order in carton quantities. \*Made of HDPE polyethylene.

# Akro-Grids

heavy duty bins, totes, containers & small parts storage

- Versatile work-in-process transfer containers
- Dividers allow subdivision of the containers down to a 1¼" square compartment size
- Injection-molded from polypropylene block copolymer
- Resists most solvents and chemicals
- Compatible with most racks, shelving and automated material handling equipment
- Dividers, lids and label holders sold separately
- Available in 8 sizes and 3 colors: Red, Blue and Gray



## features



Divider slots allow you to create hundreds of different compartment sizes



Strong stacking rims and external ribbing provide added strength

## accessories



**Dividers** allow subdivision of the containers down to a 1¼" square compartment size. Color: Black



**Clear Plastic Label Holders** snap securely on any side of the container



**Clear Plastic Covers** keep contents clean yet visible. Molded corner guides provide secure stacking



Akro-Grids	Outside Dimensions Inches			Inside Dimensions Inches					Capacity			Accessories		Pkg. Qty.
	Model No.	L	W	H	A	B	C	D	E	Ctn. Qty.	Cu. Ft.	Lbs.	Long Divider*	
33105	10⅞	8¼	5	6⅞	9⅞	9⅞	6½	4⅞	20	.16	25	42105 (5)	41105 (7)	6
33164	16½	10⅞	4	9⅞	14⅞	14⅞	9⅞	3⅞	12	.29	20	42164 (7)	41164 (11)	6
33166	16½	10⅞	6	9⅞	14⅞	14⅞	9⅞	5⅞	8	.44	35	42166 (7)	41166 (11)	6
33168	16½	10⅞	8	9⅞	14⅞	14⅞	9⅞	7⅞	6	.59	40	42168 (7)	41168 (11)	6
33220	22⅜	17⅜	10	15¼	20⅞	19⅞	14⅞	9⅞	2	1.66	50	42220 (11)	41220 (15)	6
33224	22⅜	17⅜	4	15¼	20⅞	20	15	3⅞	6	.61	30	42224 (11)	41224 (15)	6
33226	22⅜	17⅜	6	15¼	20⅞	19⅞	14⅞	5⅞	4	.96	40	42226 (11)	41226 (15)	6
33228	22⅜	17⅜	8	15¼	20⅞	19⅞	14⅞	7⅞	3	1.30	50	42228 (11)	41228 (15)	6


One color per carton. Specify Red, Blue or Gray. Order in carton quantities. \*( ) = max # of dividers.

### Clear Plastic Covers

Model No.	Fits Grid No.	Ctn. Qty.
33101	33105	10
33161	33166, 33168, 33164	4
33221	33228, 33220, 33226, 33224	3

### Label Holders

Model No.	Description	Pkg. Qty.
35010	Fits all Akro-Grids except 33164 and 33224	6
35011	Fits grids No. 33164, 33224	6



### Dollies

- Available to transport containers. See pgs. 49-50



# Attached Lid Containers

heavy duty bins, totes, containers & small parts storage



- ALCs stack and nest for optimal space use
- Reusable shipping, distribution, order picking, and storage containers
- Attached lids snap securely closed to protect contents from dust or damage
- Containers interwork for easy pallet loading
- See chart below for color options



## features



Textured bottoms provide a sure grip on conveyor belts



Strong molded-in handle grips are ergonomically designed for easy lifting and carrying



Padlock eye on both ends accommodates security ties



Reinforced hinge pins for years of smooth lid operation



Extra secure HDPE hinges "lock" when lid closes, protecting against inventory loss and theft. Available on model AA211512 only

## All-Plastic Attached Lid Container Ship & Store – More Secure!


- All-plastic hinges "lock" lid for greater security in shipping, storage or picking applications
- 100% recyclable tote
- Non-steel hinge makes product lighter
- Tie holes located in both ends of lid are compatible with a variety of closures to further secure lids
- Available in Red, Blue, Green or Gray



AA211512

ALCs	Model No.	Available Colors	Outside Dimensions Inches			Inside Dimensions Top Inches			Inside Dimensions Bottom Inches		Capacity			Ctn. Qty.	Stack Cap./Qty. Stacked
			L	W	H	L	W	H	L	W	Cu. Ft.	Gal.	Lbs.		
	39085	Blue, Gray	21½	15	9	19¾	14½	8¾	18⅞	13¼	1.12	8.5	35	6	35 lbs./5
	39120	Blue, Gray	21½	15	12½	19¾	14½	12	18⅞	13¼	1.62	12	65	6	65 lbs./5
	39160	Gray	27	17	12½	25	15½	11	23½	14	2.25	16.83	100	1	100 lbs./4
	39170	Blue, Gray	21½	15	17	19¾	14½	16¾	18⅞	13¼	2.28	17	100	3	100 lbs./3
	39175	Gray	24	19½	12½	22	18	11	20½	16½	2.3	17.20	80	1	80 lbs./5
	39280	Gray	28	21	15½	26	19	14	25	18	3.82	28.57	100	1	100 lbs./4
	AA211512	Blue, Green, Red, Gray	21¾	15¾	12½	20⅞	14½	11¼	17⅞	12¼	1.62	12	65	6	65 lbs./5

Order in carton quantities. Specify color when ordering.



### Dollies

- Plastic, steel and wood dollies available to transport containers. See pgs. 49-50



### Attached Lid Containers

- Models 39160, 39175 and 39280 are available in gray only





# Straight Wall Containers

heavy duty bins, totes, containers & small parts storage

- SWCs are reusable shipping, storage, and work-in-process containers
- Straight walls provide efficient internal and external space usage
- Solid-sided containers have smooth inner walls for easy, sanitary cleaning
- Mesh-sided containers allow hot or cold air ventilation
- Injection-molded from high-density polyethylene
- Available in 4 sizes and 3 styles
- Color: Gray



**3 Styles Per Size:**  
Solid, mesh and combinations



## features




One-inch wall thickness for secure stacking



Strong, 1" wide, stacking rims and external ribbing provide added strength



Straight walls provide efficient cubing in trucks and on pallets



Open .72 x .90 mesh pattern allows high visibility and good airflow

## related products

Add more productivity to your Straight Wall Containers with:

- Carts ..... pgs. 45-47
- Dollies..... pgs. 49-50
- Platform Trucks..... pgs. 54-57




### Dollies

- Plastic, steel and wood dollies available to transport containers. See pgs. 49-50

### Straight Wall Containers (SWCs)

Straight Wall Containers (SWCs)			Outside Dimensions Inches			Inside Dimensions Top Inches			Stacking Capacity / Qty. Bottom Type		
Model No. Mesh Side & Base	Model No. Mesh Side/Solid Base	Model No. Solid Side & Base	L	W	H	L	W	H	Ctn. Qty.	Solid	Mesh
37208	37278	37288	15¾	11¾	8¼	14¼	10¼	8	12	83 lbs./6	30 lbs./6
37608	37678	37688	23¾	15¾	8¼	22¼	14¼	8	4	83 lbs./6	45 lbs./6
37612	37672	37682	23¾	15¾	12¼	22¼	14¼	12	3	125 lbs./5	45 lbs./5
37616	37676	37686	23¾	15¾	16¾	22¼	14¼	16	2	150 lbs./4	45 lbs./4

Order in carton quantities.





# Cross-Stack Akro-Tub

heavy duty bins, totes, containers & small parts storage

- Ideal for food processing and handling operations or industrial work-in-progress activities
- Industrial-grade 90° nest and stack tub
- Nesting when empty conserves storage space
- Molded-in side handles for comfortable lifting
- Manufactured from FDA-sanctioned materials
- Smooth surface is easy to clean
- Compatible with standard 36" shelving and conveyor systems
- Color: Gray



## features


### cross-stack akro-tub features



Stacking grooves allow stable 90° stacks



Molded-in handles for easy lifting



Extra-thick walls and reinforcing ribs provide superior strength



# Akro-Tub & Rack

- Heavy-duty, industrial-grade nesting tub
- Tub manufactured from FDA-sanctioned materials
- Smooth surface is easy to clean
- Nests when empty to conserve storage space
- Use the Akro-Tub Rack (RA6TR4MR) to provide easy loading and transport of multiple Akro-Tubs
- 75 lb. capacity per tub
- Color: Gray



## features

### akro-tub features




Rounded corner design adds strength to stress points




Rolled top rim forms comfortable handles



Extra-thick walls for superior strength



Ribs prevent jamming when nested

Cross-Stack Akro-Tub	Outside Dimensions Inches							
	Model No.	L	W	H	A	B	Capacity Gal.	Ctn. Qty.
	34301	17¼	11	8	13¼	7¾	3.85	6
	34302	17¼	11	12	12¾	7	5.51	6
	34303	23¾	17¼	8	19¾	14	9.81	6
	34304	23¾	17¼	12	19	13¼	14.38	6

Order in carton quantities.

Double-Sided Cross-Stack Akro-Tub Rack		Inches			
Model No.	Description	L	W	H	Rack Weight/lbs.
RACR5MR	Holds 32 (34301) Cross-Stack Akro-Tubs* or 16 (34303) Cross-Stack Akro-Tubs*	53	29	62	1000 lbs.

Order in carton quantities. \*Tubs sold separately.

Akro-Tub		Inches					
Model No.	L	W	H	A	B	Capacity Gal.	Ctn. Qty.
34240	19	24½	9½	20½	15½	14.6	6

Order in carton quantities.

Akro-Tub Rack		Inches			Casters
Model No.	H	W	D		
RA6TR4MR	73	24	24	4" x 2" Mold-On Rubber: 2 Rigid, 2 Swivel	



### Double-Sided Cross-Stack Tub Rack

- Holds 32 (34301) or 16 (34303) Cross-Stack Akro-Tubs\*



### Akro-Tub Rack

- Holds 6 Akro-Tubs on angle-iron slides for up to 600 lb. total capacity. Welded steel frame with 12-gauge base and bolted-on casters.\*

\*Akro-Tubs sold separately.



# Steel Storage Cabinets

heavy duty bins, totes, containers & small parts storage

- Two cabinets fit side by side on standard 36" wide shelving
- Removable drawers are rust, corrosion and dent-proof



19228

**19-Series Heavy-Duty Cabinets**  
Frame: 17" wide x 11" deep x 11" high with five different drawer sizes  
• 2 dividers per drawer



17018

**17-Series Light-Duty Cabinets**  
Frame: 18" wide x 6" deep x 9½" high. Drawer depth 5¾"  
• 1 divider per drawer

## features

steel storage cabinet features – 19-Series



Heavy-duty welded-steel frame with durable powder-coated finish



Label holder and transparent window for content identification



Strong, high-impact polystyrene drawers

### 19-Series Drawers

- Available separately for a variety of uses



# Plastic Storage Cabinets

- Strong plastic cabinets organize and protect components
- A variety of drawer configurations provide versatile storage solutions
- Cabinets stack securely and are wall mountable
- Dividers included



10116



10124



10126



10144



10164

## features

storage cabinet features



Frame back interlocks into face



Flexible, strong, see-through drawers with finger grip drawer pulls



Rugged, high-impact polystyrene frame

# Storage Cabinet Hanging & Rotary Systems

## Mobile Steel Cabinet Rack\*

- Double-sided, mobile rail rack holds 12 of the 19-Series cabinets with as many as 336 drawers
- Supports up to 500 lbs.



### Components & Quantities

- 30016 Double-Sided Rail Rack – Qty: 2
- 30424 Mobile Kit – Qty: 1
- 19-Series Cabinets – Mix or Match – Qty: 12
- 98400 Suspension Straps (Set of 2 straps) – Qty: 12 Sets  
\*Assembly required

## Storage -Go-Round\*

- Access 20 cabinets and as many as 560 drawers in less than three square feet of floor space
- Holds up to 1,000 lbs. of parts
- Accommodates the 19-Series Steel Cabinets (sold separately)
- Swing diameter 43½" (1,108 mm)
- Stands 31" L x 31" W x 60" H (787 x 787 x 1524 mm)



### Components & Quantities

- 98325 Storage-Go-Round with turntable base
- 19-Series Cabinets – Mix or Match – Qty: 20
- \*Assembly required

### 19-Series Heavy-Duty Steel Cabinets

### Drawer Dimensions Inches

Model No.	Description	Drawers Per Cabinet†	W	H	D	Ctn. Qty.	Drawer Model No.	Dividers 25/Pkg. Model No.
19228	Steel Storage Cabinet*	28	2¾	2½	10⅞	1	20228	40228
19320	Steel Storage Cabinet*	20	3¾	2½	10⅞	1	20320	40320
19416	Steel Storage Cabinet*	16	4	2½	10⅞	1	20416	40416
19715	Steel Storage Cabinet*	15	3¾	3½	10⅞	1	20715	40715
19909	Steel Storage Cabinet*	9	5¾	3½	10⅞	1	20909	40909
19109	Storage Cabinet w/ Locking Door	9	5¾	3½	10⅞	1	20909	40909

† Two removable dividers and one label per drawer included. \* Available with a locking door when ordered in quantities of 50 or more.

### 17-Series Light-Duty Steel Cabinets

### Drawer Dimensions Inches

Model No.	Description	Drawers Per Cabinet†	W	H	D	Ctn. Qty.	Drawer Model No.	Dividers 25/Pkg. Model No.
17018	Storage Cabinet*	18	2¾	2½	5¾	1	20902	40901
17136	Storage Cabinet*	36	2¾	1¼	5¾	1	20502	40501

† One removable divider and one label per drawer included. \* Available with a locking door when ordered in quantities of 50 or more.

### Plastic Storage Cabinets

### Inches

Model No.	Description	L	W	H	Ctn. Qty.
10116	16-Drawer Cabinet	10⅞	6¾	8½	1
10124	24-Drawer Cabinet	20	6¾	15⅜	1
10126	26-Drawer Cabinet	20	6¾	10⅞½	1
10144	44-Drawer Cabinet	20	6¾	15⅜	1
10164	64-Drawer Cabinet	20	6¾	15⅜	1

16-Drawer Cabinet has 8 dividers. All other cabinets have 8 small and 4 large dividers.

### Additional Dividers (Plastic Cabinets)

Model No.	Description
40716	16-Pack additional dividers for small drawers
40717	6-Pack additional dividers for large drawers




# Storage Cases

heavy duty bins, totes, containers & small parts storage


- Grid design in lid keeps items from spilling into other compartments
- Cases available in 3 sizes with different divider configurations
- Small and medium cases include 4 front-to-back adjustable dividers
- Large cases include 5 front-to-back adjustable dividers
- Clarified polypropylene for durability




Small & Medium Cases



Medium Cases




Large Cases



# Portable Organizers



- Unique design keeps parts and equipment from migrating to other compartments when lids are shut
- Separate lid compartment holds small items
- The main compartment holds larger, bulky items
- Dividers included for both levels
- Molded-in "feet" allow case to stand upright



# Roto-Shelf



- Mobile storage unit can easily be moved to different work areas, ideal for assembly components
- 19% " wide unit takes up very little floor space
- 3 shelves rotate on an independent central metal shaft
- Shelf depth – 2 1/2", Shelf diameter – 19%", 75 lbs. per shelf, 300 lb. total wt. capacity



# Tote Caddy



- Hand-held tool and supply caddy
- Deep compartments hold loose parts, cleaning supplies or tools for easy transport
- Molded of heavy-duty, industrial-grade polypropylene for lasting durability
- Color: Blue

## Storage Cases

### Dimensions Inches

Model No.	Description	L	W	H	Max. Compartments	Ctn. Qty.
05705	Small Case – 2 Fixed Dividers	8%	5%	1%	15	12
05805	Medium Case – 2 Fixed Dividers	11	7	2 3/4	15	6
05807	Medium Case – 1 Fixed Divider	11	7	2 3/4	10	6
05905	Large Case – 2 Fixed Dividers	14 3/4	9 1/2	2 1/2	18	6

Order in carton quantities.

## Portable Organizers

### Inches

Model No.	Description	L	W	H	Max. Compartments	Ctn. Qty.
06115	Lid Storage Organizer	15	11 1/16	3 1/4	11 to 46	1
06118	Large Lid Storage Organizer	18 1/4	13 3/8	3 3/8	12 to 62	1
06217	Flat Bottom Organizer	11 1/16	15	3 3/8	9 to 32	6

Order in carton quantities.

## Roto-Shelf

### Inches

Model No.	Description	D	H	Ctn. Qty.
02420	Roto Shelf	19%	37 1/2	1

## Tote Caddy

### Inches

Model No.	Description	L	W	H	Ctn. Qty.
09185BLUE	Tote Caddy	13%	18%	9	6

Order in carton quantities

