



Modular System from avextras.com

Innovative design makes it simple to install and offers a high quality and cost effective solution

All the latest connectivity is fully supported including **HDMI, Toslink, Displayport and VGA**



NEW BLACK MODULE RANGE!


New range has been developed with black modules and faceplates for a sleek professional finish.

Ideal for domestic and professional AV installation.

NEW RANGE OF MOUNTING HARDWARE!

New range of hardware allows multiple mount options:

- Under Desk Mount
- Pop-Up Desk Mount
- Pop-Up Desk Tower



FLEXIBLE

Standard UK dual gang frame takes 5 snap-in brackets. This allows huge choice of connectivity for different applications. Order exactly your requirement for each job.

SIMPLE INSTALLATION

Snap-in brackets are terminated either with couplers, so you can use standard AV cables off the shelf,

Or they use terminal blocks mounted onto flexible cable – this allows easy installation with no soldering required.

HIGH QUALITY

All units are 100% tested prior to shipment. All our dual and single backboxes feature integral strain relief and cable exit for secure installation. Couplers and terminal block (cabled) ensures reliable connectivity.

Modular System – Part Number Reference Sheet (Modular Inserts)













Part Number	Description	Connectivity method*	
MOD001 MOD024 MOD036	Single Gang Bracket – Bevelled Single Gang Bracket – Flat Single Gang Bracket – Flat (BLACK)	N/A	
MOD002 MOD021 MOD022 MOD023 MOD025 MOD037	Dual Gang Bracket (White Plastic-Bevelled) Dual Gang Bracket (Chrome effect) Dual Gang Bracket (Black Nickel) Dual Gang Bracket (Stainless Steel) Dual Gang Bracket (White Plastic-Flat) Dual Gang Bracket (Black Plastic-Flat)	N/A	See spec sheet for pictures and further details
MOD026 MOD027 MOD028 MOD029	Single Gang Brush plate-Black Single Gang Brush plate-White Dual Gang Brush plate-Black Dual Gang Brush plate-White	N/A	
MOD003 MOD038	10mm x 50mm Blank Snap-in Bracket 10mm x 50mm Blank Snap-in Bracket (BLACK)	N/A	
MOD004 MOD039	20mm x 50mm Blank Snap-in Bracket 20mm x 50mm Blank Snap-in Bracket (BLACK)	N/A	
MOD040	25mm x 50mm Blank Snap-in Bracket (BLACK)	N/A	
MOD005	50mm x 50mm Snap-in Blank Bracket	N/A	
MOD006 MOD041	RJ45 / Ethernet Snap-in Bracket - WHITE RJ45 / Ethernet Snap-in Bracket - BLACK	Female to female coupler	
MOD007 MOD042	USB B Type to USB B Type Snap-in Bracket -WHITE USB B Type to USB B Type Snap-in Bracket -BLACK	Female to female coupler with 100mm cable length	
MOD008 MOD043	Toslink Snap-in Bracket - WHITE Toslink Snap-in Bracket - BLACK	Female to female coupler	
MOD009 MOD044	HDMI Female to Female Snap-in Bracket - WHITE HDMI Female to Female Snap-in Bracket - BLACK	Female to female coupler with 200mm cable length	
MOD010 MOD045	F Type Snap-in Bracket - WHITE F Type Snap-in Bracket - BLACK	Female to female coupler	
MOD011 MOD046	VGA and Stereo Audio (3.5mm) Snap-in Bracket- WHITE VGA and Stereo Audio (3.5mm) Snap-in Bracket- BLACK	Female to terminal blocks with 100mm cable length	
MOD012 MOD047	VGA and Stereo Audio (3.5mm) Snap-in Bracket- WHITE VGA and Stereo Audio (3.5mm) Snap-in Bracket- BLACK	Female to female coupler with 100mm cable length	
MOD013 MOD048	RGB Snap-in Bracket-WHITE RGB Snap-in Bracket-BLACK	Female to terminal blocks with 100mm cable length	
MOD014	RGB Snap-in Bracket	Female to female coupler with 100mm cable length	
MOD015 MOD049	Right, Left, Video Snap-in Bracket-WHITE Right, Left, Video Snap-in Bracket-BLACK	Female to terminal blocks with 100mm cable length	
MOD016 MOD050	Right, Left, Video Snap-in Bracket-WHITE Right, Left, Video Snap-in Bracket-BLACK	Female to female coupler with 100mm cable length	
MOD017	Svideo Snap-in Bracket	Female to terminal blocks with 100mm cable length	
MOD018	Svideo Snap-in Bracket	Female to female coupler with 100mm cable length	
MOD019 MOD051	Speaker x4 Snap-in Bracket-WHITE Speaker x4 Snap-in Bracket-BLACK	Female to terminal blocks with 100mm cable length	
MOD020 MOD052	Displayport Female to Female Snap-in Bracket- WHITE Displayport Female to Female Snap-in Bracket- BLACK	Female to female coupler with 200mm cable length	
MOD053 MOD054	UK Power Socket Snap In 50mmx50mm– WHITE UK Power Socket Snap In 50mmx50mm-BLACK	Requires manual assembly to mains cable	

*Female to female coupler – Uses standard AV cables to complete installation.

*Female to terminal blocks – Uses standard AV cables cut and stripped into terminal blocks.

Modular System – Part Number Reference Sheet (Mounting Hardware)



Part Number	Description	Connectivity method*	
SG215	Single Gang Backbox 47mm depth (with strain relief)	N/A	
SG216	Dual Gang Backbox 47mm depth (with strain relief)	N/A	
SG217	Single Gang Backbox 47mm depth (with strain relief) BLACK	N/A	
SG218	Dual Gang Backbox 47mm depth (with strain relief) BLACK	N/A	
MOD055	Snap in collar for mounting hardware and suitable panels	See mounting hardware as below	
MOD032	Modular Under desk Mount Assembly, accepts 2 x 50mm modular inserts (MOD055)	Use MOD055 inserts and then populate with MOD snap in assemblies	
MOD033	Modular Under desk Mount Assembly, accepts 4 x 50mm modular inserts (MOD055)	Use MOD055 inserts and then populate with MOD snap in assemblies	
MOD030	Modular Desk Pop-Up Assembly, accepts 1 x 50mm modular inserts (MOD055)	Use MOD055 inserts and then populate with MOD snap in assemblies	
MOD031	Modular Desk Pop-Up Assembly, accepts 2 x 50mm modular inserts (MOD055)	Use MOD055 inserts and then populate with MOD snap in assemblies	
MOD056	Modular Desk Tower Pop-Up Assembly, accepts 5 x 50mm modular inserts (MOD055)*. NB See detailed spec for more details about mounting options*.	Use MOD055 inserts and then populate with MOD snap in assemblies	

Modular System – Part Number Reference Sheet (Modular Kits)




Part Number	Description	Connectivity method*	
SG282	Single Gang Modular Kit, Complete (Bevelled Faceplate)	Various, see spec sheet for further details	
SG331	Single Gang Modular Kit, Complete (Flat Faceplate)	Various, see spec sheet for further details	
SG283	Dual Gang Modular Kit, Complete (Bevelled Faceplate)	Various, see spec sheet for further details	
SG332	Dual Gang Modular Kit, Complete (Flat Faceplate)	Various, see spec sheet for further details	

Keystone Jack System – Part Number Reference Sheet

Part Number	Description	Connectivity method*	
MOD001 MOD024 MOD036	Single Gang Bracket – Bevelled Single Gang Bracket – Flat Single Gang Bracket – Flat (BLACK)	N/A	
MOD002 MOD021 MOD022 MOD023 MOD025 MOD037	Dual Gang Bracket (White Plastic-Bevelled) Dual Gang Bracket (Chrome effect) Dual Gang Bracket (Black Nickel) Dual Gang Bracket (Stainless Steel) Dual Gang Bracket (White Plastic-Flat) Dual Gang Bracket (Black Plastic-Flat)	N/A	See spec sheet for pictures and further details
MOD026 MOD027 MOD028 MOD029	Single Gang Brush plate-Black Single Gang Brush plate-White Dual Gang Brush plate-Black Dual Gang Brush plate-White	N/A	
MOD003 MOD038	10mm x 50mm Blank Snap-in Bracket 10mm x 50mm Blank Snap-in Bracket (BLACK)	N/A	
MOD004 MOD039	20mm x 50mm Blank Snap-in Bracket 20mm x 50mm Blank Snap-in Bracket (BLACK)	N/A	
MOD040	25mm x 50mm Blank Snap-in Bracket (BLACK)	N/A	
MOD005	50mm x 50mm Snap-in Blank Bracket	N/A	
KEY001	1 X Keystone Housing Module	N/A	
KEY002	2 X Keystone Housing Module	N/A	
KEY003	HDMI Feedthrough Module (clips into KEY001 or KEY002)	Female to Female Coupler	
KEY004	VGA Feedthrough Module	Female to Female Coupler	
KEY005	USB Feedthrough Module (clips into KEY001 or KEY002)	Female to Female Coupler	
SG294	Single gang network plate preloaded with 1 x SG296	Female to IDC termination	
SG295	Single gang network plate preloaded with 2 x SG296	Female to IDC termination	
SG296	RJ45 Cat5e Jack Module (clips into KEY001 or KEY002)	Female to IDC termination	

*Female to female coupler – Uses standard AV cables to complete installation. Female to IDC termination – Uses standard cable on wall plate side, standard IDC termination on wall side.



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE RoSH
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY



Bevelled Single Gang Faceplate – 86 x 86mm MOD001
Flat Single Gang Faceplate – 86 x 86mm MOD024
Flat Single Gang Faceplate (BLACK) – 86 x 86mm MOD036


[Accepts 2 x 20mm modular inserts \(part numbers MODxxx\), plus one 10mm blank insert or:](#)

[Accepts 2 x 25mm Keystone jack inserts \(part numbers KEYxxx\)](#)



REVISION	NOTES	DATE		
A				
			DRAWN BY	
			DATE	
			UNITS	METRIC mm

MAT'L:	FINISH:
TITLE :	PART NO: MOD001 / MOD024 / MOD036



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE RoSH
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY



MOD002 – White Plastic (Bevelled)

Dual Gang Faceplate – 86 x 146mm

Accepts 5 x 20mm modular inserts (part numbers MODxxx) or:

Accepts 4 x 25mm Keystone jack inserts (part numbers KEYxxx)



MOD025 – White Plastic (Flat)



MOD021 – Chrome Effect



MOD022 – Black Nickel



MOD037 – Black Plastic (Flat)




MOD023 – Stainless Steel

REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	


FINISH:	
PART NO:	MOD002 / MOD021 / MOD022 / MOD023 / MOD025 / MOD037



DO NOT SCALE
IF IN DOUBT - ASK


ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



MOD026 – Single Gang Brush Plate

Suitable for use with MOD001, 024, 036



MOD027 – Single Gang Brush Plate

Suitable for use with MOD001, 024, 036



MOD028 – Dual Gang Brush Plate


Suitable for use with MOD002, 021, 022, 023, 025, 037



MOD029 – Dual Gang Brush Plate

Suitable for use with MOD002, 021, 022, 023, 025, 037
Pictured assembled to MOD002


REVISION	NOTES	DATE	MATERIAL:		FINISH:
A			TITLE: Black brush plate		PART NO: MOD026, 27, 28, 29
			DRAWN BY		
			DATE		
			UNITS	METRIC mm	



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



10mm x 50mm Blank insert
For use with:

MOD001	Single Gang Bracket – Bevelled
MOD024	Single Gang Bracket – Flat
MOD036	Single Gang Bracket – Flat (BLACK)
MOD002	Dual Gang Bracket (White Plastic-Bevelled)
MOD021	Dual Gang Bracket (Chrome effect)
MOD022	Dual Gang Bracket (Black Nickel)
MOD023	Dual Gang Bracket (Stainless Steel)
MOD025	Dual Gang Bracket (White Plastic-Flat)
MOD037	Dual Gang Bracket (Black Plastic-Flat)

MOD003 = WHITE
MOD038 = BLACK

REVISION	NOTES	DATE	DRAWN BY		MAT'L:	FINISH:
A			DATE		TITLE :	PART MOD003 / MOD038
			UNITS	METRIC mm		NO:



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE RoSH
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY




10mm x 50mm Blank insert

For use with:


MOD001	Single Gang Bracket – Bevelled
MOD024	Single Gang Bracket – Flat
MOD036	Single Gang Bracket – Flat (BLACK)
MOD002	Dual Gang Bracket (White Plastic-Bevelled)
MOD021	Dual Gang Bracket (Chrome effect)
MOD022	Dual Gang Bracket (Black Nickel)
MOD023	Dual Gang Bracket (Stainless Steel)
MOD025	Dual Gang Bracket (White Plastic-Flat)
MOD037	Dual Gang Bracket (Black Plastic-Flat)

MOD004 = WHITE

MOD039 = BLACK



REVISION	NOTES	DATE	DRAWN BY		MAT'L:	FINISH:
A			DATE		TITLE :	PART NO: MOD004 / MOD039
			UNITS	METRIC mm		



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM




25mm x 50mm Blank insert - BLACK

For use with:

MOD001	Single Gang Bracket – Bevelled
MOD024	Single Gang Bracket – Flat
MOD036	Single Gang Bracket – Flat (BLACK)
MOD002	Dual Gang Bracket (White Plastic-Bevelled)
MOD021	Dual Gang Bracket (Chrome effect)
MOD022	Dual Gang Bracket (Black Nickel)
MOD023	Dual Gang Bracket (Stainless Steel)
MOD025	Dual Gang Bracket (White Plastic-Flat)
MOD037	Dual Gang Bracket (Black Plastic-Flat)

MOD040 = BLACK




50mm x 25mm Blank insert

REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	

FINISH:	
PART NO:	MOD040



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT


INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



50mm x 50mm Blank insert - WHITE

For use with:

MOD001	Single Gang Bracket – Bevelled
MOD024	Single Gang Bracket – Flat
MOD036	Single Gang Bracket – Flat (BLACK)
MOD002	Dual Gang Bracket (White Plastic-Bevelled)
MOD021	Dual Gang Bracket (Chrome effect)
MOD022	Dual Gang Bracket (Black Nickel)
MOD023	Dual Gang Bracket (Stainless Steel)
MOD025	Dual Gang Bracket (White Plastic-Flat)
MOD037	Dual Gang Bracket (Black Plastic-Flat)



REVISION	NOTES	DATE
A		


DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:

FINISH:

TITLE :



PART NO: MOD005



DO NOT SCALE
IF IN DOUBT - ASK


ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



20mm x 50mm insert
Details of cutout (marked in red)

Fitted with RJ45 coupler



REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	


FINISH:	
PART NO:	MOD006 (RJ45) WHITE MOD041 (RJ45) BLACK



DO NOT SCALE
IF IN DOUBT - ASK


ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



20mm x 50mm insert
Details of cutout (marked in red)

Fitted with USB B Type Female Panel Mount to USB B Type Female Panel Mount x 100mm




REVISION	NOTES	DATE
A		
B	Hole dimension changed	

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	


FINISH:	
PART NO:	MOD007 (USB) WHITE MOD042 (USB) BLACK



DO NOT SCALE
IF IN DOUBT - ASK


ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Details of cutout (cutout marked in red)

Fitted with Toslink (Female to Female) Coupler




REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	


FINISH:	
PART NO:	MOD008 (TOSLINK) WHITE MOD043 (TOSLINK) BLACK



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Details of cutout (cutout marked in red)


Fitted with HDMI Female to Female Coupler
Flat Cable overall length 200mm



REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm


MAT'L:	FINISH:
TITLE :	PART NO: MOD009 (HDMI) WHITE MOD044 (HDMI) BLACK



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Details of cutout (cutout marked in red)

Fitted with F Type (Female to Female) Coupler



REVISION	NOTES	DATE
A		


DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:

FINISH:

TITLE :


PART NO: MOD010 (F TYPE) WHITE
MOD045 (F TYPE) BLACK



DO NOT SCALE
IF IN DOUBT - ASK


ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Details of cutout (cutout marked in red)


MOD011 Fitted with VGA Female and 3.5mm Stereo Jack
Cable length 100mm to terminal blocks



REVISION	NOTES	DATE
A		

DRAWN BY
DATE
UNITS METRIC mm

MAT'L:	FINISH:
TITLE :	PART NO: (VGA AND 3.5MM AUDIO) TERMINAL BLOCK WHITE=MOD011, BLACK=MOD046 (VGA AND 3.5MM AUDIO) COUPLER WHITE = MOD012, BLACK=MOD047



DO NOT SCALE
IF IN DOUBT - ASK



ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Terminal Block	Notes	15 Pin VGA Female
1	Red Signal	1
3	Green Signal	2
5	Blue Signal	3
7	Black	4
8	Brown	5
2	Red Screen	6
4	Green Screen	7
6	Blue Screen	8
	----	9
1	Red	10
2	Orange	11
3	Grey	12
4	Green	13
5	Blue	14
	----	15

Terminal Block	Notes	3.5mm Stereo Jack
1	Red	Tip
2	White	Centre
3	Screen	Screen



15 Pin VGA Female	Notes	15 Pin VGA Female
1	Red Signal	1
2	Green Signal	2
3	Blue Signal	3
4	Black	4
5	Brown	5
6	Red Screen	6
7	Green Screen	7
8	Blue Screen	8
9	----	9
10	Red	10
11	Orange	11
12	Grey	12
13	Green	13
14	Blue	14
15	----	15


3.5mm Stereo Jack	Notes	3.5mm Stereo Jack
Tip	Red	Tip
Centre	White	Centre
Screen	Screen	Screen

REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm


MAT'L:	
TITLE :	

FINISH:	
PART NO:	MOD011/012/046/047
	TECHNICAL DRAWING




ALL COMPONENTS TO BE ROHS COMPLIANT

INFORMATION USED HERE MAY ONLY BE USED IF AUTHORISED BY AVEXTRAS.COM




Details of cutout (cutout marked in red)

MOD013 RGB Cable 100mm Length to Terminal Blocks



REVISION	NOTES	DATE	DRAWN BY	DATE	UNITS	METRIC mm
A						



MAT'L:	FINISH:
TITLE :	PART NO: MOD013 RGB (TERMINAL BLOCK)-WHITE MOD048 RGB (TERMINAL BLOCK)-BLACK MOD 014 (COUPLER)




DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM




REVISION	NOTES	DATE	DRAWN BY		MATL:	FINISH:
A						
			DATE		TITLE :	PART NO: MOD013/014/048 TECHNICAL DRAWING
			UNITS	METRIC mm		



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Details of cutout (cutout marked in red)

MOD015 L,R,VIDEO Cable 100mm Length to Terminal Blocks



REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:

TITLE :

FINISH:


PART NO: MOD015 RGB (TERMINAL BLOCK)-WHITE
MOD049 RGB (TERMINAL BLOCK)-BLACK
MOD 016 (COUPLER)-WHITE
MOD 050 (COUPLER)-BLACK




DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



MOD015/049



MOD016/050

REVISION	NOTES	DATE
A		


DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:

FINISH:

TITLE :


PART NO: MOD015,016,049,050
TECHNICAL DRAWING



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Details of cutout (cutout marked in red)

MOD017 Svideo with 100mm cable to Terminal Block




REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	

FINISH:	
PART NO:	MOD017 SVIDEO (TERMINAL BLOCK) AND MOD 018 SVIDEO (COUPLER)




DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM




MOD017



Terminal Block	Notes	Svideo Panel Nount
1	White Signal	1
2	White Screen	2
3	Red Screen	3
4	Red Signal	4

MOD018




Svideo Panel Nount	Notes	Svideo Panel Nount
1	White Signal	1
2	White Screen	2
3	Red Screen	3
4	Red Signal	4

REVISION	NOTES	DATE
A		



DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	FINISH:
TITLE :	PART NO: MOD017 AND MOD018 TECHNICAL DRAWING




ALL COMPONENTS TO BE ROHS COMPLIANT

INFORMATION USED HERE MAY ONLY BE USED IF AUTHORISED BY AVEXTRAS.COM



Terminal Block	Notes	Speaker Panel Mount
2	Black	1
1	Red	2
2	Black	3
1	Red	4

Fitted with 4 x Speaker Panel Mount Connectors to 100mm cable and 2 x terminal blocks




REVISION	NOTES	DATE
1	6mm gap added between all terminal cutouts	

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	



FINISH:	
PART NO:	MOD019 SPEAKER X 4 - WHITE MOD051 SPEAKER X 4 - BLACK



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Details of cutout (cutout marked in red)

Fitted with Displayport Female to Female Coupler
Round Cable overall length 200mm




REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	


FINISH:	
PART NO:	MOD020 DISPLAYPORT-WHITE MOD052 DISPLAYPORT-BLACK



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Snap in Modular Collar


Accepts modules in 50x50mm aperture

REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	

FINISH:	
PART NO:	MOD055



DO NOT SCALE
IF IN DOUBT - ASK


ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



50X50MM Modular UK Socket

REVISION	NOTES	DATE			MAT'L:	FINISH:
A						
			DRAWN BY		TITLE :	PART NO: MOD053 - WHITE MOD054 - BLACK
			DATE			
			UNITS	METRIC mm		



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



- 1. MOD001 single gang bracket
- 2. MOD007 PLATE
- 3. MOD016 PLATE
- 4. MOD012 PLATE
- 5. MOD003, 10MM BLANK



SG282

-Bevelled faceplate

- 1. MOD024 single gang bracket
- 2. MOD007 PLATE
- 3. MOD016 PLATE
- 4. MOD012 PLATE
- 5. MOD003, 10MM BLANK



SG331

-Flat faceplate

REVISION	NOTES	DATE
A		


DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:

FINISH:

TITLE : MODULAR KIT, SINGLE GANG

PART NO: SG282 & SG331



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



1. MOD002 dual gang bracket
2. MOD007 PLATE
3. MOD016 PLATE
4. MOD012 PLATE x 2 pieces
5. MOD018 PLATE
6. MOD004 20MM BLANK X 3 PIECES



SG283

-Bevelled faceplate


1. MOD025 dual gang bracket
2. MOD007 PLATE
3. MOD016 PLATE
4. MOD012 PLATE x 2 pieces
5. MOD018 PLATE
6. MOD004 20MM BLANK X 3 PIECES



SG332

-Flat faceplate

REVISION	NOTES	DATE	DRAWN BY		MAT'L:	FINISH:
A						
			DATE		TITLE : MODULAR KIT, DUAL GANG	PART NO: SG283 & SG332
			UNITS	METRIC mm		



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Description

Features cable strain relief and 45mm width cable exit. Suitable for AV installations.

Colour: White
Depth: 47mm
Height: 85mm
Width: 170mm




REVISION	NOTES	DATE
A		

DRAWN BY	
DATE	
UNITS	METRIC mm

MAT'L:	
TITLE :	


FINISH:	
PART NO:	SG216 DUAL GANG-WHITE SG218 DUAL GANG-BLACK



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM




Description

Features cable strain relief and 45mm width cable exit. Suitable for AV installations.

Colour: White
Depth: 47mm
Height: 85mm
Width: 85mm





REVISION	NOTES	DATE			MAT'L:	FINISH:
A						
			DRAWN BY		TITLE :	PART NO: SG215 SINGLE GANG-WHITE SG217 SINGLE GANG-BLACK
			DATE			
			UNITS	METRIC mm		



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM




UNDERDESK MOUNT MODULAR ASSEMBLIES


- MOD032- Accepts 2x50mm modular snap in collars (MOD055)
- MOD033- Accepts 4x50mm modular snap in collars (MOD055)

Suitable for mounting direct to desks, walls etc.

Accepts the full range of modular inserts when mounted with part MOD055.



REVISION	NOTES	DATE	DRAWN BY		MAT'L:	FINISH:
A						
			DATE		TITLE : UNDERDESK MOUNT MODULAR ASSEMBLIES	PART NO: MOD032 2x50mm INSERTS MOD033 4x50mm INSERTS
			UNITS	METRIC mm		



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



POP-UP DESK MOUNT MODULAR ASSEMBLIES

MOD030- Accepts 1x50mm modular snap in collars (MOD055)

MOD031- Accepts 2x50mm modular snap in collars (MOD055)

Suitable for mounting direct into desks, tables etc.

Accepts the full range of modular inserts when mounted with part
MOD055.

Simply push the button and spring loaded unit pops up.
Push back down and unit locks into place for tidy storage.

Supplied with integral plastic backbox.

REVISION	NOTES	DATE	DRAWN BY		MAT'L:	FINISH:
A						
			DATE		TITLE :	PART NO:
			UNITS	METRIC mm	POP-UP DESK MOUNT ASSEMBLIES	MOD030 1x50mm INSERTS MOD031 2x50mm INSERTS

DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



Picture of supplied unit.



MODULAR POP-UP TOWER ASSEMBLY

MOD056- Accepts 5x50mm* modular snap in collars (MOD055)* NB
Bottom collar is difficult to access and is suggested to blank off only,
similar to photos.

Suitable for mounting direct into desks, tables etc.

Accepts the full range of modular inserts when mounted with part
MOD055.


Simply push the button and it pops up.
Pull the unit up to gain access to modules. Push the unit back down and
push the button to recess again in the table top.

Supplied with plastic fixings.



Picture of unit fitted with MOD055
collars and modular inserts

REVISION	NOTES	DATE			MAT'L:	FINISH:
A						
			DRAWN BY		TITLE :	PART NO: MOD056 Modular Pop-Up Tower Assembly
			DATE			
			UNITS	METRIC mm		



DO NOT SCALE
IF IN DOUBT - ASK

ALL COMPONENTS TO BE ROHS
COMPLIANT

INFORMATION USED HERE
MAY ONLY BE USED IF
AUTHORISED BY AVEXTRAS.COM



3.5mm

Interlocking Ultra Low Profile Terminal Blocks 10A 3.5mm Pitch

REVISION	NOTES	DATE			MAT'L:	FINISH:
A						
			DRAWN BY		TITLE :	PART NO: Terminal block specification
			DATE			
			UNITS	METRIC mm		