




Agilent Rack Mount Accessory Products Cross Reference Guide

Selection Guide


The Rack mount Accessory Products provide rack mount accessory solutions for your Agilent instrument assets. These accessory products are being released in two waves, starting in May, 2011. These products are offered for standalone sales, and qualify for standard discounts. The Agilent Common Rack mount Accessory Cross Reference is designed to assist you in selecting the correct product to meet your needs. Simply identify the instrument needing the rack mount accessory, then look in the column corresponding to the type of accessory needed to find the accessory product number to order. Additional information is provided to help identify the correct item including the original instrument option for the accessory, the part number of the key component making up the accessory, and the accessory description. Agilent will be adding additional rack mount accessory products to broaden coverage to more instruments and more mounting options in the near future.



Handle products



Rackmount flanges with handles



Rackmount flange products



Rackmount flange for instruments with existing handles




Introduction.....	1
1CP series rack mount including handles accessories.....	2
1CM series rack mount accessories for instruments without handles.....	3
1CM series rack mount accessories for instruments with previously supplied handles.....	3
1CM series rack mount adapter kits	4
1CN series handles accessories	4
Technical specifications	5
Contact Agilent.....	77

1CP series rack mount including handles accessories

Maneuver and securely mount your Agilent products into rack enclosures

Flange kits are available for all System II instruments. Flanges attach to pre-existing holes in the instrument case. These flanges have a notch for handles, and this kit includes both flanges and handles.




Instrument module height	Flange kit with handles (order new product if available)	New rackmount product (currently available if populated)
88.1 mm (3.5 in)	5063-9219	1CP011A
88.1 mm (3.5 in)	5063-9220	Future release, order 5063-9220
132.6 mm (5.25 in)	5063-9221	1CP008A
177.0 mm (7.0 in)	5063-9222	1CP005A
221.5 mm (8.75 in)	5063-9223	1CP020A
265.9 mm (10.5 in)	5063-9224	1CP019A
310.4 mm (12.25 in)	5063-9225	Future release, order 5063-9225
Kit includes	2 flanges, 2 handles, mounting screws, metric fasteners	
The following kits use standard flanges with 1.75 in hole spacing: 5063-9212/9219/9232		
The following kits use special flange with 3 in hole spacing: 5063-9213/9220		

1CM series rack mount accessories for instruments without handles

Securely mount your Agilent products into rack enclosures

Flange kits are available for all System II instruments. Flanges attach to pre-existing holes in the instrument case. These flanges do not have a notch for handles, and therefore cannot be used for instruments that have handles.

- Will not fit onto instruments with previously supplied handles.



Instrument module height	Rackmount flange kit (order new product if available)	New rackmount product (currently available, if populated)
88.1 mm (3.5 in)	5063-9212	34191A
132.6 mm (5.25 in)	5063-9214	34192A
177.0 mm (7.0 in)	5063-9215	1CM013A
221.5 mm (8.75 in)	5063-9216	1CM015A
265.9 mm (10.5 in)	5063-9217	1CM042A
310.4 mm (12.25 in)	5063-9218	1CM033A
Kit includes	2 flanges, mounting screws, metric fasteners	
The following kits use standard flanges with 1.75 in hole spacing: 5063-9212/9219/9232		
The following kits use special flange with 3 in hole spacing: 5063-9213/9220		

1CM series rack mount accessories for instruments with previously supplied handles

Securely mount your Agilent products into rack enclosures

Certain Agilent instruments are supplied with front handles. These flange kits have a special cut out to accommodate the handles.


- Flanges attach to pre-existing holes in the instrument case.




Instrument module height	Flange kit for instruments with previously supplied handles (order new product if available)	New rackmount product (currently available, if populated)
88.1 mm (3.5 in)	5063-9232	Future release, order 5063-9232
132.6 mm (5.25 in)	5063-9234	Future release, order 5063-9234
221.5 mm (8.75 in)	5063-9236	1CM043A
265.9 mm (10.5 in)	5063-9237	Future release, order 5063-9237
Kit includes	2 flanges, mounting screws, metric fasteners	
The following kits use standard flanges with 1.75 in hole spacing: 5063-9212/9219/9232		
The following kits use special flange with 3 in hole spacing: 5063-9213/9220		

1CM series rack mount adapter kits

Securely mount your Agilent products with pre-existing handles into rack enclosures



Rack mount adapter kits for 88.1 mm instrument module height (5063-9239, 5063-9240 (34190A), 5063-9241, 1CM019A)



Rack mount adapter kits for 1/2 MW (5063-9240 (34190A), 5063-9243 (34193A), 5063-9245)



Rack mount adapter kit with mounting hardware (5063-9239)

Instrument module height	Mounts 1/4 MW modules	New product (currently available)	Mounts 1/2 MW or 2 each 1/4 MW modules	New product (currently available)	Mounts 3/4 MW (3 each or 1/4 and 1/2 MW side by side)	New product (currently available)
88.1 mm (3.5 in)	5063-9239	Future release, order 5063-9239	5063-9240	34190A	5063-9241	1CM019A
132.6 mm (5.25 in)	–	–	5063-9243	34193A	–	–
177.0 mm (7.0 in)	–	–	5063-9245	1CM068A	–	–
Kit includes	1 rack flange + 3/4 MW, extension adapter flange, screws		1 rack flange + 1/2 MW, extension adapter flange, screws		1 rack flange + 1/4 MW, extension adapter flange, screws	

Side by side modules of equal depth require a lock link kit (5061-9694) 1/4 MW can be center mounted using two of these kits

1CN series handles accessories

Add handles to your Agilent products for easier maneuvering and lifting

Order a front handle kit when your instrument does not come with pre-installed handles. Check to make sure your instrument requires handles, as many instruments are supplied with previously installed handles.

- Flanges attach to pre-existing holes in the instrument case.
- A plastic trim strip is easily removed and the handle or flange attaches with screws supplied in the kit.
- Before rack mounting, bottom feet must be removed.



Instrument module height	Front handle kit (order new product if available)	New handle product (currently available, if populated)
88.1 mm (3.5 in)	5063-9226	1CN006A
132.6 mm (5.25 in)	5063-9227	1CN007A
177.0 mm (7.0 in)	5063-9228	1CN003A
221.5 mm (8.75 in)	5063-9229	1CN005A
265.9 mm (10.5 in)	5063-9230	1CN020A
Kit includes	2 handles, 2 trim strips, metric fasteners	

Technical specifications

Instrument info			Common accessory product categories					Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
105B	105B-908	–	Contact parts ID	–	–	–	–	Contact parts ID
11713B	11713B-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
11713B	11713B-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
11713C	11713C-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
11713C	11713C-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
11757B	11757B-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
11757B	11757B-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
11758B	11758B-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
11758B	11758B-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
11759C	11759C-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
11759C	11759C-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
11759C	11759C-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
11759D	11759D-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
11759D	11759D-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
11759D	11759D-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
11896A	11896A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
11896A	11896A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
11896A	11896A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
11980A	11980A-907	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
11980A	11980A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
16700B	16700B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
16701B	16701B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
1670G	1670G-1CM	–	5063-2157 (1)	–	–	–	–	Rack mount kit

Technical specifications (continued)

Instrument info			Common accessory product categories					Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
1671G	1671G-1CM	–	5063-2157 (1)	–	–	–	–	Rack mount kit
1672G	1672G-1CM	–	5063-2157 (1)	–	–	–	–	Rack mount kit
1673G	1673G-1CM	–	5063-2157 (1)	–	–	–	–	Rack mount kit
1680A	1680A-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1680AD	1680AD-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1681A	1681A-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1681AD	1681AD-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1682A	1682A-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1682AD	1682AD-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1683A	1683A-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1683AD	1683AD-1CM	–	01680-60002 (1)	–	–	–	–	Metal-raw material
1690A	1690A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
1690AD	1690AD-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
1691A	1691A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
1691AD	1691AD-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
1692A	1692A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
1692AD	1692AD-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
1693A	1693A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
1693AD	1693AD-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
33120A	33120A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
33210A	33210A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
33210A	33210A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
33220A	33220A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
33220A	33220A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
33250A	33250A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
33250A	33250A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
33502A	33502A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
33502A	33502A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
33521A	33521A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
33521A	33521A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
33522A	33522A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
33522A	33522A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
34401A	34401A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
34405A	34405A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
34410A	34410A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
34410A	34410A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
34411A	34411A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
34411A	34411A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
34420A	34420A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
3457A	3457A-907	5062-5380 (1)	–	–	–	–	–	907 front handle kit
3458A	3458A-907	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
3458A	3458A-908	–	34191A	–	–	–	–	Dual flange kit, 2U

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
3458A	3458A-909	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
3488A	3488A-907	5062-5380 (1)	–	–	–	–	–	907 front handle kit
34970A	34970A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
34972A	34972A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
34980A	Y1130A	–	Y1130A	–	–	–	–	Rackmount kit for 34980A, forward or reverse mount in standard 19 IN rack
3499A	3499A-1CM	–	1CM029A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets
3499A	3499A-1CP	–	–	–	–	1CP016A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
3499B	3499B-1CM	–	–	–	1CM032A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
35670A	35670A-AX4	–	1CM069A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
35670U	35670U-AX4	–	1CM069A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
4142B	4142B-907	Contact parts ID	–	–	–	–	–	Contact parts ID
4142B	4142B-908	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4142B	4142B-909	–	–	–	–	5062-3985 (1)	–	Rack flange and front handle kit
41501B	41501B-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
4155C	4155C-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4263B	4263B-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
4263B	4263B-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
4268A	4268A-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
4268A	4268A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
4279A	4279A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
4279A	4279A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
4279A	4279A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
42841A	42841A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
42841A	42841A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
42841A	42841A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
4284A	4284A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
4284A	4284A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
4284A	4284A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
4285A	4285A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
4285A	4285A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
4285A	4285A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
4287A	4287A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4287A	4287A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
4287A	4287A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
4288A	4288A-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
4288A	4288A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
4291B	4291B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4291B	4291B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
4291B	4291B-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
4294A	4294A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4294A	4294A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
4294A	4294A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
4338B	4338B-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
4338B	4338B-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
4339B	4339B-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
4339B	4339B-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
4349B	4349B-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
4349B	4349B-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
43521A	43521A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
43521A	43521A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
43521A	43521A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
4352B	4352B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4352B	4352B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
4352B	4352B-1CP	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
4395A	4395A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4395A	4395A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
4395A	4395A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
4396B	4396B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
4396B	4396B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
4396B	4396B-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
5071A	5071A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
5071A	5071A-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
5087A	5087A-908	–	Contact Parts ID	–	–	–	–	Contact parts ID
5089A	5089A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
5089A	5089A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
53131A	53131A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
53132A	53132A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
53147A	53147A-1CM	–	53147-67001 (1)	–	–	–	–	Kit rack mount
53148A	53148A-1CM	–	53147-67001 (1)	–	–	–	–	Kit rack mount
53149A	53149A-1CM	–	53147-67001 (1)	–	–	–	–	Kit rack mount
53150A	53150A-1CM	–	–	–	53150-67001 (1)	–	–	Sgt rack mount
53151A	53151A-1CM	–	–	–	53150-67001 (1)	–	–	Sgt rack mount
53152A	53152A-1CM	–	–	–	53150-67001 (1)	–	–	Sgt rack mount
53181A	53181A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
53210A	53210A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
53210A	53210A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
53220A	53220A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
53220A	53220A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
53230A	53230A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
53230A	53230A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
54621A	54621A-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54621D	54621D-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54622A	54622A-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54622D	54622D-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
54624A	54624A-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54641A	54641A-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54641D	54641D-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54642A	54642A-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54642D	54642D-1CM	–	5062-7345 (1)	–	–	–	–	Rack mount kit
54810A	54810A-1CM	–	E2609B	–	–	–	–	Rack mount
54815A	54815A-1CM	–	E2609B	–	–	–	–	Rack mount
54820A	54820A-1CM	–	E2609B	–	–	–	–	Rack mount
54825A	54825A-1CM	–	E2609B	–	–	–	–	Rack mount
54830B	54830B-1CM	–	E2609B	–	–	–	–	Rack mount
54830D	54830D-1CM	–	E2609B	–	–	–	–	Rack mount
54831B	54831B-1CM	–	E2609B	–	–	–	–	Rack mount
54831D	54831D-1CM	–	E2609B	–	–	–	–	Rack mount
54832B	54832B-1CM	–	E2609B	–	–	–	–	Rack mount
54832D	54832D-1CM	–	E2609B	–	–	–	–	Rack mount
54833A	54833A-1CM	–	E2609B	–	–	–	–	Rack mount
54833D	54833D-1CM	–	E2609B	–	–	–	–	Rack mount
54835A	54835A-1CM	–	E2609B	–	–	–	–	Rack mount
54845A	54845A-1CM	–	E2609B	–	–	–	–	Rack mount
54845B	54845B-1CM	–	E2609B	–	–	–	–	Rack mount
54846A	54846A-1CM	–	E2609B	–	–	–	–	Rack mount
54846B	54846B-1CM	–	E2609B	–	–	–	–	Rack mount
54852A	54852A-1CM	–	E2609B	–	–	–	–	Rack mount
54853A	54853A-1CM	–	E2609B	–	–	–	–	Rack mount
54854A	54854A-1CM	–	E2609B	–	–	–	–	Rack mount
54855A	54855A-1CM	–	E2609B	–	–	–	–	Rack mount
6010A	6010A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6010A	6010A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6011A	6011A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6011A	6011A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6012B	6012B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6012B	6012B-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6015A	6015A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6015A	6015A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6030A	6030A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6030A	6030A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6031A	6031A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6031A	6031A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6032A	6032A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6032A	6032A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6033A	6033A-800	–	1CM034A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
6033A	6033A-908	–	–	–	1CM001A	–	–	Rack mount flange kit 177.0 mm H (4U) - one bracket, one half-module bracket
6035A	6035A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6035A	6035A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6038A	6038A-800	–	1CM034A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
6038A	6038A-908	–	–	–	1CM001A	–	–	Rack mount flange kit 177.0 mm H (4U) - one bracket, one half-module bracket
6060B	6060B-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6060B	6060B-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6063B	6063B-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6063B	6063B-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6541A	6541A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6541A	6541A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6542A	6542A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6542A	6542A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6543A	6543A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6543A	6543A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6544A	6544A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1mm H (2U) - two flange brackets; 1.75 in hole spacing
6544A	6544A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6545A	6545A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6545A	6545A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6551A	6551A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6551A	6551A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6552A	6552A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6552A	6552A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6553A	6553A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6553A	6553A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6554A	6554A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6554A	6554A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6555A	6555A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6555A	6555A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6571A	6571A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6571A	6571A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6572A	6572A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6572A	6572A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6573A	6573A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6573A	6573A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6574A	6574A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6574A	6574A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6575A	6575A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6575A	6575A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
66000A	66000A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
66000A	66000A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
6611C	6611C-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6611C	6611C-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
6612C	6612C-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
6612C	6612C-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
6613C	6613C-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
6613C	6613C-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
6614C	6614C-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
6614C	6614C-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
6621A	6621A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6621A	6621A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6622A	6622A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6622A	6622A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6623A	6623A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6623A	6623A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6624A	6624A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6624A	6624A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6625A	6625A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6625A	6625A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6626A	6626A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6626A	6626A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6627A	6627A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6627A	6627A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6628A	6628A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6628A	6628A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6629A	6629A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6629A	6629A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
66309B	66309B-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66309B	66309B-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
66309D	66309D-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66309D	66309D-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
66311B	66311B-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66311B	66311B-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
66311D	66311D-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66311D	66311D-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
66312A	66312A-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66312A	66312A-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
66319B	66319B-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
66319B	66319B-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
66319D	66319D-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66319D	66319D-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
6631B	6631B-1CM	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6631B	6631B-1CP	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
66321B	66321B-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66321B	66321B-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
66321D	66321D-1CM	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
66321D	66321D-AXS	–	1CM021A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 1.75 in hole space, side-by-side mounting
6632B	6632B-1CM	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6632B	6632B-1CP	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
66332A	66332A-1CM	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
66332A	66332A-1CP	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6633B	6633B-1CM	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6633B	6633B-1CP	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6634B	6634B-1CM	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6634B	6634B-1CP	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6641A	6641A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6641A	6641A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6642A	6642A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6642A	6642A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6643A	6643A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6643A	6643A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6644A	6644A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6644A	6644A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6645A	6645A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
6645A	6645A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
6651A	6651A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6651A	6651A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6652A	6652A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6652A	6652A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6653A	6653A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6653A	6653A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6654A	6654A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6654A	6654A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6655A	6655A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6655A	6655A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6671A	6671A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6671A	6671A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6672A	6672A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6672A	6672A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6673A	6673A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6673A	6673A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6674A	6674A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6674A	6674A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6675A	6675A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6675A	6675A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6680A	6680A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
6680A	6680A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6681A	6681A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
6681A	6681A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6682A	6682A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
6682A	6682A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6683A	6683A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
6683A	6683A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6684A	6684A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
6684A	6684A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6690A	6690A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
6690A	6690A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6691A	6691A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
6691A	6691A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6692A	6692A-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
6692A	6692A-909	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
6811B	6811B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6811B	6811B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6812B	6812B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6812B	6812B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
6813B	6813B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
6813B	6813B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
70001A	70001A-810	–	–	–	–	–	5062-0781 (1)	Mainframe heavy duty rack slide kit
70001A	70001A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
70001A	70001A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
70004A	70004A-810	–	–	–	–	–	5062-7086 (1); 5062-0781 (1)	Kit, rack slide; mainframe heavy duty rack slide kit

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
70004A	70004A-908	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
70004A	70004A-913	–	–	5062-4073 (1)	–	–	–	Rack mount kit
71209A	71209A-810	–	–	–	–	–	5062-0781 (1)	Mainframe heavy duty rack slide kit
71210C	71210C-810	–	–	–	–	–	5062-7086 (1); 5062-0781 (2)	Kit, rack slide; mainframe heavy duty rack slide kit
71400C	71400C-908	–	Contact parts ID	–	–	–	–	Contact parts ID
71400C	71400C-913	–	–	1CM035A (1); 5062-4073 (1)	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles; rack mount kit
71450B	71450B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
71451B	71451B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
71452B	71452B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
71501D	71501D-908	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
71501D	71501D-913	–	–	5062-4073 (1)	–	–	–	Rack mount kit
71707A	71707A-908	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
71707A	71707A-913	–	–	5062-4073 (1)	–	–	–	Rack mount kit
71708A	71708A-908	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
71708A	71708A-913	–	–	5062-4073 (1)	–	–	–	Rack mount kit
71910A	71910A-810	–	–	–	–	–	5062-7086 (1); 5062-0781 (2)	Kit, rack slide; mainframe heavy duty rack slide kit
81101A	81101A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
81101A	81101A-1CN	1CN018A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
81101A	81101A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
81101A	81101A-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
81104A	81104A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
81104A	81104A-1CN	1CN018A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
81104A	81104A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
81104A	81104A-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
8110A	8110A-1CM	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
8110A	8110A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
8110A	8110A-1CP	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
8110A	8110A-1CR	–	–	–	–	–	1494-0060 (1)	Kit-slide, standard
81110A	81110A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
81110A	81110A-1CN	1CN018A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
81110A	81110A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
81110A	81110A-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
81130A	81130A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
81130A	81130A-1CN	1CN018A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
81130A	81130A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
81130A	81130A-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
81133A	81133A-1CP	–	–	–	–	Contact parts ID	–	Contact parts ID
81134A	81134A-1CP	–	–	–	–	Contact parts ID	–	Contact parts ID
8114A	8114A-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8114A	8114A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8114A	8114A-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8114A	8114A-1CR	–	–	–	–	–	1494-0060 (1)	Kit-slide, standard
81180A	81180A-1CP	–	–	–	–	Contact parts ID	–	Contact parts ID
8133A	8133A-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8133A	8133A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8133A	8133A-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8133A	8133A-1CR	–	–	–	–	–	1494-0060 (1)	Kit-slide, standard
8163A	8163A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
8163B	8163B-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
8164A	8164A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8164A	8164A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8164B	8164B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8164B	8164B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8166B	8166B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: standard
8340B	8340B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8340B	8340B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83420A	83420A-908	–	5062-3976 (1)	–	–	–	–	Rack mount kit
83420A	83420A-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
83424A	83424A-908	–	5062-3976 (1)	–	–	–	–	Rack mount kit
83424A	83424A-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
83425A	83425A-908	–	5062-3976 (1)	–	–	–	–	Rack mount kit
83425A	83425A-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
83437A	83437A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
83437A	83437A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
83437A	83437A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
83438A	83438A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
83438A	83438A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
83438A	83438A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
83475B	83475B-908	–	5062-7345 (1)	–	–	–	–	Rack mount kit
83480A	83480A-907	54710-68703 (1)	–	–	–	–	–	Front handle kit
8350B	8350B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8350B	8350B-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
83620A	83620A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83620A	83620A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83620B	83620B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83620B	83620B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83621A	83621A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83621A	83621A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83621B	83621B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83621B	83621B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83622A	83622A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83622A	83622A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83622B	83622B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83622B	83622B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83623A	83623A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83623A	83623A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
83623B	83623B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83623B	83623B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83623L	83623L-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83623L	83623L-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83624A	83624A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83624A	83624A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83624B	83624B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83624B	83624B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83630A	83630A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83630A	83630A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83630B	83630B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83630B	83630B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83630L	83630L-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83630L	83630L-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83631A	83631A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83631A	83631A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83631B	83631B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0mm H (4U) - two flange brackets
83631B	83631B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
83640A	83640A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83640A	83640A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83640B	83640B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83640B	83640B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83640L	83640L-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83640L	83640L-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83650A	83650A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83650A	83650A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83650B	83650B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83650B	83650B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83650L	83650L-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83650L	83650L-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83651A	83651A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83651A	83651A-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83651B	83651B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
83651B	83651B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
83711B	83711B-1CH	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
83711B	83711B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
83711B	83711B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
83711B	83711B-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
83712B	83712B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
83712B	83712B-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
83731B	83731B-1CH	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
83731B	83731B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
83731B	83731B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
83731B	83731B-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
83732B	83732B-1CH	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
83732B	83732B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
83732B	83732B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
83732B	83732B-1CR	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
83751A	83751A-1CH	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
83751A	83751A-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
83751A	83751A-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
83751A	83751A-1CR	–	–	–	–	–	1494-0015 (1)	Slide kit for support shelf
83751B	83751B-1CH	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
83751B	83751B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
83751B	83751B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
83751B	83751B-1CR	–	–	–	–	–	1494-0015 (1)	Slide kit for support shelf
83752A	83752A-1CH	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
83752A	83752A-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
83752A	83752A-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
83752A	83752A-1CR	–	–	–	–	–	1494-0015 (1)	Slide kit for support shelf
83752B	83752B-1CH	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
83752B	83752B-1CM	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
83752B	83752B-1CP	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
83752B	83752B-1CR	–	–	–	–	–	1494-0015 (1)	Slide kit for support shelf
8444A	8444A-908	–	Contact parts ID	–	–	–	–	Contact parts ID
8449B	8449B-907	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
8449B	8449B-908	–	–	–	1CM024A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one half-module bracket
85046A	85046A-908	–	5062-3976 (1)	–	–	–	–	Rack mount kit
85046A	85046A-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
85046B	85046B-908	–	5062-3976 (1)	–	–	–	–	Rack mount kit
85046B	85046B-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
85047A	85047A-908	–	5062-3976 (1)	–	–	–	–	Rack mount kit
85047A	85047A-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
8504B	8504B-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8504B	8504B-1CN	1CN003A (2)	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
8504B	8504B-1CP	–	–	–	–	1CP005A (2)	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
85060C	85060C-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
8509A	8509A-1CM	–	34192A (2)	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8509A	8509A-1CN	1CN007A (2)	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8509A	8509A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8509B	8509B-1CM	–	34192A (2)	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8509B	8509B-1CN	1CN007A (2); 1CP008A (2)	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles; Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8509C	8509C-1CM	–	34192A (2)	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8509C	8509C-1CN	1CN007A (2); 1CP008A (2)	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles; Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8511A	8511A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8511A	8511A-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
8511B	8511B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8511B	8511B-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
8514B	8514B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8514B	8514B-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
8515A	8515A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8515A	8515A-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
8517A	8517A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8517A	8517A-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
8517B	8517B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8517B	8517B-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
85309A	85309A-908	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
85309A	85309A-913	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
85309B	85309B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
85309B	85309B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8530A	8530A-908	–	1CM003A (1); 1CM023A (1)	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange bracket; Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8530A	8530A-913	–	–	5062-4071 (1); 1CM035A (1)	–	–	–	Rack mount kit; Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
85310A	85310A-908	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
85310A	85310A-913	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
85330A	85330A-913	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
85420E	85420E-1CM	–	–	5062-4071 (1)	–	–	–	Rack mount kit
85422E	85422E-1CM	–	–	5062-4073 (1)	–	–	–	Rack mount kit
85460A	85460A-1CM	–	–	5062-4071 (1)	–	–	–	Rack mount kit
85462A	85462A-1CM	–	–	5062-4073 (1)	–	–	–	Rack mount kit
85523A	85523A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
85523A	85523A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
85523A	85523A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
8560E	8560E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8560E	8560E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8560EC	8560EC-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8560EC	8560EC-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8560EC	8560EC-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8560EC	8560EC-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8560U	8560U-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8560U	8560U-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8561E	8561E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8561E	8561E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8561EC	8561EC-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8561EC	8561EC-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8562E	8562E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8562E	8562E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8562EC	8562EC-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8562EC	8562EC-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8562EC	8562EC-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8562EC	8562EC-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8562U	8562U-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8562U	8562U-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8563A	8563A-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8563A	8563A-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8563E	8563E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8563E	8563E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8563EC	8563EC-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8563EC	8563EC-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8563EC	8563EC-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8563EC	8563EC-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8563U	8563U-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8563U	8563U-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8564E	8564E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8564E	8564E-909	–	–	–	–	5062-4840 (1)	–	Rack Mount Kit
8564EC	8564EC-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8564EC	8564EC-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8564EC	8564EC-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8564EC	8564EC-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8564U	8564U-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8564U	8564U-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
85650A	85650A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
85650A	85650A-913	–	–	1CM005A	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two brackets for units with handles
8565E	8565E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8565E	8565E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8565EC	8565EC-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8565EC	8565EC-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8565EC	8565EC-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8565EC	8565EC-C91	–	5062-4841 (1)	–	–	-----	–	Rack mount kit without handles
8565U	8565U-C90	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8565U	8565U-C91	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
85660B	85660B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
85660B	85660B-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
85662A	85662A-908	–	1CM003A (1); 85662-60229 (1)	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets; KIT RACK MT PNL
85662A	85662A-913	–	–	5062-4071 (1); 85662-60229 (1)	–	–	–	Rack mount kit; KIT RACK MT PNL
85670A	85670A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
85670A	85670A-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
85680B	85680B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
85680B	85680B-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
85685A	85685A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
85685A	85685A-913	–	–	5062-4071 (1)	–	–	–	Rack mount kit
8590L	8590L-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8590L	8590L-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8591C	8591C-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8591C	8591C-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8591E	8591E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8591E	8591E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8591EM	8591EM-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8591EM	8591EM-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8592L	8592L-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8592L	8592L-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8593E	8593E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8593E	8593E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8593EM	8593EM-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8593EM	8593EM-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8594E	8594E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8594E	8594E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8594EM	8594EM-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8594EM	8594EM-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8594L	8594L-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8594L	8594L-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8594Q	8594Q-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8594Q	8594Q-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8595E	8595E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8595E	8595E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8595EM	8595EM-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8595EM	8595EM-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8596E	8596E-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8596E	8596E-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
8596EM	8596EM-908	–	5062-4841 (1)	–	–	–	–	Rack mount kit without handles
8596EM	8596EM-909	–	–	–	–	5062-4840 (1)	–	Rack mount kit
86060C	86060C-1CN	5063-9220 (1)	–	–	–	–	–	Rack mount kit - 88.1H with handle
86060C	86060C-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
86061C	86061C-1CM	–	–	–	1CM001A	–	–	Rack mount flange kit 177.0 mm H (4U) - one bracket, one half-module bracket
86061C	86061C-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
86061C	86061C-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
86062C	86062C-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
86062C	86062C-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
86062C	86062C-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
86082A	86082A-1CN	1CN005A (1); 1CN007A (1)	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles; Handle kit 132.6 mm H (3U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
86082A	86082A-AX4	–	34192A (1); 1CM015A (1)	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets; Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86082A	86082A-AXE	–	–	–	–	1CP008A (1); 1CP020A (1)	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles; Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
86100A	86100A-AX4	–	1CM030A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86100A	86100A-AXE	–	–	–	–	1CP018A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
86100B	86100B-AX4	–	1CM030A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86100B	86100B-AXE	–	–	–	–	1CP018A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
86100C	86100C-AX4	–	1CM030A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86100C	86100C-AXE	–	–	–	–	1CP018A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
86100D	86100D-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86100D	86100D-AXE	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
86122A	86122A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
86122A	86122A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
86122A	86122A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
86130A	86130A-AX4	–	1CM030A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86130A	86130A-AXE	–	–	–	–	1CP018A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
86140A	86140A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
86140A	86140A-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
86140A	86140A-AXE	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
86140B	86140B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
86140B	86140B-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86140B	86140B-AXE	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
86141B	86141B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
86141B	86141B-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86141B	86141B-AXE	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
86142A	86142A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
86142A	86142A-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86142A	86142A-AXE	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
86142B	86142B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
86142B	86142B-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86142B	86142B-AXE	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
86146B	86146B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
86146B	86146B-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86146B	86146B-AXE	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8642A	8642A-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8642A	8642A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8642A	8642A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8642B	8642B-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8642B	8642B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8642B	8642B-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8643A	8643A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8643A	8643A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8643A	8643A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
8644B	8644B-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8644B	8644B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8644B	8644B-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
8645A	8645A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8645A	8645A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8645A	8645A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
8648A	8648A-1CM	–	08648-60001 (1)	–	–	–	–	Rack mount kit
8648B	8648B-1CM	–	08648-60001 (1)	–	–	–	–	Rack mount kit
8648C	8648C-1CM	–	08648-60001 (1)	–	–	–	–	Rack mount kit
8648D	8648D-1CM	–	08648-60001 (1)	–	–	–	–	Rack mount kit
8662A	8662A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8662A	8662A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8662A	8662A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
8663A	8663A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8663A	8663A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8663A	8663A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8664A	8664A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8664A	8664A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8664A	8664A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
8665A	8665A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8665A	8665A-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8665A	8665A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
8665B	8665B-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8665B	8665B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8665B	8665B-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
8671B	8671B-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8671B	8671B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8671B	8671B-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8672A	8672A-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8672A	8672A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8672A	8672A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8673B	8673B-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8673B	8673B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8673B	8673B-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8673C	8673C-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
8673C	8673C-913	–	–	5062-4073 (1)	–	–	–	Rack mount kit

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8673D	8673D-908	–	1CM028A	–	–	–	–	Rack mount flange kit 88.1 mm H (3U) and 132.6 mm H (2U) - 4 brackets (5U total)
8673D	8673D-913	–	–	5062-4073 (1)	–	–	–	Rack mount kit
8673E	8673E-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8673E	8673E-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8673E	8673E-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8673G	8673G-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8673G	8673G-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8673G	8673G-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
8673H	8673H-907	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
8673H	8673H-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
8673H	8673H-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
86792A	86792A-907	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
86792A	86792A-908	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
86792A	86792A-909	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
8702B	8702B-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8702B	8702B-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
8702D	8702D-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8702D	8702D-1CP	–	–	5062-4073 (1)	–	–	–	Rack mount kit
8702E	8702E-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8702E	8702E-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
87030A	87030A-1CM	–	–	5063-9232 (1)	–	–	–	Kit-rack mount - 88.1H-W/handle

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8703A	8703A-908	–	–	5063-9232 (1); 5063-9235 (1)	–	–	–	Kit-rack mount - 88.1H-W/handle; Kit-rack mount - 177.0H-W/handle
8703B	8703B-908	–	34191A (1); 1CM015A (1)	–	–	–	–	Dual flange kit, 2U; Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8703B	8703B-913	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
87050A	87050A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
87050E	87050E-1CM	–	Contact parts ID	–	–	–	–	Contact parts ID
87075C	87075C-1CM	–	Contact parts ID	–	–	–	–	Contact parts ID
8711C	8711C-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8712C	8712C-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8712ES	8712ES-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8712ET	8712ET-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8713C	8713C-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8714C	8714C-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8714ES	8714ES-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8714ET	8714ET-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
8719D	8719D-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8719D	8719D-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8719ES	8719ES-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8719ES	8719ES-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8719ET	8719ET-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8719ET	8719ET-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8720D	8720D-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8720D	8720D-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8720ES	8720ES-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8720ES	8720ES-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8720ET	8720ET-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8720ET	8720ET-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8722D	8722D-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8722D	8722D-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8722ES	8722ES-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8722ES	8722ES-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8722ET	8722ET-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8722ET	8722ET-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8730A	8730A-1CM	–	08712-60036 (1)	–	–	–	–	Rack mount kit with handles
87511A	87511A-907	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
87511A	87511A-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
87511A	87511A-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
87511B	87511B-907	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
87511B	87511B-908	–	1CM002A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets; 1.75 in hole spacing
87511B	87511B-909	–	–	–	–	1CP001A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
8752C	8752C-1CM	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8752C	8752C-1CP	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
8753D	8753D-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8753D	8753D-1CP	–	–	5062-4073 (1)	–	–	–	Rack mount kit
8753E	8753E-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8753E	8753E-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8753ES	8753ES-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8753ES	8753ES-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8753ET	8753ET-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8753ET	8753ET-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
8757C	8757C-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8757C	8757C-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
8757D	8757D-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8757D	8757D-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
8757E	8757E-908	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
8757E	8757E-913	–	–	1CM035A	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two brackets for units with handles
8770A	8770A-908	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
8770A	8770A-909	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
8780A	8780A-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
8780A	8780A-909	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
89410A	89410A-AX3	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
89410A	89410A-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
89410A	89410A-AX5	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
89431A	89431A-AX3	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
89431A	89431A-AX4	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
89431A	89431A-AX5	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
89441A	89441A-AX3	1CN003A (1); 1CN005A (1)	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles; Handle kit 221.5 mm H (5U) - two front handles
89441A	89441A-AX5	–	–	–	–	1CP005A (1); 1CP020A (1)	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles; Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
B1500A	B1500A-1CM	–	1CM033A	–	–	–	–	Rack mount flange kit 355.6 mm H (8U) - two flange brackets
B2200A	B2200A-1CM	–	1CM033A	–	–	–	–	Rack mount flange kit 355.6mm H (8U) - two flange brackets
B2901A	B2901A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
B2902A	B2902A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
B2911A	B2911A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
B2912A	B2912A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
DSOX90000Q	DSOX90000Q-1CM	–	N2759-60001(1)	–	–	–	–	Rack mount kit
DSA90254A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSA90404A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSA90604A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSA90804A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSA91204A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSA91304A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSAX91604A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
DSAX92004A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSAX92504A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSAX92804A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSAX93204A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSO80204B	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO80304B	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO80404B	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO80604B	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO80804A	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO80804B	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO81004A	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO81004B	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO81204A	DSO80000-1CM	–	E2609B	–	–	–	–	Rack mount
DSO90254A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSO90404A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSO90604A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSO9064A	DSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
DSO90804A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSO9104A	DSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
DSO91204A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSO91304A	DSO90000A-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSO9254A	DSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
DSO9404A	DSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
DSOX91604A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSOX92004A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Sseries
DSOX92504A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSOX92804A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
DSOX93204A	DSOX90000-1CM	–	N5470A	–	–	–	–	Rackmount kit for Infiniium DSO90000 Series
E1300B	E1300B-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E1301B	E1301B-907	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
E1401B	E1401B-AX3	Contact parts ID	–	–	–	–	–	Contact parts ID
E1401B	E1401B-AX5	–	–	–	–	Contact parts ID	–	Contact parts ID
E3614A	E3614A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3615A	E3615A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3616A	E3616A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3617A	E3617A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3620A	E3620A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3631A	E3631A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E3632A	E3632A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E3632A	E3632A-1CP	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E3633A	E3633A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E3634A	E3634A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E3640A	E3640A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3641A	E3641A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3642A	E3642A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3643A	E3643A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3644A	E3644A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E3645A	E3645A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E3646A	E3646A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E3647A	E3647A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E3648A	E3648A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E3649A	E3649A-1CM	–	–	–	34193A	–	–	Rack mount flange kit 132.6 mm H (3U) - one bracket, one half-module bracket
E4350B	E4350B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4350B	E4350B-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4351B	E4351B-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4351B	E4351B-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4356A	E4356A-908	–	1CM003A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4356A	E4356A-909	–	–	–	–	1CP002A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4400A	E4400A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4400A	E4400A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4400A	E4400A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4400B	E4400B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4400B	E4400B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4400B	E4400B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4401B	E4401B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4401BU	E4401BU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4402B	E4402B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4402B	E5505A-RK4	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4402BU	E4402BU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E4403B	E4403B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4403BU	E4403BU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4404B	E4404B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4405B	E4405B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4406A	E4406A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4406A	E4406A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4406A	E4406A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4406A	E4406A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4407B	E4407B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4407BU	E4407BU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4408B	E4408B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4408BU	E4408BU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4411A	E4411A-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4411AU	E4411AU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4411B	E4411B-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4411B	E5505A-RK3	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4411BU	E4411BU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E4416A	E4416A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E4416A	E4416A-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
E4417A	E4417A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E4418B	E4418B-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E4418B	E4418B-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
E4419B	E4419B-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
E4419B	E4419B-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E4420A	E4420A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4420A	E4420A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4420A	E4420A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4420B	E4420B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4420B	E4420B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4420B	E4420B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4421A	E4421A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4421A	E4421A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4421A	E4421A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4421B	E4421B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4421B	E4421B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4421B	E4421B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4422A	E4422A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4422A	E4422A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4422A	E4422A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4422B	E4422B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4422B	E4422B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4422B	E4422B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4423B	E4423B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4423B	E4423B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4423B	E4423B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E4424B	E4424B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4424B	E4424B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4424B	E4424B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4425B	E4425B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4425B	E4425B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4425B	E4425B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4426B	E4426B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4426B	E4426B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4426B	E4426B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4428C	E4428C-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4428C	E4428C-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4428C	E4428C-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4430A	E4430A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4430A	E4430A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4430A	E4430A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4430B	E4430B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4430B	E4430B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4430B	E4430B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4431A	E4431A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4431A	E4431A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4431A	E4431A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E4431B	E4431B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4431B	E4431B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4431B	E4431B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4432A	E4432A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4432A	E4432A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4432A	E4432A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4432B	E4432B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4432B	E4432B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4432B	E4432B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4433A	E4433A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4433A	E4433A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4433A	E4433A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4433B	E4433B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4433B	E4433B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4433B	E4433B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4434B	E4434B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4434B	E4434B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4434B	E4434B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4435B	E4435B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4435B	E4435B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4435B	E4435B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E4436B	E4436B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4436B	E4436B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4436B	E4436B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4437B	E4437B-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4437B	E4437B-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4437B	E4437B-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4438C	E4438C-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E4438C	E4438C-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E4438C	E4438C-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E4440A	E4440A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4440A	E4440A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4440A	E4440A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4440A	E4440A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4440AU	E4440AU-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4440AU	E4440AU-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4440AU	E4440AU-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4440AU	E4440AU-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4443A	E4443A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4443A	E4443A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4443A	E4443A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4443A	E4443A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4443AU	E4443AU-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E4443AU	E4443AU-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4443AU	E4443AU-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4443AU	E4443AU-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4445A	E4445A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4445A	E4445A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4445A	E4445A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4445A	E4445A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4445AU	E4445AU-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4445AU	E4445AU-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4445AU	E4445AU-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4445AU	E4445AU-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4446A	E4446A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4446A	E4446A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4446A	E4446A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4446A	E4446A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4446AU	E4446AU-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4446AU	E4446AU-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4446AU	E4446AU-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4446AU	E4446AU-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4447A	E4447A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4447A	E4447A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4447A	E4447A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4447A	E4447A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E4447AU	E4447AU-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4447AU	E4447AU-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4447AU	E4447AU-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4447AU	E4447AU-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4448A	E4448A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4448A	E4448A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4448A	E4448A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4448A	E4448A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4448AU	E4448AU-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E4448AU	E4448AU-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E4448AU	E4448AU-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E4448AU	E4448AU-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E4980A	E4980A-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
E4981A	E4981A-1CM	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
E4982A	E4982A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E4982A	E4982A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E4982A	E4982A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E4991A	E4991A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E4991A	E4991A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E4991A	E4991A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5052A	E5052A-1CM	–	1CM042A	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets
E5052A	E5052A-1CN	1CN020A	–	–	–	–	–	Handle kit 265.9 mm H (6U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E5052A	E5052A-1CP	–	–	–	–	1CP019A	–	Rack mount flange and handle kit 265.9 mm H (6U) - two brackets and front handles
E5052B	E5052B-1CM	–	1CM042A	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets
E5052B	E5052B-1CN	1CN020A	–	–	–	–	–	Handle kit 265.9 mm H (6U) - two front handles
E5052B	E5052B-1CP	–	–	–	–	1CP019A	–	Rack mount flange and handle kit 265.9 mm H (6U) - two brackets and front handles
E5053A	E5053A-1CM	–	Contact parts ID	–	–	–	–	Contact parts ID
E5053A	E5053A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E5053A	E5053A-1CP	–	–	–	–	Contact parts ID	–	Contact parts ID
E5061A	E5061A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5061A	E5061A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5061A	E5061A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5061B	E5061B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5061B	E5061B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5061B	E5061B-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5062A	E5062A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5062A	E5062A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5062A	E5062A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5070B	E5070B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5070B	E5070B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5070B	E5070B-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5070C	E5070C-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5070C	E5070C-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5070C	E5070C-1CP	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E5071B	E5071B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5071B	E5071B-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5071B	E5071B-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5071C	E5071C-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5071C	E5071C-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5071C	E5071C-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5072A	E5072A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5072A	E5072A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5072A	E5072A-1CP	–	–	–	–	1CP009A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5091A	E5091A-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
E5091A	E5091A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
E5091A	E5091A-1CP	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
E5092A	E5092A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E5092A	E5092A-1CN	1CN007A	–	–	–	–	–	Handle kit 132.6 mm H (3U) - two front handles
E5092A	E5092A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
E5100A	E5100A-1CM	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E5100A	E5100A-1CN	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
E5100A	E5100A-1CP	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E5100B	E5100B-1CM	–	1CM023A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E5100B	E5100B-1CN	1CN012A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles, System II plus
E5100B	E5100B-1CP	–	–	–	–	1CP013A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E5250A	E5250A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5262A	E5262A-1CM	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E5270B	E5270B-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5505A	E5505A-RK1	–	–	–	1CM068A	–	–	Rack mount flange kit 177.0 mm H (4U) - one bracket, one half-module bracket
E5515B	E5515B-AX3	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5515B	E5515B-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5515B	E5515B-AX5	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E5515C	E5515C-AX3	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E5515C	E5515C-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E5515C	E5515C-AX5	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E6601A	E6601A-AX3	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E6601A	E6601A-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E6601A	E6601A-AX5	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E6607A	E6607A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E6607A	E6607A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E6607A	E6607A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E6607A	E6607A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E6607C	E6607C-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E6607C	E6607C-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E6607C	E6607C-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E6607C	E6607C-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E6607AK	E6607AK-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E6607AK	E6607AK-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E6607AK	E6607AK-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E6607AK	E6607AK-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E6607B	E6607B-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E6607B	E6607B-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E6607B	E6607B-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E6607B	E6607B-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
E6620A	E6620A-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E6620A	E6620A-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E6620A	E6620A-1CP	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E6900A	E6900A-AX3	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
E6900A	E6900A-AX4	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
E6900A	E6900A-AX5	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
E7401A	E7401A-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7401AU	E7401AU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7402A	E7402A-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7402AU	E7402AU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7403A	E7403A-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7403AU	E7403AU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7404A	E7404A-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7404AU	E7404AU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7405A	E7405A-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E7405AU	E7405AU-1CP	–	–	–	–	E4401-60385 (1)	–	Kit, rack mount with handles
E8241A	E8241A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E8241A	E8241A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8241A	E8241A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E8244A	E8244A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E8244A	E8244A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0mm H (4U) - two front handles
E8244A	E8244A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E8247C	E8247C-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E8247C	E8247C-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8247C	E8247C-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E8251A	E8251A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E8251A	E8251A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8251A	E8251A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E8254A	E8254A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E8254A	E8254A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8254A	E8254A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E8257C	E8257C-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E8257C	E8257C-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8257C	E8257C-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E8257D	E8257D-1CM	–	1CM014A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets, four hole plugs
E8257D	E8257D-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8257D	E8257D-1CP	–	–	–	–	1CP006A	–	Rack mount flange and handle kit 177.0 mm H (4U) - brackets, handles, hole plugs
E8257N	E8257N-1CM	–	1CM014A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets, four hole plugs

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E8257N	E8257N-1CP	–	–	–	–	1CP006A	–	Rack mount flange and handle kit 177.0 mm H (4U) - brackets, handles, hole plugs
E8267C	E8267C-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
E8267C	E8267C-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8267C	E8267C-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
E8267D	E8267D-1CM	–	1CM014A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets, four hole plugs
E8267D	E8267D-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8267D	E8267D-1CP	–	–	–	–	1CP006A	–	Rack mount flange and handle kit 177.0 mm H (4U) - brackets, handles, hole plugs
E8356A	E8356A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8356A	E8356A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8356B	E8356B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5mm H (5U) - two flange brackets; Rail: Standard
E8356B	E8356B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8357A	E8357A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8357A	E8357A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8357B	E8357B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8358A	E8358A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8358A	E8358A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8358B	E8358B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8358B	E8358B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8361A	E8361A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E8361A	E8361A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8361C	E8361C-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
E8361C	E8361C-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8362A	E8362A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
E8362A	E8362A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8362C	E8362C-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
E8362C	E8362C-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8363A	E8363A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
E8363A	E8363A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8363C	E8363C-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
E8363C	E8363C-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8364A	E8364A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
E8364A	E8364A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8364C	E8364C-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
E8364C	E8364C-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
E8663B	E8663B-1CM	–	1CM014A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets, four hole plugs
E8663B	E8663B-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8663B	E8663B-1CP	–	–	–	–	1CP006A	–	Rack mount flange and handle kit 177.0 mm H (4U) - brackets, handles, hole plugs
E8663D	E8663D-1CM	–	1CM014A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets, four hole plugs

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
E8663D	E8663D-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
E8663D	E8663D-1CP	–	–	–	–	1CP006A	–	Rack mount flange and handle kit 177.0 mm H (4U) - brackets, handles, hole plugs
E8781A	E8781A-A83	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
E8781A	E8781A-A85	–	34191A	–	–	–	–	Dual flange kit, 2U
E8801A	E8801A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8801A	E8801A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8801B	E8801B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8801B	E8801B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8802A	E8802A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8802A	E8802A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8802B	E8802B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8802B	E8802B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8803A	E8803A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8803A	E8803A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
E8803B	E8803B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
E8803B	E8803B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
J7519A	J7519A-1CM	–	Contact parts ID	–	–	–	–	Contact parts ID
J7519A	J7519A-1CR	–	–	–	–	–	E4270-60012 (1)	Rack mount 19 inch for Intel server
J7520A	J7520A-1CM	–	Contact parts ID	–	–	–	–	Contact parts ID
J7520A	J7520A-1CR	–	–	–	–	–	E4270-60012 (1)	Rack mount 19 inch for Intel server
L4490A	L4490A-AXA	–	34191A	–	–	–	–	Dual flange kit, 2U

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
L4490A	L4490A-AXB	–	–	–	–	1CP011A	–	Rack mount flange and handle kit 88.1 mm H (2U) - two brackets and front handles
L4490A	L4490A-AXC	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
L4491A	L4491A-AXA	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
L4491A	L4491A-AXB	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
L4491A	L4491A-AXC	–	–	–	–	–	1494-0059 (1)	Rack slide kit non-tilting - for 345.5 mm and 421.6 mm depth cabinets
L4532A	L4532A-908	–	L4532-67001 (1)	–	–	–	–	Kit, rack mount
L4534A	L4534A-908	–	L4532-67001 (1)	–	–	–	–	Kit, rack mount
MSO9064A	MSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
MSO9104A	MSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
MSO9254A	MSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
MSO9404A	MSO9000A-1CM	–	N2902A	–	–	–	–	Rackmount kit - 9000 Series Oscilloscope
N1911A	N1911A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
N1911A	N1911A-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
N1912A	N1912A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
N1912A	N1912A-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
N1913A	N1913A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
N1913A	N1913A-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
N1914A	N1914A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
N1914A	N1914A-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
N1996A	N1996A-1CM	–	1CM013A (1); N1996-60021 (1)	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets; Kit, rear feet, system II
N1996AK	N1996AK-1CM	–	Contact parts ID	–	–	–	–	Contact parts ID

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N1996AK	N1996AK-1CP	–	–	–	–	Contact parts ID	–	Contact parts ID
N3280A	N3280A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
N3280A	N3280A-AXS	–	Contact parts ID	–	–	–	–	Contact parts ID
N3300A	N3300A-908	–	1CM020A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - 4 brackets (4U total); 1.75 in hole spacing
N3300A	N3300A-909	–	–	–	–	Contact parts ID	–	Contact parts ID
N3301A	N3301A-800	–	1CM034A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N3301A	N3301A-908	–	–	–	1CM001A	–	–	Rack mount flange kit 177.0 mm H (4U) - one bracket, one half-module bracket
N3381A	N3381A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
N3381A	N3381A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
N3381B	N3381B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5mm H (5U) - two flange brackets; Rail: Standard"
N3381B	N3381B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
N3382A	N3382A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
N3382A	N3382A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
N3382B	N3382B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
N3382B	N3382B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
N3383A	N3383A-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
N3383A	N3383A-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard
N3383B	N3383B-1CM	–	1CM015A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets; Rail: Standard
N3383B	N3383B-1CP	–	–	1CM043A (1); E3663AC (1)	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles; Rail: Standard

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N4010A	N4994B-002	–	–	–	1CM019A	–	–	Rack mount flange kit 88.1 mm H (2U) - one bracket, one quarter-module bracket
N432A	N432A-908	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
N432A	N432A-909	–	1CM007A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - brackets, lock link for side-by-side mount
N4413A	N4413A-1CP	–	–	–	–	N4419-60001 (1)	–	Rack mount kit
N4414A	N4414A-1CP	–	–	–	–	N4419-60001 (1)	–	Rack mount kit
N4415A	N4415A-1CP	–	–	–	–	N4419-60001 (1)	–	Rack mount kit
N4416A	N4416A-1CP	–	–	–	–	N4419-60001 (1)	–	Rack mount kit
N4417A	N4417A-1CP	–	–	–	–	N4419-60001 (1)	–	Rack mount kit
N4418A	N4418A-1CP	–	–	–	–	N4419-60001 (1)	–	Rack mount kit
N4419A	N4419A-1CP	–	–	–	–	N4419-60001 (1)	–	Rack mount kit
N4421A	N4421A-1CP	–	–	–	–	1CP008A	–	Rack mount flange and handle kit 132.6 mm H (3U) - two brackets and front handles
N4906A	N4906A-AX4	–	1CM030A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
N4906A	N4906A-AXE	–	–	–	–	1CP018A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
N5105A	N5105A-1CP	–	–	–	–	1CP026A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
N5105A	N5105A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N5106A	N5106A-1CP	–	–	–	–	1CP026A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
N5106A	N5106A-1CR	–	–	–	–	–	E4406-60115 (1); W1312-40032 (4)	Kit, rack slide; plug, hole, bottom foot
N5151M	N5151M-1CM	–	1CM010A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, four hole plugs
N5151M	N5151M-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
N5151M	N5151M-1CP	–	–	–	–	1CP011A (1); W1312-40032 (4)	–	Rack mount kit - 88.1H with handle; plug, hole, bottom foot
N5151M	N5151M-1CR	–	–	–	–	–	E4406-60115 (1); W1312-40032 (4)	Kit, rack slide; plug, hole, bottom foot
N5161A	N5161A-1CM	–	1CM010A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, four hole plugs

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N5161A	N5161A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
N5161A	N5161A-1CP	–	–	–	–	1CP004A	–	Rack mount flange and handle kit 88.1 mm H (2U) - brackets, handles, hole plugs
N5161A	N5161A-1CR	–	–	–	–	–	E4406-60115 (1); W1312-40032 (4)	Kit, rack slide; plug, hole, bottom foot
N5162A	N5162A-1CM	–	1CM010A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, four hole plugs
N5162A	N5162A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
N5162A	N5162A-1CP	–	–	–	–	1CP004A	–	Rack mount flange and handle kit 88.1 mm H (2U) - brackets, handles, hole plugs
N5162A	N5162A-1CR	–	–	–	–	–	E4406-60115 (1); W1312-40032 (4)	Kit, rack slide; plug, hole, bottom foot
N5171B	–	1CN006A	1CM010A	–	–	1CP004A	1CR012A	Common accessories structured directly to Instrument, see corresponding category header
N5172B	–	1CN006A	1CM010A	–	–	1CP004A	–	Common accessories structured directly to Instrument, see corresponding category header
N5181A	N5181A-1CM	–	1CM010A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, four hole plugs
N5181A	N5181A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
N5181A	N5181A-1CP	–	–	–	–	1CP004A	–	Rack mount flange and handle kit 88.1 mm H (2U) - brackets, handles, hole plugs
N5181A	N5181A-1CR	–	–	–	–	–	E4406-60115 (1); W1312-40032 (4)	Kit, rack slide; plug, hole, bottom foot
N5181B	–	1CN006A	1CM010A	–	–	1CP004A	1CR012A	Common accessories structured directly to Instrument, see corresponding category header
N5182A	N5182A-1CM	–	1CM010A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, four hole plugs
N5182A	N5182A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
N5182A	N5182A-1CP	–	–	–	–	1CP004A	–	Rack mount flange and handle kit 88.1 mm H (2U) - brackets, handles, hole plugs
N5182A	N5182A-1CR	–	–	–	–	–	E4406-60115 (1); W1312-40032 (4)	Kit, rack slide; plug, hole, bottom foot
N5182B	–	1CN006A	1CM010A	–	–	1CP004A	–	Common accessories structured directly to Instrument, see corresponding category header
N5183A	N5183A-1CM	–	1CM010A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, four hole plugs

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N5183A	N5183A-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
N5183A	N5183A-1CP	–	–	–	–	1CP004A	–	Rack mount flange and handle kit 88.1 mm H (2U) - brackets, handles, hole plugs
N5183A	N5183A-1CR	–	–	–	–	–	E4406-60115 (1); W1312-40032 (4)	Kit, rack slide; plug, hole, bottom foot
N5183MU	N5183MU-857	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
N5221A	N5221A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5221A	N5221A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5222A	N5222A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5222A	N5222A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5224A	N5224A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5224A	N5224A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5225A	N5225A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5225A	N5225A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5227A	N5227A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5227A	N5227A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5230A	N5230A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5230A	N5230A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
N5230C	N5230C-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N5230C	N5230C-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
N5231A	N5231A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5231A	N5231A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
N5232A	N5232A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5232A	N5232A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
N5241A	N5241A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5241A	N5241A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
N5242A	N5242A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5242A	N5242A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
N5244A	N5244A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5244A	N5244A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5245A	N5245A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5245A	N5245A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5247A	N5247A-1CM	–	1CM042A (1); E3663AC (1)	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5247A	N5247A-1CP	–	–	–	–	5063-9237 (1); 1CN020A (1); E3663AC (1)	–	Kit-rack mount; handle kit 265.9 mm H (6U) - two front handles; Rail: Standard
N5262A	N5262A-1CM	–	–	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N5262A	N5262A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N5262A	N5262A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N5264A	N5264A-1CM	–	–	–	–	–	–	Rack mount flange kit 265.9 mm H (6U) - two flange brackets; Rail: Standard
N5264A	N5264A-1CP	–	–	5063-9237 (1); E3663AC (1)	–	–	–	Kit-rack mount; Rail: Standard
N6700A	N6700A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6700B	N6700B-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6701A	N6701A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6702A	N6702A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6705A	N6705A-908	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N6705A	N6705A-909	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N6705B	N6705B-908	–	–	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N6705B	N6705B-909	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N6710A	N6710A-908	–	–	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6710B	N6710B-908	–	–	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6711A	N6711A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6712A	N6712A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6715A	N6715A-908	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N6715A	N6715A-909	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N6721A	N6721A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6722A	N6722A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6723A	N6723A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6724A	N6724A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6725A	N6725A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6726A	N6726A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6727A	N6727A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N6728A	N6728A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N6729A	N6729A-908	–	N6709A	–	–	–	–	Rack mount flange kit 44.5 mm H (1U)
N8300A	N8300A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N8300A	N8300A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N8300A	N8300A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N8300A	N8300A-1CR	–	–	–	–	–	1494-0060 (1)	Kit-Slide, Standard
N8972A	N8972A-1CP	–	–	–	–	N8972-61014 (1)	–	Rack mount and handle slide kit 221.5 mm H (5U) - panel adapter support bracket
N8973A	N8973A-1CP	–	–	–	–	N8972-61014 (1)	–	Rack mount and handle slide kit 221.5 mm H (5U) - panel adapter support bracket
N8974A	N8974A-1CP	–	–	–	–	N8972-61014 (1)	–	Rack mount and handle slide kit 221.5 mm H (5U) - panel adapter support bracket
N8975A	N8975A-1CP	–	–	–	–	N8972-61014 (1)	–	Rack mount and handle slide kit 221.5 mm H (5U) - panel adapter support bracket
N9000A	N9000A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9000A	N9000A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9000A	N9000A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9000A	N9000A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N9000AK	N9000AK-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9000AK	N9000AK-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9000AK	N9000AK-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9000AK	N9000AK-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N9010A	N9010A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9010A	N9010A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9010A	N9010A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9010A	N9010A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting

Technical specifications (continued)

Instrument info		Common accessory product categories					Description	
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N9010AK	N9010AK-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9010AK	N9010AK-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9010AK	N9010AK-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9010AK	N9010AK-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N9020A	N9020A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9020A	N9020A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9020A	N9020A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9020A	N9020A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N9020AK	N9020AK-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9020AK	N9020AK-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9020AK	N9020AK-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9020AK	N9020AK-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N9030A	N9030A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9030A	N9030A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9030A	N9030A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9030A	N9030A-1CR	–	–	–	–	–	N9030-60007 (1)	Rack slide
N9030AK	N9030AK-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9030AK	N9030AK-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9030AK	N9030AK-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9030AK	N9030AK-1CR	–	–	–	–	–	N9030-60007 (1)	Rack Slide
N9038A	N9038A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9038A	N9038A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9038A	N9038A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
N9038AK	N9038AK-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9038AK	N9038AK-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9038AK	N9038AK-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9039A	N9039A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9039A	N9039A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9039A	N9039A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9039A	N9039A-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N9039AK	N9039AK-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9039AK	N9039AK-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9039AK01	N9039AK01-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
N9039AK01	N9039AK01-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
N9039AK01	N9039AK01-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
N9039AK01	N9039AK01-1CR	–	–	–	–	–	E4406-60115 (1)	Rack slide kit non-tilting
N9310A	N9310A-1CM	–	–	–	–	Contact parts ID	–	Contact parts ID
N9310AK	N9310AK-1CM	–	–	–	–	Contact parts ID	–	Contact parts ID
N9320A	N9320A-1CM	–	–	–	–	Contact parts ID	–	Contact parts ID
N9320AK	N9320AK-1CM	–	–	–	–	Contact parts ID	–	Contact parts ID
N9320B	N9320B-1CM	–	–	–	–	N9310-80001 (1)	–	Rackmount flange kit
N9320BK	N9320BK-1CM	–	–	–	–	N9310-80001 (1)	–	Rackmount flange kit
U2972A	U2972A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
U3020AM23	U3042A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3020AM23	U3042A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3020AM23	U3042A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
U3022AE06	U3022AE06-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3022AE06	U3022AE06-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3022AE06	U3022AE06-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3022AE10	U3022AE10-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3022AE10	U3022AE10-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3022AE10	U3022AE10-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3022AH10	U3022AH10-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3022AH10	U3022AH10-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3022AH10	U3022AH10-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3022AM06	U3022A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3022AM06	U3022A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3022AM06	U3022A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3022AM14	U3022A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3022AM14	U3022A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3022AM14	U3022A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3022AS66	U3022AS66-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
U3022AS66	U3022AS66-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
U3022AS66	U3022AS66-1CP	–	–	5063-9232 (1)	–	–	–	Kit-rack mount - 88.1H-W/Handle
U3022UM06	U3042A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3022UM06	U3042A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3022UM06	U3042A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3024AE06	U3024AE06-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
U3024AE06	U3024AE06-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3024AE06	U3024AE06-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3025AE06	U3025AE06-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3025AE06	U3025AE06-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3025AE06	U3025AE06-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3025AE10	U3025AE10-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3025AE10	U3025AE10-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3025AE10	U3025AE10-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3025AS06	U3025AS06-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3025AS06	U3025AS06-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3025AS06	U3025AS06-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3026AE10	U3026AE10-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3026AE10	U3026AE10-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3026AE10	U3026AE10-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3035P	U3035P-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
U3035P	U3035P-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1 mm H (2U) - two front handles
U3035P	U3035P-1CP	–	–	5063-9232 (1)	–	–	–	Kit-rack mount - 88.1H-W/Handle
U3035P	U3035P-2CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3035P	U3035P-2CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3035P	U3035P-2CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AE04	U3042A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AE04	U3042A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
U3042AE04	U3042A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AE08	U3042AE08-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AE08	U3042AE08-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3042AE08	U3042AE08-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AE12	U3042AE12-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AE12	U3042AE12-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3042AE12	U3042AE12-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AE16	U3042AE16-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
U3042AE16	U3042AE16-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
U3042AE16	U3042AE16-1CP	–	–	1CM043A	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two brackets for units with handles
U3042AM04	U3042A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AM04	U3042A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3042AM04	U3042A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AM08	U3042A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AM08	U3042A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3042AM08	U3042A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AM12	U3042A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AM12	U3042A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3042AM12	U3042A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AM12	U3042AM12-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AM12	U3042AM12-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
U3042AM12	U3042AM12-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3042AM20	U3042A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3042AM20	U3042A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3042AM20	U3042A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3044AM12	U3044A-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3044AM12	U3044A-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3044AM12	U3044A-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3045AM04	U3045AM04-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
U3045AM04	U3045AM04-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
U3045AM04	U3045AM04-1CP	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
U3045AM12	U3045AM12-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
U3045AM12	U3045AM12-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
U3045AM12	U3045AM12-1CP	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
U3047AE04	U3047AE04-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
U3047AE04	U3047AE04-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
U3047AE04	U3047AE04-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles
U3047AM04	U3047AM04-1CM	–	1CM015A	–	–	–	–	Rack mount flange kit 221.5 mm H (5U) - two flange brackets
U3047AM04	U3047AM04-1CN	1CN005A	–	–	–	–	–	Handle kit 221.5 mm H (5U) - two front handles
U3047AM04	U3047AM04-1CP	–	–	–	–	1CP020A	–	Rack mount flange and handle kit 221.5 mm H (5U) - two brackets and front handles
U3050AH11	U3050AH11-1CM	–	34191A	–	–	–	–	Dual flange kit, 2U
U3050AH11	U3050AH11-1CN	1CN006A	–	–	–	–	–	Handle kit 88.1mm H (2U) - two front handles

Technical specifications (continued)

Instrument info		Common accessory product categories						Description
Instrument	Instrument option	Handles	Rack mount	Rack mount for units with handles	Rack mount including filler panel	Rack mount including handles	Rack slide	Accessory product description
U3050AH11	U3050AH11-1CP	–	–	–	–	1CP014A	–	Double rack mount flange and handle kit 88.1 mm (2U) and 132.6 mm H (3U)
U3401A	U3400A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
U3402A	U3400A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
U3606A	U3606A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
U3606A	U3606A-1CN	–	1CM011A	–	–	–	–	Rack mount flange kit 88.1 mm H (2U) - two flange brackets, lock link kit
U8001A	U8001A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
U8002A	U8002A-1CM	–	–	–	34190A	–	–	Rackmount kit for 34401A, 33120/250A, 53131A, 34970A, etc.
U8031A	U8031A-1CM	–	–	–	1CM068A	–	–	Rack mount flange kit 177.0 mm H (4U) - one bracket, one half-module bracket
U8032A	U8032A-1CM	–	–	–	1CM068A	–	–	Rack mount flange kit 177.0 mm H (4U) - one bracket, one half-module bracket
U8903A	U8903A-908	–	34192A	–	–	–	–	Rack mount flange kit 132.6 mm H (3U) - two flange brackets
U9101A	U9101A-908	–	Contact Parts ID	–	–	–	–	Contact parts ID
V2820A	V2820A-1CM	–	–	–	Contact parts ID	–	–	Contact parts ID
V2920A	V2920A-1CM	–	–	–	Contact parts ID	–	–	Contact parts ID
V2999A	V2999A-1CM	–	–	–	Contact parts ID	–	–	Contact parts ID
Z5623AK44	Z5623AK44-1CM	–	1CM013A	–	–	–	–	Rack mount flange kit 177.0 mm H (4U) - two flange brackets
Z5623AK44	Z5623AK44-1CN	1CN003A	–	–	–	–	–	Handle kit 177.0 mm H (4U) - two front handles
Z5623AK44	Z5623AK44-1CP	–	–	–	–	1CP005A	–	Rack mount flange and handle kit 177.0 mm H (4U) - two brackets and front handles



www.agilent.com/find/myagilent

A personalized view into the information most relevant to you.

Agilent Channel Partners

www.agilent.com/find/channelpartners

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.



Three-Year Warranty

www.agilent.com/find/ThreeYearWarranty

Agilent's combination of product reliability and three-year warranty coverage is another way we help you achieve your business goals: increased confidence in uptime, reduced cost of ownership and greater convenience.



Agilent Advantage Services

www.agilent.com/find/AdvantageServices

Accurate measurements throughout the life of your instruments.



www.agilent.com/quality

www.agilent.com

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at: www.agilent.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	(11) 4197 3600
Mexico	01800 5064 800
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 375 8100

Europe & Middle East

Belgium	32 (0) 2 404 93 40
Denmark	45 45 80 12 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125 €/minute
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
United Kingdom	44 (0) 118 927 6201

For other unlisted countries:

www.agilent.com/find/contactus
(BP-3-1-13)

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2013
Published in USA, June 14, 2013
5990-8190EN



Agilent Technologies