

PRICE LIST 2021/22



KNIPEX Quality – Made in Germany

NEW PRODUCTS

Pliers Sets

S. 6–7



KNIPEX StepCut®

S. 16–17



KNIPEX WireStripper

S. 18



KNIPEX Tweezers

S. 8–9



Electrical Installations Set

S. 4–5



Tool Cases "BIG Basic Move" ElectricPlus and Mechanic

p. 10–13



Tool Case "Robust45 Move" Mechanic

p. 14–15



CONTENT

New Products	4 – 21
Combination Pliers	22 – 24
Wire Strippers and Dismantling Tools	25 – 31
Gripping Pliers / Grip Pliers	32 – 42
Circlip Pliers	43 – 46
Carpenters' Pincers	47
Cutting Pliers	48 – 62
Pipe Wrenches and Water Pump Pliers	63 – 69
Special Pliers and Tool Light	70 – 72
Precision Tweezers	73 – 78
Cable and Wire Rope Shears	79 – 84
Crimping Pliers	85 – 96
Crimp Assortments	97 – 99
Cable Connectors	100 – 102
Concreters' Nippers	103
Insulated Tools	104 – 116
Tools with Tethering	117 – 122
Control Cabinet Keys	123
Tool Kits	124 – 136
Tool Bags and Tool Cases	137 – 142
Sales Aids	143 – 151
Index Article Number	152 – 159
Index	160 – 161
General Terms of Delivery	162 – 163
Pliers ABC	164
> Knowledge of Pliers	
> Cutting Values and Wire Classes	
> Structure of Article Number	
> Symbols	

Imprint / Copyright

WE ARE BUBBLING WITH IDEAS

Information on page 19


The perfect electrical team

All-rounders for all common cable work


Electrical Installations Set

This set equips the electrical trade for practically every day-to-day work. The KNIPEX ErgoStrip® universal stripping tool, the extremely versatile pliers for electrical installation with cable shears and the powerful diagonal cutter make the perfect team!


KNIPEX ErgoStrip®



Diagonal Cutter



Pliers for Electrical Installation



Electrical Installation Set consisting of:

KNIPEX ErgoStrip®

- > For fast and precise stripping of all common round and damp-proof installation cables (e.g. NYM cable 3 x 1.5 mm² up to 5 x 2,5 mm²), data cables (e.g. twisted pair) and coax cables
- > Innovative, ergonomic pistol grip design for easy cutting, stripping and longitudinal cut of the sheath
- > Stripping device for cross-sections 0.2 / 0.3 / 0.8 / 1.5 / 2.5 / 4 mm²
- > With opening spring and locking device
- > Housing made from stable glass fibre reinforced plastic


16 95 01 SB 



Pliers for Electrical Installation

- > 6 functions in one pair of pliers
- > Multifunctional pliers for gripping flat and round material, for bending, deburring, cutting cable, stripping and crimping wire ferrules
- > Stripping holes for conductors of 0.75 - 1.5 mm² and 2.5 mm²
- > Crimping die for wire ferrules 0.5 - 2.5 mm²
- > Cable shears with induction-hardened precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm² / dia. 15 mm
- > VDE-tested safety up to 1000 V

13 86 200 



Diagonal Cutter

- > The indispensable diagonal cutter for all-round use
- > High-quality material and precise workmanship for long service life
- > With precision cutting edges for soft and hard wire
- > Narrow head style for use in confined areas
- > Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- > VDE-tested safety up to 1000 V

70 06 160



Artikel-Nr.	EAN				Number	 g
00 31 30 BK V01 	4003773-086574			Electrical Installations Set, 3 parts		635
			16 95 01 SB	KNIPEX ErgoStrip® Universal Stripping Tool	1	
		 1000V 	13 86 200	Pliers for Electrical Installation	1	
		 1000V 	70 06 160	Diagonal Cutter	1	

Always at hand

Pliers sets in a practical carry bag

Now available in
different sizes!

Pliers Wrench Set

3 or 5 parts in different sizes

Pliers wrenches from KNIPEX are ideally suited for the gentle gripping, holding, pressing and bending of workpieces, each one replacing an entire set of wrenches. The practical, hard-wearing polyester fabric tool roll protects your tools and the hook-and-loop fastener keeps them within easy reach!



KNIPEX Cobra® Set

3 or 5 parts in different sizes

The KNIPEX Cobra® are the legendary high-tech water pump pliers from KNIPEX. With their extremely strong self-locking effect, they allow energy-saving work without slipping on the workpiece! Now available as a set in different sizes in our durable tool rolls with matching motif embroidery.

Pliers Wrenches: Set of 3

These sets each contain three pliers wrenches of different sizes with slim, plastic-coated handles. Like all pliers wrenches from KNIPEX, their smooth, parallel jaws allow firm yet gentle gripping – even when working with chrome!

Size M

Equipped with pliers wrenches in lengths of 125, 180 and 250 mm. Maximum width across flats: 52 mm.

00 19 55 56

Size L

Equipped with pliers wrenches in lengths of 150, 250 and 300 mm. Maximum width across flats: 68 mm.

00 19 55 57



KNIPEX Cobra®: Set of 3

These sets each contain three high-tech water pump pliers of different sizes with slim, plastic-coated handles. They are proven for their extremely firm self-locking effect and the ingenious fine adjustment with a push-button.

Size M

Equipped with the KNIPEX Cobra® in lengths of 125, 180 and 250 mm. Maximum gripping capacity: 50 mm.

00 19 55 58

Size L

Equipped with the KNIPEX Cobra® in lengths of 150, 250 and 300 mm. Maximum gripping capacity: 70 mm.

00 19 55 59



KNIPEX Cobra®: with fine adjustment directly on the workpiece



Gripping surfaces with special hardened teeth: high wear resistance and stable gripping



Practical adjustment scale: a laser-cut scale allows the wrench opening to be set before gripping



Work without damaging sensitive surfaces

Article No.	EAN	Contents
00 19 55 56	 082613	Tool Roll size M, equipped with 3 pliers wrenches: 125, 180, 250 mm length
00 19 55 57	 086512	Tool Roll size L, equipped with 3 pliers wrenches: 150, 250, 300 mm length
00 19 55 54	077817	Tool Roll size XL, equipped with 5 pliers wrenches: 125, 150, 180, 250, 300 mm length
00 19 55 58	 086529	Tool Roll size M, equipped with 3 KNIPEX Cobra®: 125, 180, 250 mm length
00 19 55 59	 086536	Tool Roll size L, equipped with 3 KNIPEX Cobra®: 150, 250, 300 mm length
00 19 55 55	082613	Tool Roll size XL, equipped with 5 KNIPEX Cobra®: 125, 150, 180, 250, 300 mm length
00 19 55 56 LE	 082620	Tool roll, empty, 4 compartments, cut for pliers wrenches, with motif embroidery
00 19 55 58 LE	 086499	Tool roll, empty, 4 compartments, cut for KNIPEX Cobra®, with motif embroidery
00 19 55 54 LE	077824	Tool roll, empty, 6 compartments, cut for pliers wrenches, with motif embroidery
00 19 55 55 LE	082620	Tool roll, empty, 6 compartments, cut for KNIPEX Cobra®, with motif embroidery

KNIPEX Tweezers

Specialists for the finest gripping, holding and cutting

The new, expanded range of KNIPEX tweezers: Precision-manufactured, symmetrical tips and an extensive selection of different designs make KNIPEX tweezers an outstanding high-precision tool of the highest quality.

- > Material: Stainless steel, titanium, plastic or steel
- > Tip design: Needle point, point, blunt
- > Other applications: Stripping, positioning and cutting



Our complete range of tweezers can be found in this price list on pages 73-78

Precision Tweezers



Resilient and precise: Precision tweezers made of premium stainless steel offer great rigidity and resistance to most chemicals, salts and acids. Thanks to their high-quality material, they are suitable for use in the chemical, pharmaceutical and electrical industries, and thanks to the precisely crafted tweezer tips they are even suitable for the finest microscopic work.

Mini Precision Tweezers



Working in confined spaces: Their short length makes these mini precision tweezers perfect for working in confined spaces. They are especially useful for precision work close to the object.

Tweezers with exchangeable tips ESD



Flexible and variable: Precision tweezers with exchangeable tips are particularly robust due to carbon-reinforced plastic. They also have a backlash-free 3-point connection and reduce costs thanks to the variety of exchangeable tips.

Cutting Tweezers



Particularly sharp and hard: Ideal for copper, gold, silver and magnetic wire and also available in ESD versions.

Universal Tweezers



The high-quality all-rounders: Universal tweezers offer a wide range of different types of handles and tip shapes. They are anti-magnetic, highly corrosion-resistant and are ideal for all demanding standard applications.

Universal Tweezers ESD



Electrically dissipative coating: Universal tweezers in the ESD version equalize differences in electrical potential between their user and the workpieces in a controlled manner. They meet the requirements of the electronics and precision engineering industry and protect sensitive components.

SMD Precision Tweezers



The finest geometry for filigree components: SMD Precision Tweezers allow reliable work even in confined spaces thanks to the variety of jaw designs. Optimised for electronic work on SMD semiconductors.

Positioning Tweezers



Holding, inserting, pulling: With dimensionally adapted shapes, the gripping surfaces are perfect for positioning or pulling round or cubic components precisely. Even the smallest elongated components can be inserted and moved with ease.

Titanium Tweezers



Super light and corrosion-resistant: Tweezers made of titanium are extremely resistant, even to aggressive acids. They are antimagnetic, antibacterial, highly conductive, solder-repellent, glare-free and extremely heat-resistant (melting point 1677 °C).

Cross Jaw Tweezers



Hold automatically: Their spring force makes these holding tweezers perfect for soldering small and very small components, among other uses. Available, for example, with fine, smooth, shovel-like and toothed gripping surfaces.

Plastic Tweezers ESD



Extremely light and electrically dissipative in a controlled manner: These specialists achieve extraordinary strength with maximum weight savings thanks to carbon-reinforced all-plastic material. They also show high temperature resistance and excellent chemical resistance.

Universal Tweezers, insulated



Tested protection against electrical voltage: Thanks to the 1000 V-tested handle insulation, these tweezers conduct no current when the tips grip live components. For electrical and electronics professionals.

Stripping Tweezers for coated wire



Very thin layers of lacquer on fine wires protect against moisture, leakage currents and short circuits in the electronics sector. Stripping tweezers for coated remove these insulating lacquers as gently as possible.



Tweezer Sets

Optimal combination: The tweezer sets offer a selection of combinations in a high-quality roll-up pouch for safe transport and damage-free storage.

You can find sets on pages 77 and 134-135



Exchangeable ESD tips



Tool Case "BIG Basic Move" ElectricPlus

Premium equipment for electrical professionals

- ▶ Equipped with 27 KNIPEX tools, a total of 68 brand tools, partly VDE-tested according to DIN EN 60900
 - ▶ Telescopic handle set in the base as well as two external, smooth-running skater wheels
 - ▶ Two metal flip locks and a three-digit combination lock for secure locking of the cover
 - ▶ Label field with two stickers for individual labelling
 - ▶ Max. payload: 20 kg
 - ▶ Volume: 33 litres
- > Strong, ergonomic handle
 - > Heavy duty ABS material, black
 - > Circumferential aluminium frame
 - > Metal hinges
 - > Document compartment in the cover
 - > Two removable tool boards made of dirt-repellent PP twin-wall sheets with 31 tool pockets
 - > Base tray, can be fixed by a push button, 70 mm high, can be subdivided by inserts, cover board with 14 large tool pockets
 - > With a total of 54 inserting options



Tool boards made from dirt-repellent PP twin-wall sheets



Base tray with separable inserts



Extendable telescopic handle



Smooth-running skater wheels

Content overview

00 11 01 KNIPEX		74 06 200 KNIPEX		Stabila	
12 52 195 KNIPEX		78 06 125 KNIPEX		Picard	
16 95 01 SB KNIPEX		87 01 180 KNIPEX		Rennsteig	
08 26 145 KNIPEX		97 53 18 KNIPEX		9 parts Wera	
13 86 200 KNIPEX		15 x 98 2X XX KNIPEX		28 parts Wera	
26 26 200 KNIPEX		KNIPEX			
70 06 160 KNIPEX		Stabila			



Article No.	EAN 4003773- 086260				Quantity	Nominal size	g
00 21 06 N			Tool Case "BIG Basic Move" ElectroPlus, 68 parts				10600
			00 11 01	KNIPEX TwinKey®, Control Cabinet Key	1		
			12 52 195	KNIPEX PreciStrip16	1	195 mm	
	MM		16 95 01 SB	KNIPEX ErgoStrip®, Universal Stripping Tool	1	135 mm	
	△ 1000 V		08 26 145	Needle-Nose Combination Pliers	1	145 mm	
	△ 1000 V		13 86 200	Pliers for Electrical Installation	1	200 mm	
	△ 1000 V ∠40°		26 26 200	Snipe nose pliers, bent	1	200 mm	
	△ 1000 V		70 06 160	Diagonal Cutter	1	160 mm	
	△ 1000 V		74 06 200	High Leverage Diagonal Cutter	1	200 mm	
	△ 1000 V		78 06 125	Electronic Super Knips VDE	1	125 mm	
			87 01 180	KNIPEX Cobra®, Hightech Water Pump Pliers	1	180 mm	
	MM		97 53 18	KNIPEX Twistor®16 Self-Adjusting Crimping Pliers	1	478 mm	
	△ 1000 V		98 20 25	Screwdriver for slotted screws	1	2,5 mm	
	△ 1000 V		98 20 35 SL	Screwdriver (Slim) for slotted screws	1	0,6 x 3,5 x 100 mm	
			98 20 40 SL		1	0,8 x 4 x 100 mm	
			98 20 55 SL		1	1,0 x 5,5 x 125 mm	
			98 24 01 SL	Screwdrivers (Slim) for cross-recessed screws, Phillips®	1	PH 1 x 80	
	△ 1000 V		98 24 02 SL		1	PH 2 x 100	
			98 25 01 SL		1	PZ 1 x 80	
			98 25 02 SL		1	PZ 2 x 100	
	△ 1000 V		98 25 01 SLS	(Slim) PlusMinus screwdriver, Pozidriv®	1	187 mm	
			98 25 02 SLS		1	212 mm	
			98 26 10	Screwdriver for Torx® screws	1	160 mm TX 10	
			98 26 15		1	185 mm TX 15	
	△ 1000 V		98 26 20		1	185 mm TX 20	
			98 26 25		1	185 mm TX 25	
			98 26 30		1	210 mm TX 30	
				Folding rule	1	185 mm	
				Pocket Electric mini spirit level	1	430 mm	
				Spirit Level Type 70 Electric	1	400 mm	
				Safety locksmith's hammer, 300 g	1	290 mm	
				Electrician's Chisel	1	250 mm	
				8100 SA 8 Zyklus set of metal ratchets, 28 pieces	1		
				Set of hex key wrenches	1	1,5 - 10 mm	
00 21 06 LE	057512		Tool Case "BIG Basic Move", empty				6200

Tool Case "BIG Basic Move" Mechanic

Mobile professional equipment for mechanics

- ▶ Equipped with 12 KNIPEX tools, a total of 90 brand tools
- > For further benefits of the case, see page 10



Tool boards made from dirt-repellent PP twin-wall sheets



Base tray with separable inserts



Extendable telescopic handle



Smooth-running skater wheels

Content overview

00 11 01 KNIPEX		78 61 140 KNIPEX		Wera 12x		Stabila	
70 02 160 KNIPEX		16 95 01 SB KNIPEX		Wera 4x		12 parts Heyco	
74 02 200 KNIPEX		16 20 50 SB KNIPEX		Wera 4x		6 parts Rennsteig	
71 31 200 KNIPEX		86 01 250 KNIPEX		Picard		Rennsteig	
26 12 200 KNIPEX		87 01 250 KNIPEX		28 parts Wera			
26 22 200 KNIPEX		KNIPEX		9 parts Wera			

Article No.	EAN 4003773-				Quantity	Nominal size	g
00 21 06 M	N 086222			Tool Case "BIG Basic Move" Mechanic, 90 parts			12800
			00 11 01	KNIPEX TwinKey®, Control Cabinet Key	1		
			70 02 160	Diagonal Cutter	1	160 mm	
			74 02 200	High Leverage Diagonal Cutter	1	200 mm	
			71 31 200	KNIPEX CoBolt Compact Bolt Cutter	1	200 mm	
			26 12 200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers)	1	200 mm	
			26 22 200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers)	1	200 mm	
			78 61 140	Electronic Super Knips XL	1	140 mm	
			16 95 01 SB	KNIPEX ErgoStrip®, Universal Stripping Tool	1	135 mm	
			16 20 50 SB	Folding Knife for Electricians	1	120 mm	
			86 01 250	Pliers Wrench	1	250 mm	
			87 01 250	KNIPEX Cobra®, Hightech Water Pump Pliers	1	250 mm	
				Folding rule	1	185 mm	
				350 PH Screwdriver for Phillips screws	1		
				917 SPH Screwdriver for Phillips screws Kraftform Plus	1	PH2 x 100 mm	
				350 PH Screwdriver for Phillips screws	1	PH3 x 150 mm	
				355 PZ Screwdriver for Phillips screws	1	PZ1 x 80 mm	
				355 PZ Screwdriver for Phillips screws	1	PZ2 x 100 mm	
				355 PZ Screwdriver for Phillips screws	1	PZ3 x 150 mm	
				335 Screwdriver for slotted screws - electrician's blade	1	3,5 x 100 mm	
				335 Screwdriver for slotted screws - electrician's blade	1	4,0 x 100 mm	
				932 A Screwdriver for slotted screws 5.5 Kraftform Plus	1	5,5 x 100 mm	
				932 A Screwdriver for slotted screws 7.0 Kraftform Plus	1	7,0 x 125 mm	
				932 A Screwdriver for slotted screws 9.0 Kraftform Plus	1	7,0 x 125 mm	
				367 Screwdriver with holding function for TORX® screws	1	TX 10x80	
				367 Screwdriver with holding function for TORX® screws	1	TX 15x80	
				367 Screwdriver with holding function for TORX® screws	1	TX 20x100	
				367 Screwdriver with holding function for TORX® screws	1	TX 25x100	
				367 Screwdriver with holding function for TORX® screws	1	TX 30x115	
				Micro screwdriver PH0	1	PH0 x 60 mm	
				Micro screwdriver PH00	1	PH00 x 60 mm	
				Micro screwdriver 1.5	1	1,5 x 60 mm	
				Micro screwdriver 2.5	1	2,5 x 80 mm	
				Locksmith's hammer	Picard	300 g	
				8100 SA 8 Zyklop set of metal ratchets, 28 pieces	Wera	1/4"	
				Set of hex key wrenches	Wera	1,5 - 10 mm	
				Spirit level type 70 TM	Stabila	220 mm	
				Combination wrench sets	Heyco		
				Pin punch set	Heyco		
				Automatic centre punch	Rennsteig	130 mm	
00 21 06 LE	057512			Tool Case "BIG Basic Move", empty			6200

Tool Case "Robust45 Move" Mechanic

The big, robust one: Case with an extensive range of tools for mobile mechanics

- ▶ Equipped with 12 KNIPEX tools, a total of 90 brand tools
- ▶ Max. payload: 35 kg
- ▶ Volume: 45 litres
- > For the toughest conditions: Dust-tight, waterproof and temperature-resistant
- > Gas pressure absorber in the hinge
- > Pneumatically cushioned lid
- > Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- > With a total of 147 inserting options
- > Base tray with aluminium inserts
- > Extendable telescopic handle for comfortable transport
- > Large smooth-running wheels
- > External dimensions (W x H x D): 609 x 428 x 263 mm
- > Internal dimensions (W x H x D): 540 x 364 x 229 mm

Gas pressure absorber in the hinge: Convenient opening of the lid, with no risk of injury from the case closing inadvertently



With large, smooth rollers



Extendable telescopic handle

Content overview

00 11 01 KNIPEX		78 61 140 KNIPEX		Wera 12x		Stabila	
70 02 160 KNIPEX		16 95 01 SB KNIPEX		Wera 4x		12 parts Heyco	
74 02 200 KNIPEX		16 20 50 SB KNIPEX		Wera 4x		6 parts Rennsteig	
71 31 200 KNIPEX		86 01 250 KNIPEX		Picard		Rennsteig	
26 12 200 KNIPEX		87 01 250 KNIPEX		28 parts Wera			
26 22 200 KNIPEX		KNIPEX		9 parts Wera			

Article No.	EAN 4003773-				Quantity	Nominal size	g
00 21 37 M	N 086222			Tool Case "Robust45 Move" Mechanic, 90 parts			12800
			00 11 01	KNIPEX TwinKey®, Control Cabinet Key	1		
			70 02 160	Diagonal Cutter	1	160 mm	
			74 02 200	High Leverage Diagonal Cutter	1	200 mm	
			71 31 200	KNIPEX CoBolt Compact Bolt Cutters	1	200 mm	
			26 12 200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers)	1	200 mm	
			26 22 200		1	200 mm	
			78 61 140	Electronic Super Knips XL	1	140 mm	
			16 95 01 SB	KNIPEX ErgoStrip®, Universal Stripping Tool	1	135 mm	
			16 20 50 SB	Folding Knife for Electricians	1	120 mm	
			86 01 250	Pliers Wrench	1	250 mm	
			87 01 250	KNIPEX Cobra®, Hightech Water Pump Pliers	1	250 mm	
				350 PH Screwdriver for Phillips screws	1	PH1 x 80 mm	
				917 SPH Screwdriver for Phillips screws Kraftform Plus	1	PH2 x 100 mm	
				350 PH Screwdriver for Phillips screws	1	PH3 x 150 mm	
				355 PZ Screwdriver for Phillips screws	1	PZ1 x 80 mm	
					1	PZ2 x 100 mm	
				335 Screwdriver for slotted screws - electrician's blade	1	3,5 x 100 mm	
					1	4,0 x 100 mm	
				932 A Screwdriver for slotted screws 5.5 Kraftform Plus	1	5,5 x 100 mm	
				932 A Screwdriver for slotted screws 7.0 Kraftform Plus	1	7,0 x 125 mm	
				932 A Screwdriver for slotted screws 9.0 Kraftform Plus	1	7,0 x 125 mm	
				367 Screwdriver with holding function for TORX® screws	1	TX 10x80	
					1	TX 15x80	
					1	TX 20x100	
					1	TX 25x100	
					1	TX 30x115	
				Micro screwdriver PH0	1	PH0 x 60 mm	
				Micro screwdriver PH00	1	PH00 x 60 mm	
				Micro screwdriver 1.5	1	1,5 x 60 mm	
				Micro screwdriver 2.5	1	2,5 x 80 mm	
				Locksmith's hammer	Picard	1	300 g
				8100 SA 8 Zyklop set of metal ratchets, 28 pieces	Wera	1	1/4"
				Set of hex key wrenches	Wera	1	1,5 - 10 mm
				Folding ruler Stabila series 400	Stabila	1	185 mm
				Spirit level type 70 TM	Stabila	1	220 mm
				Combination wrench sets	Heyco	1	
				Pin punch set	Rennsteig	1	
				Automatic centre punch	Rennsteig	1	130 mm
00 21 37 LE	082590			Tool Case "Robust45 Move", empty			10800

KNIPEX StepCut®

Cable cutting made easy: Innovative step cutting separates wires one by one to save energy

- ▶ Small, light, strong: Comfortable cutting without crushing and just 160 mm in size
 - ▶ Noticeably less effort: The gradations cut wires one after the other; cutting is up to 40 % easier than with standard cable shears of the same length!
 - ▶ Ergonomic handle design: Optimal cutting feel even for larger cable diameters
- > Cuts multi-core stranded copper and aluminium cables up to Ø 15 mm (50 mm²)
 - > Cuts solid copper and aluminium cables up to 5 x 4 mm²
 - > Cuts without crushing
 - > Bolted joint: precise, effortless, durable
 - > Pinch guard fitted for safe work
 - > Not suitable for steel wire and hard drawn copper conductors
 - > Cutting edges additionally induction-hardened, cutting edge hardness approx. 56 HRC
 - > High-grade special tool steel, forged, oil-hardened




95 11 160




95 12 160



95 16 160



The gradations cut wires one after the other, without crushing



Cuts solid copper and aluminium cables up to 5 x 4 mm²



Bolted joint: Precise, effortless, durable; pinch guard fitted for safe work



Article No.	EAN 4003773-	↔ mm	Tool	Handles	Cutting capacities			g
					⊕ Ø mm	⊕ mm ²	AWG	
95 11 160	N 085904	160	burnished	plastic coated	15,0	50	1 / 0	180
95 11 160 SB	N 085911	160	burnished	plastic coated	15,0	50	1 / 0	205
95 12 160	N 085928	160	burnished	with multi-component grips	15,0	50	1 / 0	220
95 12 160 SB	N 085935	160	burnished	with multi-component grips	15,0	50	1 / 0	245
95 16 160	N 085966	160	⚡ 1000V	insulated with multi-component grips, VDE-tested	15,0	50	1 / 0	225
95 16 160 SB	N 085898	160	⚡ 1000V	insulated with multi-component grips, VDE-tested	15,0	50	1 / 0	250

Small, light, strong

Lighter, cleaner cut without crushing



Innovative
step cut

KNIPEX WireStripper- Multifunction Electrician Pliers, American style

Superior 7-in-1 multifunctional tool
for electrical installation

Designed for AWG cable cross-sections and UNC threads common in the USA, Great Britain, Australia – not suitable for metric cables and materials


- ▶ Strip faster: Precise positioning of the wire thanks to location ridges
- ▶ Innovative cutting edge geometry, particularly powerful cutting edges: 50 % higher cutting capacity and 25 % less cutting effort compared to standard wire strippers
- ▶ Fast, burr-free cutting of threaded rods and screws of UNC 6-32 and 8-32 up to class 4.6
- > Precisely ground: Stripping profiles for conductors from 18-10 AWG (solid) and 20-12 AWG (finely stranded)
- > Easy cutting of copper and aluminium cables up to Ø 15 mm (1/2")
- > Multifunctional gripping surfaces for reliable gripping, holding and bending of flat and round material as well as for twisting wires
- > High stability and good accessibility thanks to hybrid tips on the pliers head, which are flat and wide
- > Convenient: Comfortable opening width and ergonomic handle shape, integrated opening spring makes frequent cutting easier
- > Ideal for right- and left-handed users: locking device can be operated from either side
- > Clear-cut outside edges on the jaws for working on flush-mounted junction boxes and deburring feed-through holes
- > High-grade special tool steel, forged, multi stage oil-hardened




13 71 8



13 72 8



Laser marking of the stripping profiles for AWG dimensions shows stripping capacities for solid and stranded conductors



No screw in necessary: saves time cutting threaded rods and screws of sizes UNC 6-32 and 8-32 up to class 4.6



More convenience: cuts cables up to Ø 15 mm (1/2") up to 25% easier than comparably sized cable cutters, thanks to the stepped cutting edges



The precision-manufactured locating ridges allow for a quick selection of the correct stripping hole



The integrated opening spring makes frequent cutting easier – and it can be secured with a lock for transport

Article No.	EAN 4003773-	↔ mm		Pliers	Head	Handles	⊘ Inch	⊘ mm	AWG	⚖ g
13 71 8	086673	200		black atramentized	polished	plastic coated	1/2	15	20 - 10	260
13 72 8	086680	200		black atramentized	polished	with multi-component grips	1/2	15	20 - 10	275



WE ARE BUBBLING WITH IDEAS

And that is why we have even more new products for 2021 coming in May: Look forward to a world first in the sanitary trade, an ingenious sister of the combination pliers – and much more! A separate new products brochure will follow this spring.

NEW PRODUCTS

	Article No.	Designation	Page
	00 19 55 S6 N	Pliers Wrench Set 3 parts	124
	00 19 55 S6 LE N	Tool Roll for pliers wrenches, empty, 4 compartments	137
	00 19 55 S7 N	Pliers Wrench Set 3 parts	124
	00 19 55 S8 N	KNIPEX Cobra® Set, 3 parts	124
	00 19 55 S9 N	KNIPEX Cobra® Set, 3 parts	125
	00 19 55 S8 LE N	Tool Roll, for KNIPEX Cobra®, empty 4 compartments	137
	00 19 92 V01 LE N	Tool Roll, for insulated tweezers, empty, 5 compartments	138
	00 19 92 V02 LE N	Tool Roll, for tweezers, empty, 7 compartments	138
	00 21 06 N	Tool Case "BIG Basic Move" ElectricPlus, 68 parts, with integrated wheels and telescopic handle	132
	00 21 06 M N	Tool Case "BIG Basic Move" Mechanic, 90 parts, with integrated wheels and telescopic handle	132
	00 21 37 M N	Tool Case "Robust45 Move" Mechanic, 90 parts, with integrated wheels and telescopic handle	134
	00 31 30 BK V01 N	Electrical Installations Set	131
	09 05 240 N	Lineman's Pliers, American style	24
	09 15 240 N	Lineman's Pliers, American style	24
	13 71 8 N	KNIPEX WireStripper Multifunction Electrician Pliers, American style	29
	13 72 8 N	KNIPEX WireStripper Multifunction Electrician Pliers, American style	29

	Article No.	Designation	Page
	71 42 200 N	KNIPEX CoBolt Compact Bolt Cutter	52
	72 01 160 KA N	Diagonal Cutter for plastics	54
	92 21 01 N	KNIPEX Precision Tweezers premium stainless steel	73
	92 21 02 N	KNIPEX Precision Tweezers premium stainless steel	73
	92 21 03 N	KNIPEX Precision Tweezers premium stainless steel	73
	92 21 04 N	Mini Precision Tweezers premium stainless steel	73
	92 21 05 N	Mini Precision Tweezers premium stainless steel	73
	92 21 06 N	Mini Precision Tweezers premium stainless steel	73
	92 21 07 N	Universal Tweezers stainless steel	74
	92 21 08 N	Universal Tweezers stainless steel	74
	92 31 01 N	KNIPEX Precision Tweezers premium stainless steel	73
	92 51 01 N	Precision Tweezers premium stainless steel	73
	92 51 02 N	Mini Precision Tweezers premium stainless steel	73
	92 11 01 N	Cutting Tweezers stainless steel	73
	92 11 01 ESD N	Cutting Tweezers ESD stainless steel	73
	92 61 01 N	Universal Tweezers stainless steel	74
	92 61 02 N	Universal Tweezers stainless steel	74
	92 01 05 N	Universal Tweezers stainless steel	73
	92 01 06 N	Universal Tweezers stainless steel	73
	92 21 01 ESD N	Universal Tweezers ESD stainless steel	74
	92 21 02 ESD N	Universal Tweezers ESD stainless steel	74
	92 21 03 ESD N	Universal Tweezers ESD stainless steel	74
	92 23 01 N	Titanium Tweezers stainless steel	76
	92 01 01 N	SMD Precision Tweezers premium stainless steel	75
	92 01 02 N	SMD Precision Tweezers premium stainless steel	75
	92 01 03 N	SMD Precision Tweezers premium stainless steel	75
	92 01 04 N	SMD Precision Tweezers premium stainless steel	75
	92 91 01 N	Precision Cross Jaw Tweezers premium stainless steel	76
	92 91 02 N	Precision Cross Jaw Tweezers premium stainless steel	76

	Article No.	Designation	Page
	92 91 03	N Precision Cross Jaw Tweezers premium stainless steel	76
	92 81 01	N Tweezers with exchangeable tips ESD premium stainless steel	73
	92 81 02	N Tweezers with exchangeable tips ESD premium stainless steel	73
	92 81 03	N Tweezers with exchangeable tips ESD premium stainless steel	73
	92 81 04	N Tweezers with exchangeable tips ESD premium stainless steel	73
	92 81 05	N Tweezers with exchangeable tips ESD premium stainless steel	73
	92 89 01	N Exchangeable ESD tips for 92 81 01	73
	92 89 02	N Exchangeable ESD tips for 92 81 02	73
	92 89 03	N Exchangeable ESD tips for 92 81 03	73
	92 89 04	N Exchangeable ESD tips for 92 81 04	73
	92 89 05	N Exchangeable ESD tips for 92 81 05	73
	92 11 02	N Positioning Tweezers stainless steel	75
	92 11 03	N Positioning Tweezers stainless steel	75
	92 01 07	N Positioning Tweezers stainless steel	75
	92 16 01 ESD	N Positioning Tweezers ESD stainless steel	75
	92 16 02 ESD	N Positioning Tweezers ESD stainless steel	75
	92 47 01	N Universal Tweezers, insulated stainless steel	77, 108
	92 09 01 ESD	N Plastic Tweezers ESD	76
	92 09 02 ESD	N Plastic Tweezers ESD	76
	92 09 03 ESD	N Plastic Tweezers ESD	76
	92 09 04 ESD	N Plastic Tweezers ESD	76
	92 09 05 ESD	N Plastic Tweezers ESD	76
	92 00 01 ESD	N Universal Tweezers Set ESD, 5 parts	77, 134
	92 00 02	N Precision Tweezers Set 5 parts	77, 134
	92 00 03	N SMD Precision Tweezers Set 5 parts	77, 135
	92 00 04	N Universal Tweezers Set, insulated 5 parts	77, 135
	92 00 05 ESD	N Plastic Tweezers Set ESD 5 parts	77, 135

	Article No.	Designation	Page
	95 11 160 95 11 160 SB	N KNIPEX StepCut®, Cable shears with step cut	80
	95 12 160 95 12 160 SB	N KNIPEX StepCut®, Cable shears with step cut	80
	95 16 160 95 16 160 SB	N KNIPEX StepCut®, Cable shears with step cut	80, 109
	97 49 06 PI	N Crimping die, for insulated PIDG connectors	87
	97 49 21	N Crimping die, for insulated and non-insulated connectors	87
	98 12 01	N Screwdriver for Robertson screws	112
	98 12 02	N Screwdriver for Robertson screws	112
	98 65 43	N Electricians' Gloves size 9, class 1	116
	98 65 44	N Electricians' Gloves size 10, class 1	116
	98 65 45	N Electricians' Gloves size 11, class 1	116
	98 65 46	N Electricians' Gloves size 9, class 2	116
	98 65 47	N Electricians' Gloves size 10, class 2	116
	98 65 48	N Electricians' Gloves size 11, class 2	116
	98 65 49	N Electricians' Gloves size 9, class 3	116
	98 65 50	N Electricians' Gloves size 10, class 3	116
	98 65 51	N Electricians' Gloves size 11, class 3	116
		00 18 01 V36	N Counter Display for 10 x 03 02 180
	00 18 01 V38	N Counter Display for 6 x 90 31 02 SB	143
	00 18 01 V38 LE	N Counter Display for 6 x 90 31 02 SB	143
	00 18 01 V39	N Counter Display for 12 x 87 00 100	143
	00 18 01 V39 LE	N Counter Display for 12 x 87 00 100	143
	00 18 01 V40 LE	N Counter Display for 95 1x 160	143
	00 19 34 V02	N Wall Display insert, without pliers for KNIPEX Cobra® XS	150
	00 19 23 V02	N Sales Display, empty	145