


2023

wiha 
Tools that work for you

TOP SELLERS CATALOG



Heavy Duty RedStripe™ Backpack

**Extremely robust, extremely ergonomic
and extremely flexible**



Available Q1 2024!



77 storage and 30 flexible attachment options for tools or other utensils
External Zip Pockets keep tools and materials easily accessible and safe
Rear Compartment with padded laptop sleeve guarantees safety and security
Adjustable shoulder straps optimizes fit for maximum comfort
Durable water proof base keeps pack upright and gear dry in harsh environments
Zipper front pocket allows easy access to important gear

Heavy Duty RedStripe™ Backpack

Model #91869

21" H x 15.25" L x 10.25" W

Splash proof upper 1680D made of PU fabric and YKK zippers

Modular Foam Tray Sets



Three sizes of trays to organize each tool box drawer to fit your needs

Tool callout is printed on each tray to easily return tool to location

18 tray sets of the most popular tools available to set up tool cabinet drawers



3 TRAY SIZES



Small Tray Size:

11" x 7-3/4" x 1-1/4"

Item # 32081, 32960,
34680, 34681, 34690,
33395, 33396, 33795,
33796



Medium Tray Size:

15-1/2" x 11" x 1-1/4"

Item # 30280, 32080,
53180, 34682, 34691,
33895, 33896



Large Tray Size:

22" x 15-1/2" x 1-1/4"

Item #
30392, 30492

LARGE

FULL DRAWER SIZE, ONE TRAY PER STANDARD DRAWER



Made with premium-quality tool steel, roll-stamped die markings, and a chrome-plated satin finish.

31 Piece | SAE & Metric Combination Wrench Foam Tray Set

Model #30492

SAE | 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1"

Metric | 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 22, 24, 25mm

MODULAR SYSTEMS - Hundreds of options to choose from



Made with premium-quality tool steel, roll-stamped die markings, and a chrome-plated satin finish.



31 Piece | SAE & Metric Ratchet Wrench Foam Tray Set

Model #30392

SAE | 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1"

Metric | 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25mm

MEDIUM



Trays fit in most tool boxes



12 point deep and standard sockets made with premium tool steel, roll-stamped die markings, and a chrome-plated satin finish.

29 Piece | Metric 1/2" Drive Professional Socket Foam Tray Set

Model #33895

12 Standard Sockets | 10 - 21mm

13 Deep Sockets | 10-22mm

1/2" Dr. Ratchet | 72 Tooth

1/2" Drive Extension Bars | 3", 6"

1/2" Drive Universal Joint



12 point deep and standard sockets made with premium tool steel, roll-stamped die markings, and a chrome-plated satin finish.

28 Piece | SAE 1/2" Drive Professional Socket Foam Tray Set

Model #33896

11 Standard Sockets | 3/8" - 1"

13 Deep Sockets | 3/8" - 1-1/8"

1/2" Dr. Ratchet | 72 Tooth

1/2" Drive Extension Bars | 3", 6"

1/2" Drive Universal Joint

HALF DRAWER SIZE, TWO TRAYS PER STANDARD DRAWER



Patented pliers DynamicJoint® provides 40% easier cuts and significantly longer tool life. Designed with ergonomic soft grips, oil and solvent resistant.

8 Piece | Classic Grip Pliers & Cutters Foam Tray Set

Model #34682

Long Nose | 6.3"/160mm, 8.0"/200mm

BiCut Compound | 8.0"/200mm

Angled Diagonal Cutters | 8.0"/200mm

High Lev. Combination Pliers | 9.0"/225mm

Cable Cutters | 8.0"/200mm

Diagonal Cutters | 5.5"/140mm

Mechanic's Diagonal Cutters | 5.0"/127mm



For rapid gripping and holding of pipes and angular profiles such as hex nuts. Designed with oil and solvent resistant classic soft grips.

5 Piece | Classic Grip Adjustable Water Pump Pliers Foam Tray Set

Model #34691

Adjustable Pliers | 7.0"/180mm

Adjustable Pliers | 10.0"/250mm

Adjustable Pliers | 12.0"/300mm

Auto Grip | 10.0"/250mm

Pliers Wrench | 10.25"/260mm



Made in Germany



Designed with an ergonomic SoftFinish® cushion grip for maximum power and comfort. Extra heavy duty with hex bolster for more torque and metal cap for striking.

10 Piece | Extra Heavy Duty SoftFinish® Screwdriver Foam Tray Set

Model #53180

Slotted | 3.5, 4.5, 5.5, 6.5, 8.0, 10.0, 12.0mm

Phillips | #1, #2, #3



Made in Germany



Designed with an ergonomic SoftFinish® cushion grip for maximum power and comfort. Tips are machined to exact tolerances for a perfect fit every time.

10 Piece | SoftFinish® Screwdriver Foam Tray Set

Model #30280

Slotted | 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0mm

Phillips | #1, #2, #3



Made in Germany



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

10 Piece | Insulated SoftFinish® Screwdriver Foam Tray Set

Model #32080

Slotted | 3.5, 4.5, 4.5, 5.5, 6.5mm

Phillips | #1, #2, #3

Square | #1, #2

SMALL



6 point deep & standard sockets made with premium tool steel, roll-stamped die markings, and a chrome-plated satin finish.

27 Piece | Metric 1/4" Drive Professional Socket Foam Tray Set

Model #33395

12 Standard Sockets | 4 - 14mm
11 Deep Sockets | 5 - 14mm
1/4" Dr. Ratchet | 72 Tooth
1/4" Drive Extension Bars | 3", 6"
1/4" Drive Universal Joint



6 point deep & standard sockets made with premium tool steel, roll-stamped die markings, and a chrome-plated satin finish.

25 Piece | SAE 1/4" Drive Professional Socket Foam Tray Set

Model #33396

12 Standard Sockets | 5/32" - 9/16"
11 Deep Sockets | 5/32" - 9/16"
1/4" Dr. Ratchet | 72 Tooth
1/4" Drive Extension Bars | 3", 6"
1/4" Drive Universal Joint



Patented pliers DynamicJoint® provides 40% easier cuts and significantly longer tool life. Designed with ergonomic soft grips, oil and solvent resistant.

3 Piece | Classic Grip Pliers & Cutters Foam Tray Set

Model #34680

Long Nose | 8.0"/200mm
Angled Cutters | 8.0"/200mm
Lineman's Pliers w/Crimper's | 9.0"/225mm

QUARTER SIZE, FOUR TRAYS PER STANDARD DRAWER



12 point deep & standard sockets made with premium tool steel, roll-stamped die markings, and a chrome-plated satin finish.

24 Piece | Metric 3/8" Drive Professional Socket Foam Tray Set

Model #33795

10 Standard Sockets | 8 - 19mm
10 Deep Sockets | 8 - 19mm
3/8" Dr. Ratchet | 72 Tooth
3/8" Drive Extension Bars | 3", 6"
3/8" Drive Universal Joint



12 point deep & standard sockets made with premium tool steel, roll-stamped die markings, and a chrome-plated satin finish.

22 Piece | SAE 3/8" Drive Professional Socket Foam Tray Set

Model #33796

9 Standard Sockets | 1/4" - 3/4"
9 Deep Sockets | 1/4" - 3/4"
3/8" Dr. Ratchet | 72 Tooth
3/8" Drive Extension Bars | 3", 6"
3/8" Drive Universal Joint



Patented pliers DynamicJoint® provides 40% easier cuts and significantly longer tool life. Designed with ergonomic soft grips, oil and solvent resistant.

4 Piece | Classic Grip Pliers & Cutters Foam Tray Set

Model #34681

Long Nose | 6.3"/180mm, 8.0"/200mm
BiCut Compound Cutters | 8.0"/200mm
Lineman's Pliers w/Crimper's | 9.0"/225mm



Patented pliers DynamicJoint® provides 40% easier cuts and significantly longer tool life. Each tool tested at 10,000 Volts & rated to 1000 Volts AC or 1500 Volts DC.

3 Piece | Insulated Pliers & Cutters Foam Tray Set

Model #32960

Long Nose | 8.0"/200mm
Angled Cutters | 8.0"/200mm
NE Style Lineman's | 9.5"/245mm



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

5 Piece | Insulated SoftFinish® Screwdriver Foam Tray Set

Model #32081

Slotted | 4.5, 5.5, 6.5mm
Phillips | #1, #2



For rapid gripping and holding of pipes and angular profiles such as hex nuts. Designed with oil and solvent resistant classic soft grips.

3 Piece | Classic Grip Adjustable Water Pump Pliers Foam Tray Set

Model #34690

Adjustable Pliers | 7.0"/180mm
Adjustable Pliers | 10.0"/250mm
Auto Grip | 10.0"/250mm

Made in
Germany

Each handle is sized proportionately for powerful torque and less fatigue

SoftFinish® cushion grip handles for maximum torque

10,000 Volt Tested and 1,000 Volt Rated

 Made in Germany



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

2 Piece | Insulated SoftFinish® Screwdriver Set

Model #33580

Slotted | 6.5mm Phillips | #2



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

5 Piece | Insulated SoftFinish® Screwdriver Set

Model #32091

Slotted | 3.0, 4.5, 6.5mm Phillips | #1, #2



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

7 Piece | Insulated SoftFinish® Screwdriver Set

Model #32099

Slotted | 3.5, 4.0, 5.5, 6.5mm Phillips | #1, #2, #3



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

4 Piece | Insulated SoftFinish® Screwdriver Set

Model #32090

Slotted | 3.5, 4.5mm Phillips | #1, #2



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

6 Piece | Insulated SoftFinish® Screwdriver Set

Model #32092

Slotted | 3.5, 4.5, 6.5mm Phillips | #1, #2, #3



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

10 Piece | Insulated SoftFinish® Screwdriver Set

Model #32093

Slotted | 2.0, 2.5, 3.0, 3.5, 4.5, 6.5mm Phillips | #0, #1, #2, #3

For your safety, use tools marked:



ASTM F1505 **GOOD**
> Meets Specifications




IEC 60900 **BETTER**
> Meets Specifications




VDE 0680 **BEST**
> Certified & Tested

 **Made in Germany**



Individually tested to block potentially hazardous voltages from reaching you
Double insulation certified to protect user and equipment
Ergonomic cushion grip handles for less strain and maximum comfort




In plastic storage box

Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

7 Piece | Insulated SoftFinish® Screwdriver Set

Model #32188

Slotted | 2.0, 2.5, 3.0, 3.5, 4.0mm
Phillips | #0, #1




Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

5 Piece | Insulated SoftFinish® Screwdriver Set

Model #32059

Slotted | 4.5, 6.5mm
Phillips | #1, #2
Square | #2



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

7 Piece | Insulated SoftFinish® Screwdriver Set

Model #32097

Slotted | 3.5, 5.5, 6.5mm
Phillips | #1, #2
Square | #1, #2




Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

13 Piece | Insulated SoftFinish® Screwdriver Set

Model #32094

Slotted | 2.0, 2.5, 3.0, 3.5, 4.5, 5.5, 6.5, 8.0, 10.0mm
Phillips | #0, #1, #2, #3




Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

6 Piece | Insulated SoftFinish® Screwdriver Set

Model #35890

Slotted | 4.5, 6.5mm
Phillips | #1, #2
Square | #1, #2



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

7 Piece | Insulated SoftFinish® Screwdriver Set

Model #32087

Slotted | 4.0, 5.5, 6.5mm
Phillips | #1, #2, #3 **Square** | #2
Insulated Single Pole Voltage Detector

Insulated SoftFinish® Screwdriver & Nut Driver Sets



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

19 Piece | Insulated SoftFinish® Screwdrivers In Tool Box Tray

Model #30295

Slotted | 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0, 10.0mm

Phillips | #0, #1, #2, #3

Square | #1, #2

Xeno Terminal | #1, #2

Cat. III Voltage Detector | Battery Operated



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

15 Piece | Insulated SoftFinish® Screwdriver Set

Model #32190

Slotted | 2.5, 2.5, 3.0, 3.5, 4.5, 6.5, 8.0mm

Phillips | #1, #2, #3

SAE Nut Drivers | 1/4, 5/16, 3/8, 7/16, 1/2"

In roll-up pouch



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

9 Piece | Insulated SoftFinish® SAE Nut Driver Set

Model #32288

SAE Nut Drivers | 3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8"



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

10 Piece | Insulated SoftFinish® Screwdrivers

Model #32592

TORX® | T6, T7, T8, T9, T10, T15, T20, T25, T27, T30



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

5 Piece | Insulated SoftFinish® SAE Nut Driver Set

Model #32292

SAE Nut Drivers | 7/32, 1/4, 5/16, 3/8, 1/2"



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

11 Piece | Insulated SoftFinish® SAE Nut Driver Set

Model #32296

SAE Nut Drivers | 5/32, 3/16, 7/32, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8"



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

6 Piece | Insulated SoftFinish® Screwdrivers

Model #32590

TORX® | T8, T9, T10, T15, T20, T25



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

7 Piece | Insulated SoftFinish® SAE Nut Driver Set

Model #32294

SAE Nut Drivers | 3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

7 Piece | Insulated SoftFinish® Metric Nut Driver Set

Model #32293

Metric Nut Drivers | 5.0, 5.5, 6.0, 7.0, 8.0, 10.0, 13.0mm

Insulated SoftFinish® SlimLine Screwdriver Sets



Wiha SlimTECHNOLOGY

Achieves blade diameters up to 33% narrower utilizing integrated insulation

Insulation Test Standards:

According to EN/IEC, ASTM, VDE, DIN 7437, NFPA & CSA specification


Integrated Slim Insulation molded directly onto blade



 **Made in Germany**



Ideal for jobs where access is limited




Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC. PicoFinish® rotating cap for precise turning and control with fingertip.

8 Piece | Insulated PicoFinish® Screwdriver Set

Model #32088

Slotted | 1.5, 2.0, 2.5, 3.0, 3.5mm
Phillips | #00, #0, #1



5 Piece | Insulated PicoFinish® Screwdriver Set

Model #32085

Slotted | 1.5, 2.5, 3.5mm
Phillips | #0, #1



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

6 Piece | Insulated SlimLine SoftFinish® Screwdriver Set

Model #32196

Slotted | 4.5, 6.5mm
Phillips | #1, #2
Square | #1, #2




Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

8 Piece | Insulated SlimLine SoftFinish® Screwdriver Set

Model #32197

Slotted | 3.5, 4.0, 4.5, 5.5mm
Phillips | #1, #2
Square | #1, #2



Designed with an SoftFinish® cushion grip for maximum power and comfort. Each tool tested at 10,000 Volts and rated to 1,000 Volts AC or 1,500 Volts DC

11 Piece | Insulated SlimLine SoftFinish® Screwdriver Set

Model #32198

Slotted | 3.5, 4.0, 4.5, 5.5, 6.5mm
Phillips | #1, #2 Square | #1, #2
Xeno Terminal | #1, #2

Switch Cabinet Key



For applications with all common switch cabinets and locking systems. Diecast Zinc. Bit insert Slotted 7.0mm & Phillips #2. Adapter for 1/4" bits on securing chain and 1/4" bit adapter in one arm.

Switch Cabinet Key

Model #

21103 3.0"/76mm

Insulated SoftFinish® SlimLine Screwdriver Sets

Friction hold blade holder, holds blades securely. Up to 33% narrower insulation diameter than standard insulated tools.



Made in Germany

SoftFinish® cushion grip handles for comfort and control



Blades High quality CV steel, through-hardened

Locking blade holder securely holds blades in place for precise fastening

1000Volt Rated
10,000 Volt Tested

Certified to VDE, EN ISO, BS EN, ASME specifications



Each SlimLine bit can be taken in and out of the holder easily and conveniently



7 Piece | Insulated SoftFinish® SlimLine Blade Set

Model #28391

Slotted | 4.0, 6.5mm
Phillips | #1, #2
Terminal Xeno SLT/PH | #2
TORX® | T15, T20
28301 | SlimLine Blade Holder



30 Piece | Insulated SoftFinish® SlimLine Blade Set

Model #28399

Slotted | 2.5, 3.0, 3.5, 4.0, 5.5, 6.5mm
Phillips | #1, #2 Square | #1, #2
Pozidriv® | #1, #2
Terminal Xeno SLT/PH | #1, #2
Terminal Xeno SLT/PZ | #1, #2
Hex Metric | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
28301 | SlimLine Blade Holder



"Apprentice"

Cushion grip. Friction hold blade holder, holds blades securely. Up to 33% narrower insulation diameter than standard insulated tools.

7 Piece | Insulated Pop-Up SlimLine Blade Set

Model #28393

Slotted | 3.0, 4.0, 5.5, 6.5mm
Phillips | #1, #2



"Residential"

7 Piece | Insulated Pop-Up SlimLine Blade Set

Model #28394

Slotted | 3.0, 4.0mm
Phillips | #1, #2
Square | #1, #2



"MRO"

7 Piece | Insulated Pop-Up SlimLine Blade Set

Model #28395

Slotted | 3.0, 4.0mm
Phillips | #1, #2 & Terminal Xeno | #1, #2



15 Piece | Insulated SoftFinish® SlimLine Blade Set

Model #28390

Slotted | 3.0, 4.0, 5.5, 6.5mm
Phillips | #1, #2 Square | #1, #2
Terminal Xeno SLT/PH | #1, #2
TORX® | T8, T10, T15, T20
28301 | SlimLine Blade Holder



19 Piece | Insulated SoftFinish® SlimLine Blade Set

Model #28398

Slotted | 3.0, 4.0, 5.5mm Phillips | #1, #2
Square | #1, #2 TORX® | T8, T10, T15, T20
Terminal Xeno SLT/PH | #1, #2
Terminal Xeno SLT/PZ | #1, #2
Hex Metric | 3.0, 4.0, 5.0mm
28301 | SlimLine Blade Holder



Insulated TorqueControl SlimLine Blade Sets

 **Made in Germany**



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. With certificate of calibration.

20 Piece | Insulated SoftFinish® TorqueControl Blade Set

Model #28781

Slotted | 2.5, 3.5, 4.0, 6.5mm

Phillips | #1, #2 (qty. 2 of #2) Square | #1, #2

TORX® | T10, T15, T20, T25

Terminal Xeno SLT/PH | #1, #2

TorqueControl-S Handle | 10-50 In/lbs.

SoftFinish® Handle | Holds SlimLine Blades

PicoFinish® Handle | Holds SlimLine Blades

SlimLine Blade Holder | 6.75" OAL

Torque Adjustment Tool



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. With certificate of calibration.

8 Piece | Insulated SoftFinish® TorqueControl Blade Set

Model #28791

Slotted | 3.0, 4.0, 5.5mm

Phillips | #1, #2

TorqueControl-S Handle | 10-50 In/lbs.

SlimLine Blade Holder | 6.75" OAL

Torque Adjustment Tool



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. With certificate of calibration.

16 Piece | Insulated SoftFinish® TorqueControl Blade Set

Model #28792

Slotted | 4.0, 5.5, 6.5mm

Phillips | #1, #2 Square | #1, #2

TORX® | T8, T10, T15, T20

Terminal Xeno SLT/PH | #1, #2

TorqueControl-S Handle | 18-62 In/lbs.

SoftFinish® Handle | Holds SlimLine Blades

PicoFinish® Handle | Holds SlimLine Blades

SlimLine Blade Holder | 6.75" OAL

Torque Adjustment Tool

Insulated speedE-II Electric SlimLine Blade Set



 **Made in Germany**

13 Piece | Insulated speedE-II SlimLine Blade Set

Model #32490

Slotted | 3.5, 5.5mm

Phillips | #1, #2 Square | #1, #2

Terminal Xeno SLT/PH | #1, #2

speedE-II Electric Handle | 0.4 Nm - 1.0 Nm

*speedE electric screwdriver is only insulated when used with Wiha SlimLine blades



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. With certificate of calibration.

11 Piece | Insulated SoftFinish® TorqueControl Blade Set

Model #28789

Slotted | 4.0, 6.5mm

Phillips | #1, #2 Square | #1, #2

Terminal Xeno SLT/PZ | #1, #2

TorqueControl-S Handle | 10-50 In/lbs.

SlimLine Blade Holder | 6.75" OAL

Torque Adjustment Tool

Insulated PocketMax® SlimLine Screwdriver



Cushion grip. Friction hold blade holder, holds blades securely. Up to 33% narrower insulation diameter than standard insulated tools.



6 Piece | Insulated PocketMax® SlimLine Blade Set

Model #28345

Slotted | 3.5, 6.5mm

Phillips | #1, #2 Square | #2

Compact and light weight, fits easily into a pants or shirt pocket




Insulated Master Electrician's Tools

Insulation Test Standards:

Insulation according to EN/IEC 60900,
ASTM F-1505, New VDE 0682/part 201,
DIN 7437, NFPA70E & CSA

1000Volt
Rated
10,000 Volt
Tested

All Tools In
Dedicated
Positions For
Quick Storage &
Easy Location
Tracking



Inch



Metric



Included in #32801

80 Piece Insulated Master Electrician's Tool Set

Model #32800

6.3" Long Nose Pliers	6.3" Diagonal Cutters
8.0" Long Nose Pliers	8.0" High Leverage Cutters
6.3" Bent Nose Pliers	6.3" Cable Cutters
6.3" Long Flat Nose Pliers	6.3" Stripping Pliers
9.0" Combo Pliers/Crimper's	8.0" Adjustable Wrench

SAE Sockets | 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8"

METRIC Sockets | 13.0, 14.0, 15.0, 17.0, 19.0, 20.0, 22.0mm

Ratchet | 3/8" Drive / **4.9" Extension** | 3/8" Drive

SAE Nut Drivers | 7/32, 1/4, 5/16, 3/8, 7/16"

METRIC Nut Drivers | 5.0, 5.5, 6.0, 7.0, 8.0, 10.0, 13.0mm

T-handle SAE Hex | 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

T-handle METRIC Hex | 4.0, 5.0, 6.0, 8.0mm

Slotted | 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0, 10.0mm

Phillips | #0, #1, #2, #3

Xeno Slotted/Phillips Terminal | #1, #2

Square | #1, #2

TORX | T6, T7, T8, T9, T10, T15, T20, T25, T30

L-key | 10mm / **L-key** | 1/2"

Cable Knife | 50mm

Folding Ruler | SAE/MM

Cat. III Voltage Detector | Battery Operated

112 Piece Insulated Master Electrician's Tool Set

Model #32801

6.3" Long Nose Pliers	6.3" Diagonal Cutters
8.0" Long Nose Pliers	8.0" High Leverage Cutters
6.3" Bent Nose Pliers	6.3" Cable Cutters
6.3" Long Flat Nose Pliers	6.3" Stripping Pliers
9.0" Combo Pliers/Crimper's	8.0" Adjustable Wrench

SAE Sockets | 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8"

METRIC Sockets | 13.0, 14.0, 15.0, 17.0, 19.0, 20.0, 22.0mm

Ratchet | 3/8" Drive / **4.9" Extension** | 3/8" Drive

SAE Nut Drivers | 7/32, 1/4, 5/16, 3/8, 7/16"

METRIC Nut Drivers | 5.0, 5.5, 6.0, 7.0, 8.0, 10.0, 13.0mm

T-handle SAE Hex | 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

T-handle METRIC Hex | 4.0, 5.0, 6.0, 8.0mm

Slotted | 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0, 10.0mm

Phillips | #0, #1, #2, #3

Xeno Slotted/Phillips Terminal | #1, #2

Square | #1, #2

TORX | T6, T7, T8, T9, T10, T15, T20, T25, T30

L-key | 10mm / **L-key** | 1/2"

Cable Knife | 50mm

Folding Ruler | SAE/MM

Cat. III Voltage Detector | Battery Operated

SAE Deep Offset Ring Wrenches | 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/4"

METRIC Deep Offset Ring Wrenches | 8.0, 9.0, 10.0, 11.0, 12.0, 13.0, 14.0, 15.0, 17.0, 19.0, 20.0, 22.0, 24.0, 27.0, 30.0, 32.0mm

Insulated Electrician's Tool Sets



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

66 Piece Insulated Electrician's Tool Set

Model #32876

8.0" Long Nose	6.3" Side Cutters
6.3" Long Flat Nose	8.0" BiCut SuperCut
9.0" Combo Pliers/Crimper's	6.3" Stripping Pliers
8.0" Cable Cutters	8.0" Adjustable Wrench

Slotted | 2.0, 2.5, 3.0, 4.0, 4.5, 5.5, 6.0, 8.0, 10.0mm

Phillips | #0, #1, #2, #3

TORX | T8, T10, T15, T20, T25, T30

Square | #1, #2

Slit/Ph Terminal | #1, #2

Nut Drivers SAE | 1/4, 5/16, 11/32, 3/8, 7/16"

T-handle Metric | 4.0, 5.0, 6.0, 8.0mm

T-handle SAE | 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Hex L-keys | 1/2", 10.0mm

Sockets SAE | 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8"

Sockets Metric | 8, 10, 13, 14, 15, 17, 19, 22mm

Extension Bar | 4.9"

Ratchet | 3/8" Drive

Cable Knife | 50mm



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

50 Piece Insulated Electrician's Tool Set

Model #32874

6.3" Long Nose Pliers	6.3" Side Cutters
8.0" Long Nose Pliers	8.0" BiCut SuperCut
6.3" Combination Pliers	6.3" Stripping Pliers
9.0" Combo Pliers/Crimper's	8.0" Adjustable Wrench
10.0" Water Pump Pliers	

Slotted | 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 8.0mm

Phillips | #0, #1, #2, #3 **Square** | #1, #2

TORX | T8, T9, T10, T15, T20, T25, T27, T30

Slit/Ph Terminal | #1, #2

Hex SAE | 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Nut Driver SAE | 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"

Cable Knife | 50mm & **Folding Ruler** | SAE/Metric

Battery Operated Voltage Detector 110V | Category IV



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

25 Piece Insulated Electrician's Tool Set

Model #32879

8.0" Long Nose	8.0" BiCut SuperCut
9.0" Combination Pliers	6.3" Stripping Pliers

Slotted | 3.0, 4.5, 6.0mm

Phillips | #1, #2 **Square** | #1, #2

Slit/Ph Terminal | #1, #2

Nut Driver SAE | 1/4, 5/16, 11/32, 3/8, 7/16, 1/2"

Nut Driver Metric | 7.0, 8.0, 10.0, 13.0mm

Cable Knife | 50mm

Folding Ruler | SAE/Metric

Insulated Tool Sets



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

14 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32895

8.0" Long Nose 6.3" Side Cutters
9.0" Combination Pliers 8.0" BiCut SuperCut
6.3" Stripping Pliers

Slotted | 2.0, 2.5, 3.0, 3.5, 4.5, 6.5mm

Phillips | #1, #2, #3



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

13 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32894

8.0" Bent Nose 8.0" Combination Pliers
6.3" Long Nose 6.3" Side Cutters
10" Water Pump Pliers

Slotted | 4.5, 6.5mm Phillips | #1, #2

SAE Nut Drivers | 1/4, 5/16, 3/8, 1/2"



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

14 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32869

9.0" Lineman's Pliers 8.0" BiCut SuperCut
8.0" Cable Cutters 8.0" Long Nose Pliers
6.0" Stripping Pliers 10-20 AWG

SlimLine Slotted | 3.0, 4.5, 6.5mm SlimLine Phillips | #1, #2

SlimLine Square | #1, #2 SlimLine Terminal | #2

Single Pole Tester | 3.0mm



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

13 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32878

8.0" Long Nose Pliers 50mm Cable Stripping Knife
8.0" BiCut Compound Cutters
9.0" Combination Pliers with Crimper's

Slotted | 3.0, 4.5, 6.0mm Phillips | #1, #2

Square | #1, #2 Zeno Terminal Sit/Ph | #1, #2



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

11 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32888

6.3" Long Nose	6.3" Side Cutters
8.0" Combination Pliers	6.3" Stripping Pliers

Slotted | 2.5, 3.5, 4.5, 6.0mm Phillips | #0, #1, #2



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

10 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32868

7.0" Diagonal Cutters	9.0" Combo Pliers
8.0" Long Nose Pliers	6.3" Wire Strippers
7.0" Crimping Pliers	

Slotted | 3.0, 4.5, 6.0mm Phillips | #1, #2



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

10 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32891

8.0" Combination Pliers	8.0" Long Nose
8.0" BiCut SuperCut	6.3" Cable Cutters
6.3" Universal Wire Stripper	

Slotted | 4.5, 6.5mm Phillips | #1, #2, #3



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

3 Piece Insulated Pliers & Cutters Tool Set

Model #32873

6.3" / 160mm Diagonal Cutters
8.0" / 200mm Long Nose Pliers
8.0" / 200mm Combination Pliers



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

10 Piece Insulated Pliers & Screwdrivers Tool Set

Model #32892

8.0" Bent Nose	8.0" Combination Pliers
6.3" Long Nose	6.3" Side Cutters

Slotted | 3.0, 4.5, 6.5mm Phillips | #0, #1, #2



Insulated Industrial Tool Sets

**1000Volt
Rated**
10,000 Volt
Tested



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

3 Piece | Industrial Insulated Pliers & Cutters Tool Set

Model #32968

9.5"/245mm Industrial NE Style Lineman's Pliers
8.0"/200mm Industrial Long Nose Pliers
8.0"/200mm Industrial Heavy Duty Diagonal Cutters



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

16 Piece | Industrial Insulated Apprentice Tool Set

Model #32934

9.5" Industrial NE Style Lineman's Pliers
8.0" Industrial Long Nose Pliers
8.0" Industrial Heavy Duty Diagonal Cutters
7.25" Wire Stripping Pliers 10-20 AWG

Slotted | 4.5, 6.5mm **Phillips** | #1, #2 & **Square** | #2

Insulated PicoFinish® Precision Screwdrivers:

Slotted | 2.5, 3.0, 3.5mm **Phillips** | #0

25 Ft. Tape Measure, 20 oz. Claw Hammer, 9" Torpedo Level



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

30 Piece | Industrial Insulated Journeyman's Electrician's Tool Set

Model #32935

9.5" Industrial NE Style Lineman's Pliers
8.0" Industrial Long Nose Pliers
8.0" Industrial Heavy Duty Diagonal Cutters
8.0" Industrial Cable Cutters
10.0" Water Pump Pliers
10.0" Auto Water Pump Pliers
7.25" Wire Stripping Pliers 10-20 AWG

Slotted | 4.0, 4.5, 6.5mm

Phillips | #1, #2 **Square** | #1, #2

SAE Nut Drivers | 1/4, 5/16, 3/8"

Insulated PicoFinish® Precision Screwdrivers:

Slotted | 2.5, 3.0, 3.5mm **Phillips** | #0, #1

Extra Heavy Duty SoftFinish® Slotted Screwdriver | 8.0mm

Nut Setters | 1/4, 5/16, 3/8"

25 Ft. Tape Measure, 20 oz. Claw Hammer, 9" Torpedo Level

5.75" Cat. IV Voltage Detector 50-1000 Volts



Insulated Industrial Tool Sets



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

59 Piece | Industrial Insulated Master Electrician's Tool Set

Model #32937

9.5" Industrial NE Style Lineman's Pliers
8.0" Industrial Long Nose Pliers
8.0" Industrial Heavy Duty Diagonal Cutters
8.0" Industrial Cable Cutters
10.0" Water Pump Pliers
10.0" Auto Water Pump Pliers
7.25" Wire Stripping Pliers 10-20 AWG

Slotted | 4.0, 4.5, 5.5, 6.5mm

Phillips | #1, #2 Square | #1, #2

Xeno Slotted/Phillips Terminal | #1, #2

Nut Drivers Inch | 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"

Insulated PicoFinish® Precision Screwdrivers:

Slotted | 2.5, 3.0, 3.5mm Phillips | #00, #0, #1

22 Pc. ErgoStar Ball End Hex Inch & Metric L-keys

Inch | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Metric | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

Extra Heavy Duty SoftFinish® Slotted Screwdriver | 8.0mm

Nut Setters | 1/4, 5/16, 3/8"

25 Ft. Tape Measure, 20 oz. Claw Hammer, 9" Torpedo Level

5.75" Cat. IV Voltage Detector 50-1000 Volts



33% narrower



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

22 Piece | Industrial Insulated Electrician's Tool Set

Model #32973

9.0" Lineman's Pliers W/Cutters

8.0" Long Nose Pliers W/Cutter

8.0" Diagonal Cutters

SlimLine Slotted | 3.5, 4.5mm

SlimLine Phillips | #1, #2

SlimLine Square | #1, #2

SlimLine Terminal Xeno | #1, #2

SAE T-handle Hex SAE | 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

SAE Nut Drivers | 3/8, 7/16, 1/4, 5/16"

Cable Stripping Knife | 50mm



33% narrower



Insulated cushion grip handles for comfort and control. Certified to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505, NFPA70E & CSA standards. 1000 volt rated, individually tested. Industrial brushed finished pliers & cutters, premium quality tool steel for strength and durability.

11 Piece | Industrial Insulated Electrician's Tool Set

Model #32977

6.3" & 8.0" Long Nose Pliers W/Cutter

6.3" Diagonal Cutters

8.0" High Leverage Cutters

8.0" Combination Pliers

SlimLine Slotted | 3.0, 4.0, 6.5mm

SlimLine Phillips | #0, #1, #2

Insulated Industrial Tool Sets

 **1000Volt Rated**
10,000 Volt
Tested



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards.
1000 volt rated. Individually Tested. Pliers & cutters,
Industrial brushed finish.

14 Piece | Insulated Pliers & Screwdrivers Set

Model #32192

6.3" & 8.0" Long Nose Pliers with Cutters
8.0" Combination Pliers
6.3" Diagonal Cutters

Slotted | 3.0, 4.5, 6.5mm

Phillips | #1, #2

SAE Nut Drivers | 1/4, 5/16, 11/32, 3/8, 1/2"



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards.
1000 volt rated. Individually Tested. Pliers & cutters,
Industrial brushed finish.

8 Piece | Insulated Pliers & Cutters Set

Model #32987

6.3" Long Nose Pliers with Cutters
6.3" Diagonal Cutters
8.0" Long Nose Pliers
8.0" H.D. Diagonal Cutters
9.0" Lineman's Pliers with Cutters
6.3" Stripping Pliers
8.0" Cable Cutters
7.0" Crimper's



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards.
1000 volt rated. Individually Tested. Pliers & cutters,
Industrial brushed finish.

3 Piece | Insulated Pliers & Cutters Set

Model #32981

8.0" Long Nose Pliers
8.0" Diagonal Cutters
8.0" Combination Pliers



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards.
1000 volt rated. Individually Tested. Pliers & cutters,
Industrial brushed finish. In belt pack pouch

7 Piece | Insulated Pliers & Screwdrivers Set

Model #32985

6.3" Long Nose Pliers
6.3" Diagonal Cutters
8.0" Combination Pliers

Slotted | 3.0, 4.5mm **Phillips** | #1, #2



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards.
1000 volt rated. Individually Tested. Pliers & cutters,
Industrial brushed finish.

11 Piece | Insulated Pliers & Screwdrivers Set

Model #32986

6.3" Long Nose Pliers with Cutters
6.3" Diagonal Cutters
8.0" Combination Pliers
6.3" Stripping Pliers

Slotted | 3.0, 4.5, 5.5mm

Phillips | #1, #2

Square | #1, #2



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards.
1000 volt rated. Individually Tested. Pliers & cutters,
Industrial brushed finish. In blow molded tray

8 Piece | Insulated Pliers & Cutters Set

Model #32999

9.0" Lineman's Pliers
8.0" High Leverage Combo Pliers
6.3" & 8.0" Long Nose Pliers with Cutters
8.0" Cable Cutters
6.3" & 8.0" Diagonal Cutters
6.3" Stripping Pliers
7.0" Crimping Pliers



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards.
1000 volt rated. Individually Tested. Pliers & cutters,
Industrial brushed finish. Cushion grip friction hold bit
holder. In belt pack pouch

17 Piece | Insulated Pop-Up Bit Holder & Pliers/Cutters Set

Model #32990

8.0" Long Nose Pliers
8.0" High Leverage Cutters
9.5" Lineman's Pliers

Slotted | 4.5, 5.5, 6.0mm **Phillips** | #0, #1, #2, #3

Square | #1, #2, #3 **TORX®** | T15, T20, T25

Insulated Industrial Tool Sets



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Dynamic joint provides 40% easier cuts & significantly longer tool life. C70 special tool steel. Industrial brushed finish.

Insulated Industrial Long Nose Pliers with Cutters

Model #	↔	Cut Cap. Copper AWG
32926	6.3"/160mm	#10
32923	8.0"/200mm	#8



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Cutting capacity up to 3mm hardened piano wire. Industrial brushed finish. Double the power at a press of the button.

Insulated Industrial BiCut Compound Cutters

Model #	↔
32936	8.0"/200mm



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Dynamic joint provides 40% easier cuts & significantly longer tool life. C70 special tool steel. Industrial brushed finish.

Insulated Industrial Serrated Cutters

Model #	↔
32902	6.3/160mm
32927	8.0"/200mm



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Dynamic joint provides 40% easier cuts & significantly longer tool life. C70 special tool steel. Industrial brushed finish.

Insulated Industrial Diagonal Cutters

Model #	↔	Cut Cap. Copper AWG
32933	6.3"/160mm	#6
32929	8.0"/180mm	#6



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Dynamic joint provides 40% easier cuts & significantly longer tool life. C70 special tool steel. Industrial brushed finish.

Insulated Industrial High Leverage Combination Pliers

Model #	↔	Cut Cap. Copper AWG
32930	8.0"/200mm	#4



Knurled Striking Zone



Meets EN/IEC, ASTM, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Dynamic joint provides 40% easier cuts & significantly longer tool life. C70 special tool steel. Industrial brushed finish.

Insulated Industrial Lineman's Pliers with Crimper's

Model #	↔
32948	9.5"/245mm



Knurled Striking Zone



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Industrial brushed finish. C70 special tool steel. Industrial brushed finish.

Insulated Industrial High Leverage Diagonal Cutters

Model #	↔	Cut Cap. Copper AWG
32939	8.0"/200mm	#4



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Industrial brushed finish. C70 special tool steel. Industrial brushed finish.

Insulated Industrial Crimping Pliers

Model #	↔	Crimps AWG	mm2
32945	7.0"/180mm	6-30	0.25-2.5



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Dynamic joint provides 40% easier cuts & significantly longer tool life. C70 special tool steel. Industrial brushed finish.

Insulated Industrial NE Style Lineman's Pliers

Model #	↔
32938	9.5"/245mm

Insulated Pop-Up Bit Sets


1000Volt Rated
10,000 Volt Tested

Precision machined bits for reduced cam-out



Convenient rotating cap

Premium quality tool steel for strength and durability




Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Cushion grip friction hold bit holder, holds 1/4" bits.

14 Piece | Insulated Pop-Up Bit Holder Set

Model #38050

Slotted | 4.5, 5.5, 6.0mm
Phillips | #0, #1, #2, #3
Square | #1, #2, #3
Pozidriv® | #1, #2, #3



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually Tested. Cushion grip friction hold bit holder, holds 1/4" bits.

14 Piece | Insulated Pop-Up Bit Holder Set

Model #38051

Slotted | 4.5, 5.5, 6.0mm
Phillips | #0, #1, #2, #3
Square | #1, #2, #3
TORX® | T15, T20, T25

Insulated Professional Tools



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Individually tested. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

Insulated Stripping Pliers

Model #	↔	Crimps AWG	Ø
10250	6.3"/160mm	20-10	0.81-2.59



Meets EN/IEC, ASTM, VDE, NFPA70E & CSA standards. 1000 volt rated. Made from stainless 420 grade steel.

Insulated Electrician's Shears

Model #	↔
32951	6.3"/160mm

Audible alarm signal is variable for indicating voltage strengths

Visual voltage strength meter for precise voltage location



Voltage Detector 12-1000V AC Rated. Non-Contact Category IV Single-Pole Red LED & audible alarm indicate present voltage (Includes 2 AAA batteries)

Insulated Cat. IV Detector

Model #	↔
25506	6.0"/152mm



Tools designed with soft grip handles for maximum power and control

Insulated EV Essential Tool Kit

1000Volt Rated
10,000 Volt Tested



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

26 Piece | 3/8" Drive Insulated EV Essential Tool Kit

Model #91890

Slotted | 3.5, 4.5, 6.5mm **Phillips** | #1, #2
TORX® | T20, T25, T30
Metric Sockets | 5, 6, 8, 10, 12, 13mm
Extension Bar | 125mm, 250mm
Ratchet | 3/8" Drive / 190mm
Open End Wrenches | 8, 10, 12, 13mm
Tweezers | 8"/200mm Serrated Straight Blunt
Electrician's Knife | 50mm
Long Nose Pliers | 8.0"/160mm
Diagonal Cutters | 8.0"/160mm
Combination Pliers | 8.0"/200mm

*Sockets must be used with insulated ratchets & extensions

Insulated Professional Tools



#30138



#30114

Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. Visible reading scale for easy reading and adjustment. Locking endcap Torque adjuster for easy adjustment. Accuracy +/- 10%. Dual scale reading Ft. lbs. / Nm. 1000 volt rated.

Insulated 3/8" Square Drive Ratcheting Torque Wrench

Model #	Drive	Length	Weight	NM
30114	1/4"	210mm	8.25"	5-25
30138	3/8"	370mm	14.5"	5-50
30152	1/2"	530	21.0"	40-220



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

7 Piece | Insulated 3/8" Drive Bit Socket Set

Model #31890

SAE | 3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

16 Piece | Insulated 3/8" Drive Ratcheting Torque Wrench & Socket Set

Model #30190

SAE Sockets | 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8"

Extension Bar | 125mm, 250mm

Ratcheting Torque | 3/8" Drive Wrench | 5 - 50 Nm

*Sockets must be used with insulated ratchets & extensions



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

16 Piece | Insulated 3/8" Drive Ratcheting Torque Wrench & Socket Set

Model #30192

Metric Sockets | 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20mm

Extension Bar | 125mm, 250mm

Ratcheting Torque | 3/8" Drive Wrench | 5 - 50 Nm

*Sockets must be used with insulated ratchets & extensions



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

16 Piece | Insulated 3/8" Drive Socket Set

Model #31491

SAE | 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"

Metric | 8, 10, 11, 12, 13, 14, 17, 19mm



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

13 Piece | Insulated 1/4" Drive Socket Set

Model #31390

SAE Sockets | 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16"

Extension Bar | 50mm, 100mm

Ratchet | 1/4" Drive



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

13 Piece | Insulated 1/4" Drive Socket Set

Model #31391

Metric Sockets | 5, 6, 7, 8, 9, 10, 11, 12, 13, 14mm

Extension Bar | 50mm, 100mm

Ratchet | 1/4" Drive

Insulated Professional Tools



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

24 Piece | Insulated 3/8" Drive Socket Set

Model #31592

Slotted | 3.5, 4.5, 6.5mm **Phillips** | #1, #2, #3
Metric Sockets | 6, 7, 8, 9, 10, 11, 12, 13, 14, 17, 19mm
Extension Bar | 125mm, 250mm
Ratchet | 3/8" Drive / 190mm
Electrician's Knife | 50mm
Long Nose Pliers | 6.3"/160mm
Diagonal Cutters | 6.3"/160mm
Combination Pliers | 8.0"/200mm

*Sockets must be used with insulated ratchets & extensions



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

24 Piece | Insulated 3/8" Drive Socket Set

Model #31495

Slotted | 3.5, 4.5, 6.5mm **Phillips** | #1, #2, #3
SAE Sockets | 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"
Extension Bar | 125mm, 250mm
Ratchet | 3/8" Drive / 190mm
Electrician's Knife | 50mm
Long Nose Pliers | 6.3"/160mm
Diagonal Cutters | 6.3"/160mm
Combination Pliers | 8.0"/200mm

*Sockets must be used with insulated ratchets & extensions



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

10 Piece | Insulated 3/8" Drive T-handle & Socket Set

Model #31496

SAE Sockets | 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"
Extension Bar | 125mm
T-handle | 3/8" Drive



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

10 Piece | Insulated 3/8" Drive Socket Set

Model #31493

SAE Sockets | 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"
Extension Bar | 125mm
Ratchet | 3/8" Drive / 190mm OAL

*Sockets must be used with insulated ratchets & extensions

10 Piece | Insulated 3/8" Drive Socket Set

Model #31590

Metric Sockets | 8, 10, 11, 12, 13, 14, 17, 19mm
Extension Bar | 125mm
Ratchet | 3/8" Drive / 190mm OAL

*Sockets must be used with insulated ratchets & extensions



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. Socket release button. Thumb lever for rapid reverse. 1000 volt rated.

Insulated Ratchets

Model #	Drive	Length	Width
12851	1/4"	140mm	5.5"
12852	3/8"	190mm	7.5"
12853	1/2"	260mm	10.2"



Certified to EN ISO 6789, BS EN 26789, ASME B107.14M, EN/IEC 60900. CV steel, forged, oil-hardened sockets. 1000 volt rated.

14 Piece | Insulated 1/2" Drive Socket Set

Model #31694

Metric Sockets | 8, 9, 10, 11, 12, 13, 14, 17, 19, 22, 24mm
Extension Bar | 125mm, 250mm
Ratchet | 1/2" Drive / 190mm

*Sockets must be used with insulated ratchets & extensions



14 Piece | Insulated 1/2" Drive Socket Set

Model #31792

SAE Sockets | 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1"
Extension Bar | 125mm, 250mm
Ratchet | 1/2" Drive / 190mm

*Sockets must be used with insulated ratchets & extensions

Insulated Professional Tools



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. Etched on scale for pre-setting size. Slip guard handle for added protection. 1000 volt rated.

Insulated | Adjustable Wrenches

Model #			Cap. Opening
76208	8.0"	200mm	1"
76210	10"	250mm	1-1/4"
76212	12"	300mm	1-1/2"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

8 Piece | Insulated Offset Ring Wrench Set

Model #21096

SAE | 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

8 Piece | Insulated Open End Wrench Set

Model #20192

SAE | 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. Etched on scale for pre-setting size. Slip guard handle for added protection. 1000 volt rated.

3 Piece | Insulated Adjustable Wrench Set

Model #76290

Adjustable Wrenches | 8", 10", 12"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

16 Piece | Insulated Offset Ring Wrench Set

Model #21094

SAE | 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/4"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

14 Piece | Insulated Open End Wrench Set

Model #20190

SAE | 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

6 Piece | Insulated Ratchet Wrench Set

Model #21391

SAE | 3/8, 7/16, 1/2, 9/16, 5/8, 3/4"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

7 Piece | Insulated Ratchet Wrench Set

Model #21290

Metric | 8, 10, 12, 13, 14, 17, 19mm



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

15 Piece | Insulated Open End Wrench Set

Model #20091

Metric | 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 19, 22, 24mm

Insulated Professional Tools



Wiha Insulated T-handle
Blade CVM tool steel, hardened to average 58/60RC

Insulation Molded directly onto blade for permanent bonding

Insulation Test Standards:
Insulation to ASTM, F-1505,
EN/IEC 60900 and CSA
standards

Insulation applied
directly onto blade
for permanent
bonding



 **Made in Germany**



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

8 Piece | Insulated L-key Hex Set

Model #13690

SAE | 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

12 Piece | Insulated L-key Hex Set

Model #13694

SAE | 1/16, 5/64, 3/32, 7/64, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

6 Piece | Insulated T-handle Hex Set

Model #33490

SAE | 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

7 Piece | Insulated L-key Hex Set

Model #13691

Metric | 3, 4, 5, 6, 8, 10, 12mm



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

10 Piece | Insulated L-key Hex Set

Model #13693

Metric | 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10, 12mm



Insulated to EN/IEC 60900:2004, ASTM F1505, CSA Standards. 1000 volt rated.

5 Piece | Insulated T-handle Hex Set

Model #33478

Metric | 4, 5, 6, 8, 10mm



MicroFinish® Extra Heavy Duty Screwdriver Sets



Wiha MicroFinish Handle

It won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. Get maximum force & comfort with dry, oily or wet hands.



Premium quality tool steel for strength and durability. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque.

5 Piece | MicroFinish® Extra Heavy Duty Screwdriver Set

Model #53390

Slotted | 5.5, 6.5, 8.0mm

Phillips | #1, #2



Premium quality tool steel for strength and durability. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque.

8 Piece | MicroFinish® Extra Heavy Duty Screwdriver Set

Model #53398

Slotted | 4.5*, 5.5, 6.5, 8.0, 10.0mm

Phillips | #1, #2, #3

*No hex bolster

SoftFinish® Extra Heavy Duty Screwdriver Sets



Wiha Extra Heavy Duty Handle

The Extra Heavy Design features a metal striking cap for hammer impact resistance and hex bolstered blades for wrenching function and torque strength.



Premium quality tool steel for strength and durability. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque.

2 Piece | SoftFinish® Extra Heavy Duty Screwdriver Set

Model #53082

Slotted | 8.0mm Phillips | #2



Premium quality tool steel for strength and durability. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque.

5 Piece | SoftFinish® Extra Heavy Duty Screwdriver Set

Model #53095

Slotted | 6.5, 8.0, 10.0mm

Phillips | #1, #2



Premium quality tool steel for strength and durability. Hex blade extending through handle with steel striking cap. Hex bolster for additional torque.

5 Piece | SoftFinish® Extra Heavy Duty Screwdriver Set

Model #53075

Slotted | 4.5, 5.5, 6.5mm

Phillips | #1, #2



7 Piece | SoftFinish® Extra Heavy Duty Screwdriver Set

Model #53097

Slotted | 5.5, 6.5, 8.0, 10.0mm

Phillips | #1, #2, #3



10 Piece | SoftFinish® Extra Heavy Duty Screwdriver Set

Model #53099

Slotted | 3.5, 4.5, 5.5, 6.5, 8.0, 10.0, 12.0mm

Phillips | #1, #2, #3

SoftFinish® Cushion Grip Screwdriver Sets



Designed with an SoftFinish® cushion grip for maximum power and comfort. Premium quality tool steel for strength and durability.

2 Piece | SoftFinish® Screwdriver Set

Model #30279

Slotted | 6.5mm Phillips | #2



Designed with an SoftFinish® cushion grip for maximum power and comfort. Premium quality tool steel for strength and durability.

8 Piece | SoftFinish® Screwdriver Set

Model #30298

Slotted | 3.0, 4.0, 5.5, 6.5, 8.0mm

Phillips | #1, #2, #3



Designed with an SoftFinish® cushion grip for maximum power and comfort. Premium quality tool steel for strength and durability.

6 Piece | SoftFinish® Screwdriver Set

Model #36291

TORX® | T6, T7, T8, T9, T10, T15



Designed with an SoftFinish® cushion grip for maximum power and comfort. Premium quality tool steel for strength and durability.

5 Piece | SoftFinish® Screwdriver Set

Model #30277

Slotted | 4.5, 6.5, 8.0mm Phillips | #1, #2



12 Piece | SoftFinish® Screwdriver Set

Model #30297

Slotted | 3.0, 4.0, 5.5, 6.5, 8.0, 10.0mm

Stubby | SLT 6.5mm & PH #2

Phillips | #0, #1, #2, #3



Designed with an SoftFinish® cushion grip for maximum power and comfort. Premium quality tool steel for strength and durability.

8 Piece | SoftFinish® Screwdriver Set

Model #36294

TORX® | T6, T8, T10, T15, T20, T25, T27, T30



7 Piece | SoftFinish® Screwdriver Set

Model #30278

Slotted | 3.5, 4.0, 5.5, 6.5mm

Phillips | #1, #2, #3



14 Piece | SoftFinish® Screwdriver Set

Model #30284

Slotted | 3.0, 4.5 x 80mm, 3.0, 6.5 x 100mm, 4.5, 5.5 x 125mm, 6.5 x 150mm

Stubby | SLT 6.5mm & PH #2 x 25mm

Phillips | #0 x 60mm, #1 x 80mm, #2 x 100mm, #2 x 200mm, #2 x 300mm



Designed with an SoftFinish® cushion grip for maximum power and comfort. Premium quality tool steel for strength and durability.

12 Piece | SoftFinish® Screwdriver Set

Model #36267

TORX® | T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40

SoftFinish® Cushion Grip Screwdriver Sets

A standard for professional quality. Each handle is sized proportionately for powerful torque and less fatigue.



Designed with a SoftFinish® cushion grip for maximum power and comfort. Premium quality tool steel for strength and durability.

20 Piece | SoftFinish® Screwdriver Set

Model #30299

Slotted | 3.0, 4.0, 5.5, 6.5, 8.0mm
Phillips | #0, #1, #2 **Square** | #1, #2, #3
TORX® | T6, T8, T10, T15, T20, T25, T30
Pozidriv® | #1, #2

SoftFinish® Stubby Multi-Bit Set



Double end Ultra Driver bits fit stubby handle




14inOne | SoftFinish® Stubby Multi-Bit Set

Model #30299

Slotted | 3.0+4.5, 4.0+6.0, 5.5+6.5mm
Phillips | #0+#3 #1+#2
Square | #0+#3 #1+#2

SoftFinish® Multi-Driver Screwdriver



On the clock



Double-ended bits phosphate finish for corrosion protection and surface resilience

Premium quality tool steel engineered for strength and durability and feature exact fit precision machined tips for reduce cam-out of fastener heads.

6inOne | SoftFinish® Multi-Driver Screwdriver

Model #77890

Slotted | 3/16, 1/4" **Phillips** | #1, #2
Nut Driver | 1/4", 5/16"




Reams 1/2", 3/4", 1" conduit

Reams both the inside and outside edges for consistent efficiency. Shrouded slotted screwdriver tip for fastener-slip prevention.

5 Piece | Conduit & 6inOne SoftFinish® Multi-Driver

Model #77892

Slotted | 3/16, 1/4" **Phillips** | #1, #2
Nut Driver | 1/4", 5/16"



Off the clock



Premium quality tool steel engineered for strength and durability and feature exact fit precision machined tips for reduce cam-out of fastener heads.

11inOne | SoftFinish® Multi-Driver Screwdriver

Model #77891

Slotted | 3/16, 1/4" **Phillips** | #1, #2
Square | #1, #2 **TORX®** | T20, T25
Nut Driver | 1/4", 5/16, 3/8"



Reams 1/2", 3/4", 1" conduit for smooth edges and proper fit

Drive-Loc VI Adjustable Locking Blade Sets

SoftFinish® and ESD Safe grip



Blade length can be adjusted from 1.7 to 4.7" In 1/8" increments

Adjust interchangeable blades from 40 to 120mm

Drive-Loc mechanism guarantees a secure hold & rapid blade exchange



Drive-Loc mechanism guarantees a secure hold & rapid blade exchange. SoftFinish® cushion grip handle for comfort and control.

15 Piece | SoftFinish® Drive-Loc VI Blade Set

Model #28189

Slotted | 3.5+4.5, 5.5+6.5mm

Phillips | #1+#2

Security TORX® | T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s

SAE Hex | 3/32+7/64, 1/8+9/64, 5/32+3/16"

Metric Hex | 2.0+2.5, 3.0+4.0, 5.0+6.0mm

SoftFinish® Handle | Holds Drive-Loc VI blades



Drive-Loc mechanism guarantees a secure hold & rapid blade exchange. SoftFinish® cushion grip handle for comfort and control.

32 Piece | ESD Safe Drive-Loc VI Blade Set

Model #28187

Slotted | 3.5+4.5, 5.5+6.5mm

Slotted/Phillips | 3.0+#0, 4.0+#1, 6.0+#2

Square | #1+#2

Security TORX® | T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s

SAE Hex | 3/32+7/64, 1/8+9/64, 5/32+3/16"

Metric Hex | 2.0+2.5, 3.0+4.0, 5.0+6.0mm

SAE Nut Drvrs | 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"

MM Nut Drvrs | 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0mm

ESD Safe Handle | Holds Drive-Loc VI blades



32 Piece | SoftFinish® Drive-Loc VI Blade Set

Model #28188

Slotted | 3.5+4.5, 5.5+6.5mm Square | #1+#2

Slotted/Phillips | 3.0+#0, 4.0+#1, 6.0+#2

Security TORX® | T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s

SAE Hex | 3/32+7/64, 1/8+9/64, 5/32+3/16"

Metric Hex | 2.0+2.5, 3.0+4.0, 5.0+6.0mm

SAE Nut Drvrs | 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"

MM Nut Drvrs | 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0mm

SoftFinish® Handle | Holds Drive-Loc VI blades



Drive-Loc mechanism guarantees a secure hold & rapid blade exchange. SoftFinish® cushion grip handle for comfort and control.

8 Piece | SoftFinish® Drive-Loc VI Blade Set

Model #28196

SAE Nut Drivers | 3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2"

SoftFinish® Handle | Holds Drive-Loc VI blades

ESD Safe SoftFinish® Cushion Grip Screwdrivers

Wiha Precision ESD Static Dissipative Screwdrivers meet the requirements for tools used in static sensitive areas



DIN EN 61340-5-1/61340-5-2 Round blade, high alloy CVM steel, hardened, hard chromed. Dissipative SoftFinish® cushion grip handle, multi-component, ESD Safe. (10⁶-10⁹ Ohm).

6 Piece | ESD Safe SoftFinish® Screwdriver Set

Model #30292

Slotted | *3.0, *4.0, *5.5mm

Phillips | #0, #1, #2

*Cabinet Tips

ESD Safe SoftFinish® TorqueControl Handles

ESD TorqueVario handle has unique serial number and certificate of calibration



ESD Safe Dissipative SoftFinish® cushion grip handle, multi-component. Newton meter with window scale. +/-6% accuracy. Includes Certificate

ESD Safe TorqueVario-S

Model #	Range Nm	Length	Weight
28500	.04 - .46	124mm	4.875"



ESD Safe Dissipative SoftFinish® cushion grip handle, multi-component. Newton meter with window scale. +/-6% accuracy. Includes Certificate

ESD Safe TorqueVario-S

Model #	Range In/oz.	Length	Weight
28522	15-80 In/oz.	122mm	4.8"




Shaft high alloy Chrome-vanadium-molybdenum steel, corrosion protected. (Not for use in Insulated handles)

1/4" Drive | ESD Safe Bit Holder Adapter For 1/4" Drive Bits

Model #	Length	Weight
28882	1/4 162mm	4.0mm


 **Made in Germany**
SoftFinish® cushion grip handles for maximum torque

SoftFinish® cushion grip for maximum torque

Precision ground driver tips for exact fit


+/-6% accuracy. SoftFinish® cushion grip handles for comfort and control. Exact fit machined tips for reduced cam-out. Includes Certificate of calibration.

53 Piece | TorqueVario-S 1/4" Bit Set

Model #28595
Slotted | 4.5, 5.5, 6.5, 8.0mm

Phillips | #0, #1, #2, #3 **Square** | #1, #2, #3

TORX® | T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

SAE Hex | 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

Pozidriv® | #0, #1, #2, #3 **Torq Set** | #4, #5, #6, #8

Tri-Wing | #0, #1, #2, #3, #4

Torque Handle | 10-50 in/lbs. with Torque adj. tool

Bit Holder | Holds 1/4" Bits


59 Piece | TorqueVario-S 1/4" Bit & Socket Set

Model #28589
Slotted | 4.5, 5.5, 6.0mm **Phillips** | #0, #1, #2

Square | #1, #2, #3 **Pozidriv®** | #1, #2

TORX® | T5, T6, T7, T8, T9, T10, T15, T20, T25, T30

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm

SAE Sockets | 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"

Metric Sockets | 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm

3 Torque Handle | 15-80 in/oz., 5-10 & 10-50 in/lbs.

Bit Holder | Holds 1/4" Bits

Adapter | 1/4" Hex to 1/4" Square

TorqueVario-STplus T-handle



Meets EN ISO 6789, BS EN 26789, ASME B107.14M Standards. +/-6% accuracy. T-handle grip handle for good power transfer. Includes Calibration Certificate.

Adj. TorqueVario STPlus T-handle

Model #	Nm	In/lbs.	mm x mm
28940	5-14	44.3-123.9	56 X 120

*(1 Nm 8.8507) (Scale is shown in Nm only)



TORX® tip blades for TorqueFix T-handle on 6mm Hex shafts. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

TORX® Interchangeable Blades for TorqueFix T-Handles

Model #	Icon	Length	Width
28903	T15	130mm	6.0mm
28904	T20	130mm	6.0mm
28905	T25	130mm	6.0mm
28906	T27	130mm	6.0mm
28907	T30	130mm	6.0mm
28908	T40	130mm	6.0mm



TORXPlus® tip blades for TorqueFix T-handle on 6mm Hex shafts. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

TORXPlus® Interchangeable Blades for TorqueFix T-Handles

Model #	Icon	Length	Width
28910	IP15	130mm	6.0mm
28911	IP20	130mm	6.0mm
28912	IP25	130mm	6.0mm
28913	IP27	130mm	6.0mm
28914	IP30	130mm	6.0mm



Hex Metric tip blades for TorqueFix T-handle on 6mm Hex shafts. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Hex Metric Interchangeable Blades for TorqueFix T-Handles

Model #	Icon	Length	Width
28916	3.0	130mm	6.0mm
28917	4.0	130mm	6.0mm
28918	5.0	130mm	6.0mm
28919	6.0	130mm	6.0mm

Pre-Set Torque Handles

- Audible Click At Torque
- Replaceable Blades
- +/- 10% Repeatability
- Improve Productivity
- Reduces Waste
- Controls Costs
- Save Time!

Torque accuracy of +/- 10% to 5000 cycles



Each tool factory preset

SoftFinish® Pre-Set Torque Screwdrivers



Torque value pre-set. +/-10% accuracy. SoftFinish® cushion grip handles for good power transfer.

Pre-Set Torque Screwdrivers

Model #	Pre-Set In/lbs.	Nm	Length	Bit Size
29205	4.4	0.5	130mm	5.1"
29209	8.0	0.9	130mm	5.1"
29211	9.7	1.1	130mm	5.1"
29225	22.1	2.5	130mm	5.1"

* No Calibration Certificates



Shaft high alloy Chrome-vanadium-molybdenum steel, corrosion protected. (Not for use in Insulated handles)

1/4" Drive I Bit Holder Adapter

Model #	Bit Size	Length	Bit Size
28581	1/4"	149mm	4.0mm



For 1/4" drive sockets. Shaft high alloy Chrome-vanadium-molybdenum steel, corrosion protected. (Not for use in Insulated handles)

1/4" Drive I Square Drive Adapter

Model #	Bit Size	Length	Bit Size
28582	1/4"	145mm	4.0mm



Shaft high alloy Chrome-vanadium-molybdenum steel, corrosion protected. (Not for use in Insulated handles)

Bit Holder Adapter For 4mm MicroBits

Model #	Bit Size	Length	Bit Size
28583	4.0	149mm	4.0mm

TorqueControl Screwdrivers

Made in Germany


TorqueFix factory preset torque
TorqueVario adjustable torque drivers

molded cushion grip two component handles allow for maximum achievable torque to be reached with comfort

Precise repeatability!

All TorqueFix & TorqueVario tools are tested and comply with:

- EN ISO 6789
- BS EN 26789
- ASME B107.14M



Each tool has unique serial number and certificate of calibration

SoftFinish® TorqueControl Handles



Meets EN ISO 6789, BS EN 26789, ASME B107.14M standards. +/-6% accuracy. Light and compact SoftFinish® cushion grip handles for comfort and control. Audible & perceptible click when the torque setting has been attained, automatically resets for next torque cycle. Includes certificate of calibration.

TorqueFix Handle Fixed torque value pre-set

Model #	oz.	lbs.	Nm	Length	Bit Size
28503	80	5	0.56	112mm	4.4"
28515	400	25	2.82	126mm	4.9"



Meets EN ISO 6789, BS EN 26789, ASME B107.14M standards. +/-6% accuracy. Light and compact SoftFinish® cushion grip handles for comfort and control. Audible & perceptible click when the torque setting has been attained, automatically resets for next torque cycle. Includes certificate of calibration.

TorqueVario-S Handle in Newton Meter Scale

Model #	Nm	Increments	Length	Bit Size
28550*	0.1-0.6	0.5 Nm	127mm	5.0"
28551	0.4-1.0	0.5 Nm	127mm	5.0"
28552	0.5-2.0	.10 Nm	131mm	5.2"
28553	0.8-5.0	.20 Nm	138mm	5.4"
28655	2.0-7.0	.25 NM	142MM	5.6"

* +/- 10% (#28550 This unit only)



1/4" Bit Holder

Meets EN ISO 6789, BS EN 26789, ASME B107.14M standards. +/-6% accuracy. Light and compact SoftFinish® cushion grip handles for comfort and control. Audible & perceptible click when the torque setting has been attained, automatically resets for next torque cycle. Includes certificate of calibration.

TorqueVario-S Handle with 1/4" Bit Holder

Model #	In/lbs.	Increments	Length	Bit Size
28410*	15-80(in/oz.)	2.5(in/oz.)	127mm	5.0"
28412	10-50	.5 in/lbs.	138mm	5.4"
28413	5-18	.5 in/lbs.	131mm	5.2"

* +/- 10% (#28410 This unit only)



4mm Bit Holder

Meets EN ISO 6789, BS EN 26789, ASME B107.14M standards. +/-6% accuracy. Light and compact SoftFinish® cushion grip handles for comfort and control. Audible & perceptible click when the torque setting has been attained, automatically resets for next torque cycle. Includes certificate of calibration.

TorqueVario-S Handle with 4mm Micro Bit Holder

Model #	In/lbs.	Increments	Length	Bit Size
28501*	15-80(in/oz.)	2.5(in/oz.)	127mm	5.0"
28502	5-10	.5 in/lbs.	127mm	5.0"
28404	5-18	1 in/lbs.	131mm	5.2"
28506	10-50	2 in/lbs.	138mm	5.4"

* +/- 10% (#28501 This unit only)

Torque Control Screwdriver Blades



TORX® tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

TORX® Interchangeable Blades for TorqueFix & TorqueVario Handles

Model #				Max.
28561	T5	175mm	4.0mm	Nm 0.4
28562	T6	175mm	4.0mm	Nm 0.6
28563	T7	175mm	4.0mm	Nm 0.9
28564	T8	175mm	4.0mm	Nm 1.3
28565	T9	175mm	4.0mm	Nm 2.5
28566	T10	175mm	4.0mm	Nm 3.8
28567	T15	175mm	4.0mm	Nm 5.5
28568	T20	175mm	4.0mm	Nm 8.0
28569	T25	175mm	4.0mm	Nm 8.0



TORXPlus® tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

TORXPlus® Interchangeable Blades for TorqueFix & TorqueVario Handles

Model #				Max.
28571	IP5	175mm	4.0mm	Nm 0.5
28572	IP6	175mm	4.0mm	Nm 0.8
28573	IP7	175mm	4.0mm	Nm 1.3
28574	IP8	175mm	4.0mm	Nm 2.0
28575	IP9	175mm	4.0mm	Nm 3.0
28576	IP10	175mm	4.0mm	Nm 4.5
28577	IP15	175mm	4.0mm	Nm 6.6
28578	IP20	175mm	4.0mm	Nm 8.0
28579	IP25	175mm	4.0mm	Nm 8.0



Slotted tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Slotted Interchangeable Blades for TorqueFix & TorqueVario Handles

Model #				Max.
28534	1.5	175mm	4.0mm	Nm 0.15
28535	2.0	175mm	4.0mm	Nm 0.4
28536	2.5	175mm	4.0mm	Nm 0.4
28537	3.0	175mm	4.0mm	Nm 0.6
28538	3.5	175mm	4.0mm	Nm 1.1
28539	4.0	175mm	4.0mm	Nm 2.5



MagicSpring TORX® tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

MagicSpring TORX® Interchangeable Blades For TorqueFix/TorqueVario Handles

Model #				Max.
28512	T6	175mm	4.0mm	Nm 0.6
28527	T7	175mm	4.0mm	Nm 0.9
28528	T8	175mm	4.0mm	Nm 1.3
28529	T9	175mm	4.0mm	Nm 2.5
28530	T10	175mm	4.0mm	Nm 3.8
28531	T15	175mm	4.0mm	Nm 5.5



MagicRing TORXPlus® tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

MagicRing TORXPlus® Interchangeable Blades for TorqueFix & TorqueVario Handles

Model #				Max.
28611	IP6	175mm	4.0mm	Nm 0.8
28612	IP7	175mm	4.0mm	Nm 1.3
28613	IP8	175mm	4.0mm	Nm 2.0
28614	IP9	175mm	4.0mm	Nm 3.0
28616	IP10	175mm	4.0mm	Nm 4.5
28617	IP15	175mm	4.0mm	Nm 6.6
28618	IP20	175mm	4.0mm	Nm 8.0
28619	IP25	175mm	4.0mm	Nm 8.0



Phillips tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Phillips Interchangeable Blades for TorqueFix & TorqueVario Handles

Model #				Max.
28540	000	175mm	4.0mm	Nm 0.4
28541	00	175mm	4.0mm	Nm 0.4
28542	0	175mm	4.0mm	Nm 0.9
28543	1	175mm	4.0mm	Nm 3.8
28544	2	175mm	4.0mm	Nm 5.5



Hex Inch tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Hex Inch Interchangeable Blades for TorqueFix & TorqueVario Handles

Model #				Max.
28555	.050	175mm	4.0mm	Nm 0.4
28556	1/16	175mm	4.0mm	Nm 0.9
28557	5/64	175mm	4.0mm	Nm 1.8
28558	3/32	175mm	4.0mm	Nm 1.8
28559	7/64	175mm	4.0mm	Nm 3.8
28560	1/8	175mm	4.0mm	Nm 5.5
28587	9/64	175mm	4.0mm	Nm 8.0
28588	5/32	175mm	4.0mm	Nm 8.0



Hex Metric tip blade on narrow 5/32 Hex shaft. High alloy Chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Hex Metric Interchangeable Blades for TorqueFix & TorqueVario Handles

Model #				Max.
28545	1.5	175mm	4.0mm	Nm 0.9
28546	2.0	175mm	4.0mm	Nm 1.8
28547	2.5	175mm	4.0mm	Nm 3.8
28548	3.0	175mm	4.0mm	Nm 5.5
28549	4.0	175mm	4.0mm	Nm 8.0



TorqueVario drivers have variable torque settings that can be adjusted in increments using an adjustment tool



Torque Control Blades are designed to be used with Wiha TorqueVario, TorqueFix & iTorque handles

*None of the blades featured on this page will function in a TorqueVario Insulated Handle

PRECISION SCREWDRIVERS

PicoFinish® & Classic Precision Drivers - the tightest fitting precision-machined driver tips from the company that set the standard for precision

When it comes to working on small components and modern electronics, using the best precision screwdriver is essential



Precision ground tips for exact fit



Tapered handle for rapid rotation



Hex profile finger grip for precise control

Classic Precision Screwdriver Sets



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

6 Piece | Precision Screwdriver Set

Model #26090

Slotted | 1.5, 2.0 x 40mm
2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

8 Piece | Precision Screwdriver Set

Model #26099

Slotted | 1.0, 1.2, 1.5, 2.0 x 40mm
2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

4 Piece | Precision Screwdriver Set

Model #26194

Phillips | #000, #00 x 40mm, #0 x 50mm,
#1 x 60mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

7 Piece | Precision Screwdriver Set

Model #26092

Slotted | 2.5 x 50mm, 2.5, 3.0, 4.0 x 100mm
3.0, 4.0 x 150mm **Phillips** | 0 x 75mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

7 Piece | Precision Screwdriver Set

Model #26197

Slotted | 1.5 x 40mm, 2.0, 2.5 x 50mm, 3.0 x 60mm
Phillips | #00 x 40mm, #0 x 75mm, #1 x 60mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

8 Piece | Precision Screwdriver Set

Model #26199

Slotted | 1.0, 2.0 x 40mm, 3.0 x 50mm, 4.0 x 60mm
Phillips | #000, #00 x 40mm, #0 x 50mm, #1 x 60mm

Precision screwdriver with rotating cap for precise turning and control with fingertip. Smooth operation SoftGrip pliers anti-slip handles for safe gripping. Natural brushed finish.

8 Piece | Precision Screwdriver & Pliers Set

Model #26190

Industrial Long Nose Pliers | 6.3"/160mm
Slotted | 1.5 x 40mm, 2.0, 2.5 x 50mm, 3.0 x 60mm
Phillips | 0 x 50mm, 1 x 60mm

Rotating cap
for precise turning and control with fingertip

Precision handle
high quality plastic, cadmium free

Molded on tapered handle
allows rapid rotation

High performance blades
CVM steel,
Hard chrome finished

Tip
precision ground for exact fit, hard chromed non-slip surface



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

5 Piece | Precision Extra Long Screwdriver Set

Model #26192

Slotted | 2.5, 3.0, 4.0 x 150mm
Phillips | #0, #1 x 150mm



ESD Safe Dissipative precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out. ESD Safe. (10⁶-10⁹ Ohm). ESD standard IEC 61340-5-1

7 Piece | ESD Safe Precision Extra Long Screwdriver Set

Model #27393

Slotted | 2.0, 2.5, 3.0, 3.5, 4.0mm
Phillips | #0, #1



Classic Precision Screwdriver Sets



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

8 Piece | Precision Screwdriver Set

Model #26791

TORX® | T1, T2, T3, T4, T5, T6, T7, T8



Precision screwdriver with rotating cap for precise turning and control with fingertip. Angle entry up to 30°. Precision ground exact fit tips for reduced cam-out.

5 Piece | Precision Ball End Hex Screwdriver Set

Model #26491

Ball End Hex Metric | 1.3 x 40mm, 1.5, 2.0 x 50mm & 2.5, 3.0 x 60mm



Precision screwdriver with rotating cap for precise turning and control with fingertip.

8 Piece | Precision Nut Driver Set

Model #26590

Metric Nut Drivers | 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5, 6.0mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

8 Piece | Precision Screwdriver Set

Model #26799

TORX® | T3, T4, T5, T6, T7, T8 x 40mm, T9, T10 x 50mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Angle entry up to 30°. Precision ground exact fit tips for reduced cam-out.

8 Piece | Precision Ball End Hex Screwdriver Set

Model #26391

Ball End Hex SAE | .028, .035, .050 x 1.6" 1/16, 5/64 x 2.0" & 3/32, 7/64, 1/8 x 2.4"



Precision screwdriver with rotating cap for precise turning and control with fingertip.

7 Piece | Precision Nut Driver Set

Model #26592

Metric Nut Drivers | 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

7 Piece | Precision Hex Screwdriver Set

Model #26390

Metric Hex | .7, .9, 1.3 x 40mm & 1.5, 2.0 x 50mm 2.5, 3.0 x 60mm



Precision screwdriver with rotating cap for precise turning and control with fingertip.

8 Piece | Precision Nut Driver Set

Model #26591

SAE Nut Drivers | 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Classic Precision Screwdriver Sets



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

51 Piece | Precision Tool Tray Set

Model #92191

Slotted | .8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

Phillips | #000, #00, #0, #1

TORX® | T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

SAE Hex | .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Metric Hex | 1.27, 1.5, 2.0, 2.5, 3.0, 4.0mm

Metric Nut Drivers | 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm

26810 | Chip Lifter



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

50 Piece | Precision Master Tech Bench Top Set

Model #92189

Slotted | 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

Phillips | #000, #00, #0, #1

Pentalobe | PL1, PL2, PL3, PL4

TORX® | T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

SAE Hex | .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Metric Hex | 1.27, 1.5, 2.0, 2.5, 3.0mm

Metric Nut Drivers | 1.5, 1.8, 2.0, 2.5, 3.0, 3.5,

4.0, 4.5, 5.0, 5.5mm

26810 | Chip Lifter



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

50 Piece | Precision Master Tech Bench Top Set

Model #92190

Slotted | .8, 1.0, 1.2, 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

Phillips | #000, #00, #0, #1

TORX® | T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

SAE Hex | .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Metric Hex | 1.27, 1.5, 2.0, 2.5, 3.0mm

Metric Nut Drivers | 1.5, 1.8, 2.0, 2.5, 3.0, 3.5,

4.0, 4.5, 5.0, 5.5mm

26810 | Chip Lifter

Magnetizer/Demagnetizer

Uses 2 C8 industrial permanent magnets



(+) to Magnetize

(-) to Demagnetize

Magnetize or Demagnetize tools and small parts instantly

To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools.

To magnetize, lead tool slowly through the (+) opening. To demagnetize guide tool slowly through the (-) opening.

Magnetizer/Demagnetizer

Model #	Dimensions
40010	2.1" x 2.0" x 1.1"

(Parts under 1" Length or 1/8" Diameter may not demagnetize)

Tool Pouches



Heavy duty nylon. Keeps tools & accessories organized.

Cordura® General Purpose Zipper Bag

Model #	Dimensions
91473	9.75" x 7.25" x 3.0"



Holds 10 precision tools up to 170mm in length

Roll-up Tool Pouch

Model #	Dimensions
91472	14" x 7.5"

The Comfortable Precision Screwdriver



Soft grip multi-component handle with rotating cap for maximum user comfort and precise control



ESD Standard
IEC 61340-5-1

Surface resistance
of handles is
 $10^6 - 10^9$ Ohms



ESD standard IEC 61340-5-1

Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

50 Piece | PicoFinish® Precision ESD Safe Bench Top Set

Model #92093

Slotted | .8, 1.0, 1.2, 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

Phillips | #000, #00, #0, #1


TORX® | T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

SAE Hex | 1/16, 3/32, 7/64, 1/8"

Metric Nut Drivers | 1.5, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm

SAE Nut Drivers | 1/8, 5/32, 3/16, 1/4"

Chip Lifter | 3.5mm x 50mm



In storage pouch

Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

8 Piece | PicoFinish® Precision Screwdriver Set

Model #26193

Slotted | 1.0, 1.5, 2.0 x 40mm & 2.5 x 50mm
3.5 x 60mm

Phillips | #00 x 40mm, #0 x 50mm, #1 x 60mm



ESD Safe Dissipative precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out. ESD Safe. (10^6-10^9 Ohm). ESD standard IEC 61340-5-1

7 Piece | ESD Safe PicoFinish® Precision Screwdriver Set

Model #27392

Slotted | 1.5, 2.0, 2.5, 3.5mm

Phillips | #00, #0, #1



Precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out.

5 Piece | PicoFinish® Precision Screwdriver Set

Model #26195

Slotted | 1.5, 2.5, 3.5mm

Phillips | #0, #1

No Pouch - In clamshell



ESD Safe Dissipative precision screwdriver with rotating cap for precise turning and control with fingertip. Precision ground exact fit tips for reduced cam-out. ESD Safe. (10^6-10^9 Ohm). ESD standard IEC 61340-5-1

8 Piece | ESD Safe PicoFinish® Precision Screwdriver Set

Model #27396

Slotted | 1.5, 2.0, 2.5, 3.0mm

Phillips | #000, #00, #0, #1



SYSTEM 4 Micro Bit Sets



4mm Precision ground exact fit tips for reduced cam-out. ESD Safe Dissipative precision screwdriver with rotating cap for precise turning and control with fingertip.

68 Piece | SYSTEM 4 Master Tech Micro Bit Set

Model #75971

Slotted | 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
Phillips | #000, #00, #0, #1, #2
Pentalobe | PL1, PL2, PL3, PL4, PL5, PL6
TORX® | T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
SAE Hex | .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
Metric Hex | 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
Metric Nut Drivers | 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
ESD Safe Precision Handle | 4mm
Micro Bit Storage Handle | Holds 4mm Micro Bits
Bit Extension | 100mm
Adapter | 1/4" to 4mm



4mm Precision ground exact fit tips for reduced cam-out. ESD Safe Dissipative precision screwdriver with rotating cap for precise turning and control with fingertip.

68 Piece | SYSTEM 4 Master Tech Micro Bit Set

Model #75965

Slotted | 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
Phillips | #000, #00, #0, #1
Pentalobe | PL1, PL2, PL3, PL4, PL5, PL6
TORX® | T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
Metric Hex | .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
Metric Nut Drivers | 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
SAE Nut Drivers | 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
ESD Safe Precision Handle | 4mm
1/4" Mini Ratchet | 72 tooth
Bit Extension | 100mm
Adapter | 1/4" to 4mm



4mm Precision ground exact fit tips for reduced cam-out. ESD Safe PicoFinish® screwdriver with rotating cap for precise turning and control with fingertip.

39 Piece | PicoFinish® Master Tech Micro Bit Set

Model #75980

Slotted | 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
Phillips | #000, #00, #0, #1, #2
Pentalobe | PL1, PL2, PL3, PL4, PL5, PL6
TORX® | T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
Metric Hex | 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
ESD Safe PicoFinish® Precision Handle | 4mm
Bit Extension | 100mm



4mm Precision ground exact fit tips for reduced cam-out. PicoFinish® screwdriver with rotating cap for precise turning and control with fingertip.

36 Piece | GoBox™ PicoFinish® Precision Micro Bit Set

Model #75958

Slotted | 0.8, 1.5, 2.0, 2.5, 3.0, 3.5mm
Phillips | #000, #00 (2), #0, #1
Pentalobe | PL1, PL2, PL3, PL4, PL5, PL6
TORX® | T2, T3, T4, T6, T8
SAE Hex | 1/16, 5/32, 5/64, 1/8"
Metric Hex | .9, 1.3, 1.5, 2.0, 2.5, 3.0mm
Y-Type | #000
Standoff | #00
PicoFinish® Precision Handle | 4mm
Bit Extension | 100mm




4mm Precision ground exact fit tips for reduced cam-out. ESD Safe PicoFinish® screwdriver with rotating cap for precise turning and control with fingertip.

36 Piece | GoBox™ ESD Safe PicoFinish® Precision Micro Bit Set

Model #75979

Slotted | 0.8, 1.5, 2.0, 2.5, 3.0, 3.5mm
Phillips | #000, #00 (2), #0, #1
Pentalobe | PL1, PL2, PL3, PL4, PL5, PL6
TORX® | T2, T3, T4, T6, T8
SAE Hex | 1/16, 5/32, 5/64, 1/8"
Metric Hex | .9, 1.3, 1.5, 2.0, 2.5, 3.0mm
Y-Type | #000
Standoff | #00
PicoFinish® Precision Handle | 4mm
Bit Extension | 100mm



4mm Precision ground exact fit tips for reduced cam-out. ESD Safe PicoFinish® screwdriver with rotating cap for precise turning and control with fingertip.

16 Piece | SYSTEM 4 PicoFinish® Micro Bit Set

Model #75093

Slotted | 1.5, 2.0, 2.5, 3.0mm
Phillips | #00, #0, #1
TORX® | T6, T7, T8, T9, T10, T15, T20
ESD Safe PicoFinish® Precision Handle | 4mm
Bit Extension | 100mm

ESD Safe Tweezers

ESD standard IEC 61340-5-1.



Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy. Special stainless steel, anti-magnetic and acid resistant. (10⁶-10⁹ Ohm)

10 Piece | ESD Safe Tweezers Set

Model #44593

AA SA | Fine Point, 2a SA | Flat Round Tip

3 SA | Round Point, 3c SA | Fine Round Points Shorter

4 SA | Very Fine Points, 7a SA | Curved Extra Fine

PSF SA | Flat 1.0mm Wide, 5bb SA | Extra Fine Bent

7abb SA | Curved Extra Fine, 4b SA | Very Fine Point 40°



Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy. Special stainless steel, anti-magnetic and acid resistant. (10⁶-10⁹ Ohm)

Universal Fine Point Tweezers

Model #	Description	
44501	AA SA ESD	130mm



Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy. Special stainless steel, anti-magnetic and acid resistant. (10⁶-10⁹ Ohm)

Flat Round Tip Smooth Sides

Model #	Description	
44505	2a SA ESD	120mm



Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy. Special stainless steel, anti-magnetic and acid resistant. (10⁶-10⁹ Ohm)

Long Rounded to 1.0mm Wide No serration

Model #	Description	
44523	PSF SA ESD	125mm



Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy. Special stainless steel, anti-magnetic and acid resistant. (10⁶-10⁹ Ohm)

MicroTip 30° Bend & 0.5mm Slot Milled

Model #	Description	
55531	11SA-SMD ESD	117mm

Electronic Precision Pliers and Cutters



ESD standard IEC 61340-5-1.



ESD Safe static dissipative. Extra long cutters for flat and round cables. Serrated jaws. Two component non-slip soft grip handle.

ESD Safe | Precision Long Nose Pliers With Return Spring

Model #		Head Width
32762	6.5"/165mm	.625"



Flush Cutters, ESD Safe static dissipative. Lightweight action, clean cutting. Two component non-slip soft grip handle.

ESD Safe | Precision Flush Cutting Diagonal Cutters

Model #		Head Width
32760	5.25"/133mm	.5"

The Comfortable Precision Pliers & Cutters

Electronics pliers with cutting edges are designed especially for cutting soft to medium hard wires.



Wide Pointed Head Cutting edge - full flush. With return spring. For an absolutely flush cut of copper wire.

Precision | Full Flush Cutting Electronic Diagonal Cutters

Model #		Cut Capacity
56818	5.5"/138mm	1.3mm/16AWG



Full Flush Cutters, ESD Safe static dissipative. Lightweight action, clean cutting. Two component non-slip soft grip handle.

ESD Safe | Precision Wide Tapered Head

Model #		Head Width
32710	4.5"/115mm	11.0mm



ESD Safe static dissipative. Straight, Serrated Jaws, drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle.

ESD Safe | Precision Long Needle Nose Pliers

Model #		Head Width
32746	5.75"/145mm	12.0mm



Classic Soft Grip Pliers and Cutters



DynamicJoint® provides 40% easier cuts and significantly longer tool life. Lightweight action, clean cutting. Special C70 tool steel hardened & tempered. For flush cutting soft and semi-hard wires.

Classic | Flush Cutting Mechanic's Diagonal Cutters

Model #		Cut Capacity
32613	5.0"/127mm	#12



Long nose pliers with return spring. For flat and round cables. Serrated Jaws. Special C70 tool steel. Soft vinyl grips are oil & solvent resistant.

Classic | Long Nose Pliers with Return Spring

Model #		Cut Cap. Copper AWG
32617	6.3"/160mm	#12

Classic Soft Grip Pliers and Cutters

Handle sized proportionate to blade for consistent mechanical advantage



Wiha Pliers and Cutters, professional quality at competitive prices. A wide selection covering most applications in which pliers and cutters are required.



Induction Hardened Cutting Edges and Jaws for superior sharpness and longevity



Double the power at the press of a button, switch between 2 strengths in one-handed operation



Double the power at the press of a button, switch between 2 strengths in one-handed operation. For cutting various materials from soft to extremely hard, such as nails, screws, bolts, wire cables, spring wires, chains, etc. Cutting capacity up to 3mm hardened piano wire.

Classic | BiCut Compound Cutters

Model #	↔
32636	8.0"/200mm



DynamicJoint® provides 40% easier cuts and significantly longer tool life. Lightweight action, clean cutting. Special C70 tool steel hardened & tempered. For flush cutting soft and semi-hard wires.

Classic | Flush Cutting Diagonal Cutters with Return Spring

Model #	↔
32614	6.3"/160mm
32607	5.0"/127mm



Low force action, clean cutting. Special C70 tool steel hardened and tempered. For cutting copper & aluminum cables without crushing, also suitable for stripping. Oil and solvent resistant classic grips.

Classic | Serrated Cable Cutters

Model #	↔	Cut Cap. Copper AWG
32600	6.3"/160mm	16mm
32602	8.0"/200mm	20mm



26° offset cutting angle. DynamicJoint® provides 40% easier cuts and significantly longer tool life. Low force action, clean cutting. C70 special tool steel. Soft vinyl grips are oil and solvent resistant.

Classic | Serrated Cable Cutters

Model #	↔	Cut Cap. Copper AWG
32620	8.0"/200mm	#4



Long nose pliers. Extra long cutters for flat and round cables. Serrated Jaws. Special C70 tool steel. Soft vinyl grips are oil & solvent resistant.

Classic | Long Nose Pliers with Cutters

Model #	↔	Cut Cap. Copper AWG
32618	6.3"/160mm	#10
32621	8.0"/200mm	#8



Low force action, clean cutting. Special C70 tool steel hardened and tempered. Oil and solvent resistant classic grips.

Classic | End Cutting Nippers

Model #	↔	Cut Cap. Copper AWG
32659	8.0"/200mm	#6



Knurled striking zone on vinyl grip pliers. Lower crimping jaw accepts most standard non-insulated electrical connectors. Soft vinyl grips are oil and solvent resistant.

Classic | NE Style Lineman's

Model #	↔
32631	9.5"/245mm

Knurled Striking Zone



Extra long cutting edge for flat and round cables. Lower crimping jaw accepts most standard non-insulated electrical connectors. Soft vinyl grips are oil and solvent resistant.

Classic | NE Style Lineman's Pliers with Crimper's

Model #	↔
32624	9.5"/245mm



Extra long cutting edge for flat and round cables. Serrated jaws. For gripping and holding as well as cutting soft & hard wires and cables.

Classic | Combination Pliers with Cutters

Model #	↔
32609	8.0"/200mm

Classic Soft Grip WaterPump Pliers



Just squeeze and pliers automatically adjust to diameter. Induction hardened jaws. Heavy duty box steel joints. Made from high quality CV special tool steel. Oil and solvent resistant classic grips.

Classic | Auto Grip Pliers

Model #	Capacities
32637	10.0"/250mm 1.5" Round / 1-9/16" Hex



Extra narrow head for working in restricted spaces. Rapid and simple push button setting and locking. Finger jam protection in all settings ensures safe operation. Soft vinyl grips are oil and solvent resistant.

3 Piece | Adjustable Push Button Water Pump Pliers

Model #32669

7"/180mm | 10"/250mm | 12"/300mm



9 different opening sizes provide optimal adjustment to objects being gripped. Long durability achieved through additional induction hardening of jaws to approx. 58-60 HRC. Oil and solvent resistant classic grips.

Classic | Box Type V-Jaw Tongue & Groove Pliers

Model #	Capacities
32660	7.0"/180mm 1.25" Round / 1-1/2" Hex
32661	10.0"/250mm 1.75" Round / 2" Hex
32663	12.0"/300mm 2.0" Round / 2-1/4" Hex



Smooth jaws for damage free turning on parallel surfaces. Fully adjustable jaws from 1-3/4" round / 46mm Hex. Easy & quick adj. just slide & close directly on the work piece.

Classic | Auto Grip Pliers

Model #	Capacities
32635	10.25"/260mm

Classic Soft Grip Retaining Ring Pliers



DIN ISO 5256. Shape C, straight tips. Die forged cylindrical precision formed. For inserting & removing internal retaining rings.

Classic | Straight Internal Retaining Ring Pliers

Model #	Capacities	Tip
32683	180 7.0 3/4-2 3/8 19-60	.070/1.5

DIN ISO 5256. Shape A, straight tips. Die forged cylindrical precision formed. For inserting & removing external retaining rings.

Classic | Straight External Retaining Ring Pliers

Model #	Capacities	Tip
32691	180 7.0 3/4-2 3/8 19-60	.070/1.5



Extra narrow head for working in restricted spaces. Rapid and simple push button setting and locking. Finger jam protection in all settings ensures safe operation. Soft vinyl grips are oil and solvent resistant.

3 Piece | Pliers & Cutters Set

Model #32634

9.5" NE Style Lineman's, 8.0" Long Nose Pliers
8.0" High Leverage Pliers

Tips made of premium quality hardened CVM tool steel, HRC 64



DIN ISO 5256. Shape D, 90° angled tips. Die forged cylindrical precision formed. For inserting & removing internal retaining rings.

Classic | 90° Angle Internal Retaining Ring Pliers

Model #	Capacities	Tip
32687	180 7.0 3/4-2 3/8 19-60	.070/1.5



DIN ISO 5256. Shape B, 90° angled tips. Die forged cylindrical precision formed. For inserting & removing external retaining rings.

Classic | 90° Angle External Retaining Ring Pliers

Model #	Capacities	Tip
32696	180 7.0 3/4-2 3/8 19-60	.070/1.5



Holes in the jaw for looping wire. Crimper's Long head with cushion gripping surface, shears blade and firm wire stripping stations.

Vinyl Grip | Wire Strippers

Model #	Capacities
57810	7.25"/184mm Strips 10-18
57814	8.25"/210mm Strips 10-22
57820	7.75"/197mm Strips 12-14

TERMINATORblue IMPACT BITS

TST™

Torsion Stabilizing Technology



Wiha TERMINATORblue™ impact bits feature an energy absorbing torsion zone for 30 times performance & computer-controlled heat treatment for 120 times life-time over Wiha standard bits

TerminatorBlue™ Impact Bits



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

7 Piece | TerminatorBlue™ 2" Impact BitBuddy Set

Model #70298

Phillips | #1, #2

Square | #1, #2

TORX® | T20, T25, T30

8 Piece | TerminatorBlue™ 1" Impact BitBuddy Set

Model #70098

Phillips | #1, #2 Square | #1, #2

TORX® | T20, T25, T30

SlimFix Locking Bit Holder | 1/4"



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

32 Piece | TerminatorBlue™ Ratchet & 1" Impact Bit Set

Model #76889

Phillips | #1, #2, #3 (2 of each)

Square | #1, #2, #3

TORX® | T10, T15, T20, T25, T27, T30, T40

Metric Hex | 3.0, 4.0, 5.0, 6.0mm

SAE Hex | 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Pozidriv® | #1, #2, #3

Locking Bit Holder | 1/4" SlimFix

Adapter | 1/4" Hex to 1/4" Square

1/4" Reversible Bit Ratchet | 72 tooth



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

40 Piece | TerminatorBlue™ Impact Bit Set

Model #70297

Phillips | #1, #2 (5), #3 x 25mm

Square | #1, #2 (2), #3 x 25mm

TORX® | T15, T20 (2), T25 (5), T30 x 25mm

Phillips | #1, #2 (3), #3 x 50mm

Square | #1, #2, #3 x 50mm

TORX® | T20, T25 (2), T30, T40 x 50mm

Phillips | #2 x 89mm

Square | #2 x 89mm

TORX® | T20, T25, T30 x 89mm

Magnetic Nut Setters | 5/16, 3/8" x 76mm

Magnetic Bit Holder | 1/4" x 60mm

Impact Rated Bits



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

2 Bit Pack | TerminatorBlue™ Phillips 1/4" Impact Bits

Model #	+	—	—
70002	#2	25mm	2.0"

2 Bit Pack | TerminatorBlue™ TORX® 1/4" Impact Bits

Model #	+	—	—
70020	T25	25mm	2.0"

2 Bit Pack | TerminatorBlue™ Square 1/4" Impact Bits

Model #	+	—	—
70025	#2	25mm	2.0"



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

2 Bit Pack | TerminatorBlue™ Phillips 1/4" Impact Bits

Model #	+	—	—
70201	#1	50mm	2.0"
70202	#2	50mm	2.0"
70203	#3	50mm	2.0"



2 Bit Pack | TerminatorBlue™ TORX® 1/4" Impact Bits

Model #	+	—	—
70218	T15	50mm	2.0"
70219	T20	50mm	2.0"
70220	T25	50mm	2.0"
70222	T30	50mm	2.0"
70223	T40	50mm	2.0"



2 Bit Pack | TerminatorBlue™ Square 1/4" Impact Bits

Model #	+	—	—
70225	#2	50mm	2.0"



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

5 Bit Pack | TerminatorBlue™ Phillips 1/4" Impact Bits

Model #	+	—	—
70269	#2	50mm	2.0"



5 Bit Pack | TerminatorBlue™ TORX® 1/4" Impact Bits

Model #	+	—	—
70277	T25	50mm	2.0"
70279	T30	50mm	2.0"



5 Bit Pack | TerminatorBlue™ Square 1/4" Impact Bits

Model #	+	—	—
70282	#2	50mm	2.0"



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

2 Bit Pack | TerminatorBlue™ Phillips 1/4" Impact Bits

Model #	+	—	—
70302	#2	90mm	3.5"



2 Bit Pack | TerminatorBlue™ TORX® 1/4" Impact Bits

Model #	+	—	—
70319	T20	90mm	3.5"
70320	T25	90mm	3.5"
70322	T30	90mm	3.5"



2 Bit Pack | TerminatorBlue™ Square 1/4" Impact Bits

Model #	+	—	—
70325	#2	90mm	3.5"



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

20 Bit Pack | TerminatorBlue™ Phillips 1/4" Impact Bits

Model #	+	—	—
70042	#2	25mm	1.0"



20 Bit Pack | TerminatorBlue™ TORX® 1/4" Impact Bits

Model #	+	—	—
70060	T25	25mm	1.0"



20 Bit Pack | TerminatorBlue™ Square 1/4" Impact Bits

Model #	+	—	—
70065	#2	25mm	1.0"



Exact fit precision machined tips for reduced cam-out. Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

15 Bit Pack | TerminatorBlue™ Phillips 1/4" Impact Bits

Model #	+	—	—
70242	#2	50mm	2.0"



15 Bit Pack | TerminatorBlue™ TORX® 1/4" Impact Bits

Model #	+	—	—
70260	T25	50mm	2.0"



15 Bit Pack | TerminatorBlue™ Square 1/4" Impact Bits

Model #	+	—	—
70265	#2	50mm	2.0"

1/4" Drive Bit Holders



Collar locks bits securely into place for repetitive high impact work. Sliding quick-release and spring-loaded bit ejector for quick and easy bit exchange.

1/4" Quick Release Locking Bit Holder

Model #		
70096	1/4"	2.4"



Sleeker, more productive SlimFix for instant bit changes. Just 10.9mm/0.42 diameter. Bit locks securely in place.

SlimFix Impact Rated Bit Holder

Model #		
71496	1/4"	2.6"



Quick release tool folder for drills, countersinks & power bits. Includes Phillips #2 / 70mm

CentroFix Bit Holder

Model #		
71480	1/4"	2.4"



Magnetic for 1" insert bits. One-handed bit change.

ClickFix Bit Holder

Model #		
71491	1/4"	2.9"



Wiha soft grips are molded on with through the handle side torque drive. Magnetic holds bit and screw.

Soft Grip Magnetic T-handle Bit Holder

Model #			
38802	1/4"	178mm	7.0"



Stainless steel with strong magnet. Wiha-SoftFinish® cushion grip handle. For working in confined spaces.

SoftFinish® Stubby Magnetic Bit Holder

Model #			
28103	1/4"	57mm	2.2"

Contractor Bit Sets



Exact fit precision machined tip for reduced cam-out. Premium quality tool steel for strength and durability.

10 Piece | 1" Bit Pack

Model #72593

Slotted | 4.5, 5.5, 6.0mm Phillips | #1, #2, #3
Square | #1, #2, #3

Model #72595

TORX® | T7, T8, T9, T10, T15, T20, T25, T27, T30, T40

Model #72596

SAE Hex | 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



Exact fit precision machined tip for reduced cam-out. 2"/50mm OAL

10 Pc. | Belt Bit Pack Hex Bits

Model #74986

Inch | 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
Metric | 3.0, 4.0, 5.0, 6.0mm



10 Piece | Belt Bit Pack Ball End Screw Holding Hex Bits

Model #74999

Inch | 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
Metric | 3.0, 4.0, 5.0, 6.0mm



10 Piece | Belt Bit Pack Security TORX® Bits

Model #74987

TORX® | T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s



SoftFinish® cushion grip handle for comfort and control. Exact fit precision machined tip for reduced cam-out.

7 Piece | SoftFinish® Cushion Grip Stubby Bit Holder Set

Model #38048

Slotted | 4.5, 6.0mm
Phillips | #1, #2 Square | #1, #2



SoftFinish® cushion grip handle for comfort and control. Exact fit precision machined tip for reduced cam-out.

7 Piece | SoftFinish® Cushion Grip Stubby Bit Holder Set

Model #38045

TORX® | T8, T10, T15, T20, T25, T30



Exact fit precision machined tip for reduced cam-out. Premium quality tool steel for strength and durability.

39 Piece | Bits Collector 1/4" Ratchet & 1" Bit Set

Model #71988

Slotted | 6.5, 8.0mm Phillips | #1, #2
Square | #1, #2, #3 Pozidriv® | #0, #1, #2, #3
Security TORX® | T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
SAE Security Hex | 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
Spanner | #4, #6, #8, #10
Tri-Wing | #1, #2, #3, #4
Torq Set | #6, #8, #10
SoftFinish® Bit Holder Handle | Holds 1/4" Bits
Magnetic Bit Holder | Holds 1/4" Bits
Socket Adapter | 1/4" bit holding

GoBox™ Bit Sets



Exact fit precision machined tips for reduced cam-out.
72 tooth Bit ratchet & 1/4" magnetic bit holder.

32 Piece | 1"/25mm GoBox™ 1/4" Ratchet Standard Bit Set

Model #74984

Slotted | 5.5, 6.5mm

Phillips | #0, #1, #2, #3

Square | #1, #2

TORX® | T8, T10, T15, T20, T25, T27, T30

Metric Hex | 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm

SAE Hex | 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"

Magnetic Bit Holder | 1/4" x 2.625"

Adapter | 1/4" Hex to 1/4" Square Drive

Bit Ratchet Handle | 1/4" x 3.5"



Exact fit precision machined tips for reduced cam-out.
72 tooth Bit ratchet & 1/4" magnetic bit holder.

32 Piece | 1"/25mm GoBox™ 1/4" Ratchet Security Bit Set

Model #74958

Security Hex MM | 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

Security Hex SAE | 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Security TORX® | T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

Slotted | 3.5, 5.5mm

Phillips | #0, #1, #2

Spanner | #4, #6, #8, #10

Magnetic Bit Holder | 1/4" x 2.625"

Bit Ratchet Handle | 1/4" x 3.5"



Exact fit precision machined tips for reduced cam-out.
72 tooth Bit ratchet & 1/4" magnetic bit holder.

32 Piece | 1"/25mm GoBox™ 1/4" Ratchet TORX® Bit Set

Model #74959

TORXPlus® | IP3, IP4, IP5, IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40

Security TORX® | T7S, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

TORX® Align | T10, T15, T20, T25, T30

Phillips | #2

Magnetic Bit Holder | 1/4" x 2.625"

Bit Ratchet Handle | 1/4" x 3.5"



Exact fit precision machined tip for reduced cam-out.
Premium quality tool steel for strength and durability.

39 Piece | Bits Collector SoftFinish® Handle & 1" Bit Set

Model #71990

Slotted | 6.0, 8.0mm Phillips | #1, #2

Square | #1, #2, #3 Pozidriv® | #0, #1, #2, #3

Security TORX® | T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

SAE Security Hex | 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Spanner | #4, #6, #8, #10

Tri-Wing | #1, #2, #3, #4

Torq Set | #6, #8, #10

SoftFinish® Bit Holder Handle | Holds 1/4" Bits

Magnetic Bit Holder | Holds 1/4" Bits

Socket Adapter | 1/4" bit holding



Exact fit precision machined tip for reduced cam-out.
Premium quality tool steel for strength and durability.

39 Piece | Bits Collector SoftFinish® Handle & 1" Bit Set

Model #71991

Slotted | 6.0, 8.0mm & Phillips | #1, #2

Square | #1, #2, #3 Pozidriv® | #0, #1, #2, #3

Security TORX® | T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

SAE Security Hex | 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Spanner | #4, #6, #8, #10

Tri-Wing | #1, #2, #3, #4

Torq Set | #6, #8, #10

SoftFinish® Bit Holder Handle | Holds 1/4" Bits

Magnetic Bit Holder | Holds 1/4" Bits

Socket Adapter | 1/4" bit holding

Impact Bit Set



Exact fit precision machined tips for reduced cam-out.
Tuned torsion zone for maximum flex and reduced tip stress. Impact rated for power tool applications.

34 Piece | MaxxTor™ 1" Impact Bit Set

Model #76899

Phillips | #1, #2, #3 (2 of each)

Square | #1, #2 (2), #3

TORX® | T10, T15, T20 (2), T25 (2), T30 (2), T40

Metric Hex | 3.0, 4.0, 5.0, 6.0mm

SAE Hex | 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Pozidriv® | #1, #2, #3

Locking Bit Holder | 1/4" SlimFix

Bit Holder Handle | Holds 1/4" Bits

SoftFinish® Stubby Bike Repair Multi-Driver



SoftFinish® cushion grip Stubby bit holder handle holds seven 1" standard bits securely. 2.2" handle is perfect for working in confined spaces.

14 Piece | Stubby Bike Repair

Model #38083

Slotted | 4.5mm Phillips | #1, #2

TORX® | T10, T15, T20, T25

Hex Metric | 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm

Contractor Bit Sets



Exact fit precision machined tips for reduced cam-out. 1/4" magnetic bit holder. 1"/25mm bits

31 Piece | XLSelector Bit Set

Model #79495

Slotted | 4.5, 5.5, 6.0mm

Phillips | #0, #1, #2, #3

TORX® | T6, T7, T8, T9, T10, T15, T20, T25

Metric Hex | 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm

SAE Hex | 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Magnetic Bit Holder | 1/4"



Exact fit precision machined tips for reduced cam-out. 1/4" magnetic bit holder. 1"/25mm bits

10 Piece | Bit-Selector TORX® Bit Set

Model #79242

TORX® | T5, T6, T7, T8, T9, T10, T15, T20, T25, T30

CentroFix Blade Holder



Wiha-SoftFinish® handle multi-component, cushion grips. Holds 90mm power blades.

SoftFinish® Cushion Grip CentroFix Blade Holding Handle

Model #			
76000	6.0mm	149mm	5.8"



SoftFinish® impact resistant, with roll off protection. Quick release bit holder with magnet. Quick release tool holder for drill bits, countersinks & power bits.

37 Piece | Power Blade Set

Model #76099

Slotted | 2.5, 3.0, 4.5, 5.5, 6.0mm

Phillips | #0, #1, #2, #3

Security TORX® | T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s

Security Hex SAE | 1/16", 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Pozidriv® | #1, #2, #3 Square | #1, #2, #3

Nut Setters | 1/4", 5/16, 3/8"

CentroFix Blade Holder | Holds 90mm Blades

* 1/16" Standard Inch Hex Only

Razor Edged Scraper



Wiha-SoftFinish® handle multi-component, cushion grips. 10 replacement blades included

SoftFinish® Cushion Grip Razor Edged Scraper

Model #		
43090	170mm	6.7"

Wing Handle Screwdrivers



Black oxide finish, through hardened. Exact fit precision tips for reduced cam-out. Top spinner grip knob.

7 Piece | Wing Handle Set

Model #36590

TORX® | T6, T7, T8, T9, T10, T15, T20



Black oxide finish, through hardened. Exact fit precision tips for reduced cam-out. Top spinner grip knob.

7 Piece | Wing Handle Set

Model #36592

TORXPlus® | IP6, IP7, IP8, IP9, IP10, IP15, IP20



Black oxide finish, through hardened. Exact fit precision tips for reduced cam-out. Top spinner grip knob.

7 Piece | Flag Handle Set

Model #37090

TORX® | T6, T7, T8, T9, T10, T15, T20

Made in Germany

Made in Germany

Made in Germany

TORX® and Hex L-key Sets



Long arm laser welded MagicSpring assembly, holds screws securely. Black oxide finish, through hardened.

10 Piece | MagicSpring Screw Holding L-key Set

Model #37192

TORX® | T6, T7, T8, T10, T15, T20, T25, T27, T30

Laser Welded MagicSpring Assembly



Long arm, ball end allows 25° angle drive of TORX® screws. Black oxide finish, through hardened.

13 Piece | ErgoStar Ball End L-key Set

Model #36689

TORX® | T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45



Black oxide finish, through hardened. Exact fit precision tips for reduced cam-out.

13 Piece | Long Arm L-key Set

Model #36699

TORX® | T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T50



Black oxide finish, through hardened. Exact fit precision tips for reduced cam-out.

7 Piece | Mini L-key Set

Model #36392

TORX® | T6, T7, T8, T9, T10, T15, T20



Black oxide finish, through hardened. Exact fit precision tips for reduced cam-out.

5 Piece | Mini L-key Set

Model #35393

Hex SAE | .028, .035, .050, 1/16, 5/64"



Black oxide finish, through hardened. Exact fit precision tips for reduced cam-out.

5 Piece | Mini L-key Set

Model #35392

Hex Metric | 0.7, 0.9, 1.3, 1.5, 2.0mm



Screw Holding Hex Tools!



Screw Holding Ball Ends for one-handed fastener management. Wiha premium quality tool steel for strength and durability.

22 Piece | MagicRing® Screw Holding L-key Sets

Model #66992

SAE Hex | .050", 1/16", 5/64", 3/32", 7/64", 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Metric Hex | 1.5*, 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

* Standard Ball - No Ring



13 Piece | MagicRing® Screw Holding L-key Set

Model #66991

SAE Hex | .050", 1/16", 5/64", 3/32", 7/64", 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

* Standard Ball - No Ring



9 Piece | MagicRing® Screw Holding L-key Set

Model #66990

Metric Hex | 1.5*, 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

* Standard Ball - No Ring



Hex Inch & Metric L-key Sets



Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out.

22 Piece | ErgoStar® L-key Sets

Model #66982

Ball End SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Ball End Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm



Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out.

22 Piece | L-key Sets

Model #66993

Ball End SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Ball End Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm



Long arm, ball end allows 25° angle drive of hex screws. Black oxide finish, through hardened.

22 Piece | L-key Sets

Model #36995

Ball End SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Ball End Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm



13 Piece | ErgoStar® L-key Set

Model #66988

Ball End SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



9 Piece | ErgoStar® L-key Set

Model #66996

Ball End Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm



13 Piece | L-key Set

Model #36998


Ball End SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



9 Piece | L-key Set

Model #66994

Ball End Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm




Bright-bold Color Coding for quick and easy identification. Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out.

13 Piece | Color Coded L-key Set

Model #66981

Ball End SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



Bright-bold Color Coding for quick and easy identification. Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out.

9 Piece | Color Coded L-key Set

Model #66980

Ball End Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

PocketStar Fold-Ups



Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out.

7 Piece | PocketStar Fold-Up

Model #35195

Metric Hex | 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm



9 Piece | PocketStar Fold-Up

Model #35197

SAE Hex | 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Mechanics Tools




Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out. Black oxide finish, through hardened.

8 Piece | Soft Grip Dual Drive T-handle Set

Model #33489

Metric Hex | 2.0*, 2.5*, 3.0*, 4.0, 5.0,
6.0, 8.0, 10.0mm

* Standard Ball - No Ring



Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out. Black oxide finish, through hardened.

11 Piece | Soft Grip Dual Drive T-handle Set

Model #33494

Ball End SAE Hex | 5/64*, 3/32*, 7/64*, 1/8*,
9/64*, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

* Standard Ball - No Ring




Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out. Black oxide finish, through hardened.

8 Piece | Soft Grip Dual Drive T-handle Set

Model #33496

Ball End Metric Hex | 2.0*, 2.5*, 3.0*, 4.0,
5.0, 6.0, 8.0, 10.0mm

* Standard Ball - No Ring



Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out.

10 Piece | Soft Grip Dual Drive T-handle Set

Model #54097

Ball End SAE Hex | 3/32*, 7/64*, 1/8*, 9/64*,
5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

* Standard Ball - No Ring



8 Piece | Soft Grip Dual Drive T-handle Set

Model #54095

Metric Hex | 2.0*, 2.5*, 3.0*, 4.0, 5.0,
6.0, 8.0, 10.0mm

* Standard Ball - No Ring



Wiha premium quality tool steel for strength and durability. Precision machined exact fit tips for reduced cam-out.

10 Piece | T-handle Set

Model #33492

SAE Hex | 3/32, 7/64, 1/8, 9/64, 5/32, 3/16,
7/32, 1/4, 5/16, 3/8"



8 Piece | T-handle Set

Model #33493

Metric Hex | 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm



Magnetic
Impact Rated

Impact Rated Nut Setters



High visibility color coded for fast selection, rugged corrosion resistant black oxide finish, impact rated to 700 in/lbs.. 6"/152mm OAL.

6 Piece | SAE Color Coded Impact Nut Setters

Model #70486

Red | 1/4", **Yellow** | 5/16", **Blue** | 3/8"
Brown | 7/16", **Orange** | 1/2", **Black** | 9/16"



6 Piece | Metric Color Coded Impact Nut Setters

Model #70487

Red | 8mm, **Blue** | 10mm, **Teal** | 11mm
Green | 12mm, **Yellow** | 13mm, **Orange** | 14mm

Digital Caliper



Non-metallic high-tech material with 60% fiber glass content. 5 digit digital display with 7.5mm numeral height for easy reading. For outside, inside, depth and step measurements. Switches on automatically when used and switches off automatically after five minutes of non-use. Zero setting possible in every position for quick comparison measurements.

Digital Caliper DigiMax

Model #	Reading	Reading	Reading
41101	0.0005"	6"	.01mm 150mm

Adjustable Wrenches



Etched on scale for pre-setting size. Black oxide finish for superior corrosion resistance. Precision jaw and knurl for easy and precise adjustments. Expanded jaw capacity for broader applications.

Adjustable Wrenches

Model #	—	—	Cap. Opening
76201	8.0"	200mm	1"
76202	10"	250mm	1-1/4"
76203	12"	300mm	1-1/2"



3 Piece | Adjustable Wrench Set

Model #76280

3 Piece | 8", 10", 12"

Ratcheting Wrench Sets

Soft grip rack with wire bail holds wrenches securely



72 tooth geared ratcheting. 12 point box end with 5° swing arc. Wiha premium quality tool steel for strength and durability.

12 Piece | Ratcheting Metric Wrench Set

Model #30391

Metric | 8.0, 9.0, 10.0, 11.0, 12.0, 13.0, 14.0, 15.0, 16.0, 17.0, 18.0, 19.0mm

MaxiFlex Folding Ruler



Patented play free joint with steel spring pin, wear resistant & maintenance free. 90° positive stop joints. Tough and Flexible, impact resistant.


Combination Metric & Inch MaxiFlex Folding Ruler

Model #61662

2 Meter/78" Inch | Width 15mm | 10 Sections
1/16 & 1mm Increments

Heavy Duty Split Head Mallet

Easy replacement with standard components
Malleable cast iron heads



With hickory handle, safety ribbed housings for handle & faces. Faces replaceable.

50mm | Malleable Cast Iron Hammer

Model #83256

50mm Hammer Faces | Hard/Soft



72 tooth geared ratcheting. 12 point box end with 5° swing arc. Wiha premium quality tool steel for strength and durability.

12 Piece | Ratcheting SAE Wrench Set

Model #30394

SAE | 1/4, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8"



Outside Reading Metric Long Life MaxiFlex Folding Rulers Molded 30% fiber glass reinforced polyimide scratch, chemical & weather resistant both tough & flexible, impact resistant. Metric rules have 10cm red marking. 90° positive stop joints.

Combination Metric & Inch MaxiFlex Folding Ruler

Model #61602

2 Meter | Width 15mm | 10 Sections
1mm to CM Increments

Dead Blow Hammers



Anti-vibration ergo cushion grips. All steel body for incredible durability. Filled with environmentally safe shot. Medium hard faces.

3 Piece | Dead Blow Hammer Set

Model #80290

Hammer Faces | 3.0, 40, 50mm



Dead Blow Hammers

Model #	—	—	—
80250	50mm	365mm	14.4"
80260	60mm	375mm	14.8"

Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty
10250	20	3	28196	28	1	28550	30	1	28619	31	1	30391	49	1	32592	8	1
12851	22	1	28345	11	3	28551	30	1	28655	30	1	30392	3	1	32600	39	3
12852	22	1	28390	10	1	28552	30	1	28781	11	1	30492	3	1	32602	39	3
12853	22	1	28391	10	1	28553	30	1	28789	11	1	30394	49	1	32607	39	3
13690	24	1	28393	10	3	28555	31	1	28791	11	1	31390	21	1	32609	39	3
13691	24	1	28394	10	3	28556	31	1	28792	11	1	31391	21	1	32613	38	3
13693	24	1	28395	10	3	28557	31	1	28882	28	1	31491	21	1	32614	39	3
13694	24	1	28398	10	1	28558	31	1	28903	29	1	31493	22	1	32617	38	3
20091	23	1	28399	10	1	28559	31	1	28904	29	1	31495	22	1	32618	39	3
20190	23	1	28404	30	1	28560	31	1	28905	29	1	31496	22	1	32620	39	3
20192	23	1	28410	30	1	28561	31	1	28906	29	1	31590	22	1	32621	39	4
21094	23	1	28412	30	1	28562	31	1	28907	29	1	31592	22	1	32624	39	4
21096	23	1	28413	30	1	28563	31	1	28908	29	1	31694	22	1	32631	39	3
21103	9	3	28500	28	1	28564	31	1	28910	29	1	31792	22	1	32634	40	3
21290	23	1	28501	30	1	28565	31	1	28911	29	1	31890	21	1	32635	40	3
21391	23	1	28502	30	1	28566	31	1	28912	29	1	32059	7	3	32636	39	4
25506	20	3	28503	30	1	28567	31	1	28913	29	1	32080	4	1	32637	40	4
26090	33	3	28506	30	1	28568	31	1	28914	29	1	32081	5	1	32659	39	3
26092	33	3	28512	31	1	28569	31	1	28916	29	1	32085	9	3	32660	40	3
26099	33	3	28515	30	1	28571	31	1	28917	29	1	32087	7	1	32661	40	4
26190	33	3	28522	28	1	28572	31	1	28918	29	1	32088	9	3	32663	40	3
26192	33	3	28527	31	1	28573	31	1	28919	29	1	32090	6	3	32669	40	1
26193	36	3	28528	31	1	28574	31	1	28940	29	1	32091	6	3	32683	40	1
26194	33	3	28529	31	1	28575	31	1	29205	30	1	32092	6	3	32687	40	3
26195	36	6	28530	31	1	28576	31	1	29209	30	1	32093	6	1	32691	40	3
26197	33	4	28531	31	1	28577	31	1	29211	30	1	32094	7	1	32696	40	3
26199	33	3	28534	31	1	28578	31	1	29225	30	1	32095	8	1	32710	38	1
26390	34	3	28535	31	1	28579	31	1	30114	21	1	32097	7	3	32746	38	3
26391	34	3	28536	31	1	28581	30	1	30138	21	1	32099	6	3	32760	38	3
26491	34	3	28537	31	1	28582	30	1	30152	21	1	32188	7	1	32762	38	1
26590	34	3	28538	31	1	28583	30	1	30190	21	1	32190	8	1	32800	12	1
26591	34	3	28539	31	1	28587	31	1	30192	21	1	32192	18	1	32801	12	1
26592	34	3	28540	31	1	28588	31	1	30277	26	3	32196	9	1	32868	15	1
26791	34	3	28541	31	1	28589	29	1	30278	26	3	32197	9	1	32869	14	1
26799	34	3	28542	31	1	28595	29	1	30279	26	3	32198	9	1	32873	15	1
27392	36	3	28543	31	1	28611	31	1	30280	4	1	32288	8	1	32874	13	1
27393	33	3	28544	31	1	28612	31	1	30284	26	1	32292	8	1	32876	13	1
27396	36	1	28545	31	1	28613	31	1	30292	28	1	32293	8	1	32878	14	1
28103	43	3	28546	31	1	28614	31	1	30295	8	3	32294	8	1	32879	13	1
28187	28	1	28547	31	1	28616	31	1	30297	26	1	32296	8	1	32888	15	1
28188	28	1	28548	31	1	28617	31	1	30298	26	1	32490	11	1	32891	15	1
28189	28	1	28549	31	1	28618	31	1	30299	27	1	32590	8	1	32892	15	1

Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty	Item No.	Page No.	Case Pack Qty
32894	14	1	34680	5	1	53180	4	1	70277	42	6	76889	41	6			
32895	14	1	34681	5	1	53390	25	1	70279	42	6	76899	44	1			
32902	19	3	34682	4	1	53398	25	1	70282	42	6	77890	27	6			
32923	19	3	34690	5	1	54095	48	1	70297	41	4	77891	27	6			
32926	19	3	34691	4	1	54097	48	1	70298	41	6	77892	27	3			
32927	19	3	35195	47	6	56818	38	3	70302	42	6	79242	45	6			
32929	19	3	35197	47	6	57810	40	3	70319	42	6	79495	45	3			
32930	19	3	35392	46	6	57814	40	3	70320	42	6	80250	49	1			
32933	19	3	35393	46	6	57820	40	3	70322	42	6	80260	49	1			
32934	16	1	35890	7	1	61602	49	3	70325	42	6	80290	49	1			
32935	16	1	36267	26	1	61662	49	3	70486	48	6	83256	49	1			
32936	19	3	36291	26	1	66980	47	3	70487	48	6	91459	35	3			
32937	17	1	36294	26	3	66981	47	3	71480	43	3	91473	35	3			
32938	19	3	36392	46	1	66982	47	3	71491	43	3	91869	2	1			
32939	19	3	36590	45	1	66988	47	3	71496	43	3	91890	20	1			
32945	19	3	36592	45	3	66990	46	3	71988	43	3	92093	36	1			
32948	19	3	36689	46	1	66991	46	3	71990	44	3	92189	35	1			
32951	20	3	36699	46	1	66992	46	3	71991	44	1	92190	35	1			
32960	5	1	36995	47	1	66993	47	3	72595	43	3	92191	35	1			
32968	16	3	36998	47	3	66994	47	3	72596	43	3						
32973	17	1	37090	45	3	66996	47	3	74958	44	6						
32977	17	1	37192	46	3	70002	42	6	74959	44	6						
32981	18	3	38045	43	3	70020	42	6	74984	44	6						
32985	18	1	38048	43	3	70025	42	6	74986	43	3						
32986	18	1	38050	20	3	70042	42	6	74987	43	3						
32987	18	1	38051	20	3	70060	42	6	74999	43	3						
32990	18	1	38083	43	3	70065	42	6	75093	37	3						
32999	18	1	38090	27	3	70096	43	6	75958	37	6						
33395	5	1	38802	43	3	70098	41	6	75965	37	3						
33396	5	1	40010	35	10	70201	42	6	75971	37	3						
33478	24	1	41101	48	1	70202	42	6	75979	37	6						
33489	48	1	43090	45	3	70203	42	6	75980	37	3						
33490	24	1	44501	38	3	70218	42	6	76000	45	3						
33492	48	1	44505	38	3	70219	42	6	76099	45	1						
33493	48	1	44523	38	3	70220	42	6	76201	49	3						
33494	48	1	44531	38	3	70222	42	6	76202	49	3						
33496	48	1	44593	38	1	70223	42	6	76203	49	3						
33580	6	3	53075	25	1	70225	42	6	76208	23	1						
33795	5	1	53082	25	3	70242	42	6	76210	23	1						
33796	5	1	53095	25	1	70260	42	6	76212	23	1						
33895	4	1	53097	25	1	70265	42	6	76280	49	1						
33896	4	1	53099	25	1	70269	42	6	76290	23	1						



No Hassle Guarantee

Wiha branded tools are regarded as the most durable, best designed and highly innovative products around. Our tools are used by demanding professional tradespeople and tool aficionados alike. They are meant to be used and utilized often. However, if you are not happy for any reason return them within 12 months of purchase with proof of purchase and we will **Repair or Replace**.

Rest assured, if for some reason there is a defect in material or workmanship we will replace your tool free of charge for as long as you own the tool.

Failures due to misuse, abuse or normal wear and tear are not covered by this guarantee. We stand by our products with what we believe is the best **No Hassle Guarantee** in the industry.

Exclusions

Wiha Tools has the right to exclude Bits, Tweezers and Ceramic Screwdrivers. These products are either consumable or wear easily.

All torque tools are designed for 5,000 cycles or 1 year (whichever comes first). If a tool becomes out of specification within that period Wiha Tools will **Repair or Replace**. Visit www.wihatools.com to learn more about our Torque Control Service Program.

Legal

Some areas do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This guarantee gives you specific rights, and you may also have other rights, which vary, from state to state, province to province, or country to country.

This **No Hassle Guarantee** is the sole and exclusive guarantee for the Willi Hahn Corporation dba Wiha Tools. No employee, agent, dealer, or other person is authorized to alter this guarantee or make any other guarantees on behalf of Wiha Tools.

Willi Hahn Corporation USA | Attn: No Hassle Guarantee
1348 Dundas Circle | Monticello, MN 55362




USA

(800) 494-6104 | (763) 295-6591
fax: (800) 494-7456 | (763) 295-6598
cservice@wihatools.com
www.wihatools.com

CANADA

(866) 494-0096 | (763) 295-6591
fax: (763) 295-6598
canada@wihatools.com
www.wihatools.com




99002 Screwdrivers Catalog



99001 TorqueControl Catalog



99919 Insulated Catalog



99951 Bits Catalog



99060 Product Guide

Distributed By:

Subject to change without notice

©2023 Willi Hahn Corporation

®Torx is a registered trademark of
Acument Intellectual Properties LLC.

Catalog Item No. 91327
version - 10/1/2023