

2026

wiha 
Tools that work for you

TORX® / HEX L-keys and Dual Drive T-handles



Color Coded L-key Sets Ball End Hex



25°
angle for
improved
access

Premium
Quality
Tool Steel



SAE

Color Coded L-keys

Metric

Color Coded L-keys



Ideal for fastening screws in
difficult-to-access spots and fastening
into horizontal, inclined or deep tapped
blind holes

- Works smoothly for up to 25° angles chamfered ball end
- Fast and easy tool identities with bright and bold color coding and compact holder with marked sizes
- Slip resistant grip from the textured surface



**13 Piece | Color Coded
SAE L-key Set**

Model #66981

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8,
9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



**9 Piece | Color Coded
Metric L-key Set**

Model #66980

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0,
8.0, 10.0mm



Made in
Germany

NO HASSLE
GUARANTEE

► MagicRing® L-key Sets Ball End Screw Holding



25°
angle for
improved
access

Premium
Quality
Tool Steel



SAE

MagicRing® L-keys



Metric

MagicRing® L-keys



- ◆ 20% Longer keys for hard to reach fasteners
- ◆ Works smoothly for up to 25° angles chamfered ball end
- ◆ Exact fit precision machined tip for reduced cam-out
- ◆ Chrome-plated satin finish for corrosion protection

Wiha exclusive ErgoStar holder works by turning the largest L-key to turn all keys 90° for clear and unimpeded selection and includes the size marked on the holder for easy identification

Screw
Holding
Hex keys



Screw
Holding
Hex
Tools!



Wiha MagicRing® Ball End Hex L-Keys feature Screw Holding Ball Ends for one-handed fastener management with a non-wearing steel spring compression ring for holding screws securely and a Ball End for fastener interlock of up to 25°

13 Piece | MagicRing® Screw Holding L-key Set

Model #66991

SAE Hex | .050*, 1/16*, 5/64*, 3/32*, 7/64*, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

* Standard Ball - No Ring

9 Piece | MagicRing® Screw Holding L-key Set

Model #66990

Metric Hex | 1.5*, 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

* Standard Ball - No Ring

22 Piece | MagicRing® Screw Holding L-key Sets

Model #66992

SAE Hex | .050*, 1/16*, 5/64*, 3/32*, 7/64*, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Metric Hex | 1.5*, 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

* Standard Ball - No Ring

NO HASSLE
GUARANTEE



ErgoStar® L-key Sets

Ball End Hex



25°
angle for
improved
access

Premium
Quality
Tool Steel



SAE

Ball End L-keys



Metric

Ball End L-keys



- ◆ 20% Longer keys for hard to reach fasteners
- ◆ Works smoothly for up to 25° angles chamfered ball end
- ◆ Exact fit precision machined tip for reduced cam-out
- ◆ Chrome-plated satin finish for corrosion protection

Wiha exclusive ErgoStar holder works by turning the largest L-key to turn all keys 90° for clear and unimpeded selection and includes the size marked on the holder for easy identification



13 Piece | ErgoStar® L-key Set

Model #66988

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



9 Piece | ErgoStar® L-key Set

Model #66996

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm



22 Piece | ErgoStar® L-key Sets

Model #66982

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm



► L-key Foam Tray Set Ball End Hex & TORX®



25°
angle for improved
access

Premium
Quality
Tool Steel



15.5" x 11" x 1.25"
Modular laminated foam storage tray


Wiha excels at keeping tools systematically organized. Each tool finds its designated spot, enhancing efficiency and reducing the time spent searching for specific items.



Fast Auto Open
Key Holder



Custom-fit compartments with
finger-recesses for easy tool
retrieval



Durable tri-layer laminated foam
tray for professional tool storage



**35 Piece | ErgoStar® L-key Foam
Tray Set in MM/SAE/TORX®**

Model #66979

9 Piece | Metric Hex L-keys 1.5-10mm
13 Piece | SAE Hex L-keys .050 - 3/8"
13 Piece | TORX® L-keys T5-T45

Chrome Finish L-key Sets Ball End



25°
angle for
improved
access

Premium
Quality
Tool Steel

Exact Fit
Precision
Machined
Tips



SAE


Chrome Finish L-keys

Metric

Chrome Finish L-keys



Ideal for fastening screws in
difficult-to-access spots and fastening
into horizontal, inclined or deep tapped
blind holes



**6 Piece | Ball End
Chrome Finish MM L-key Set**

Model #66995

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm



**11 Piece | Ball End
Chrome Finish MM L-key Set**

Model #66998

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0,
7.0, 8.0, 9.0, 10.0mm



**13 Piece | Ball End Chrome
Finish SAE L-key Set**

Model #36998

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8,
9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



**9 Piece | Ball End Chrome
Finish Metric L-key Set**

Model #66994

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0,
8.0, 10.0mm



**22 Piece | Chrome
Finish L-key Sets**

Model #66993

13Pc. SAE Hex | .050 - 3/8"
9Pc. Metric Hex | 1.5-10.0mm

► Nickel Finish L-key Sets Long & Short Arm Hex



Premium
Quality
Tool Steel

Exact Fit
Precision
Machined
Tips

SAE
Metric



Chamfered hexagonal ends slide into fasteners easily, reducing wear on wrenches and fastener heads.



Long Arm

Nickel Finish L-keys



Short Arm

Nickel Finish L-keys

► L-key Sets Short Arm Hex



**13 Piece | Nickel Finish
Short Arm SAE L-key Set**

Model #35194

SAE | .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64,
5/32, 3/16, 7/32, 1/4, 5/16, 3/8"




Wiha exclusive ErgoStar holder works by turning the largest L-key to turn all keys 90° for clear and unimpeded selection and includes the size marked on the holder for easy identification



**13 Piece | Nickel Finish
Long Arm SAE L-key Set**

Model #35295

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8,
9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



**9 Piece | Nickel Finish
Long Arm Metric L-key Set**

Model #35297

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0,
8.0, 10.0mm



**9 Piece | Nickel Finish
Short Arm Metric L-key Set**

Model #35191

MM | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

NO HASSLE
GUARANTEE



Black Finish L-key Sets Ball End



25°
angle for
improved
access

Premium
Quality
Tool Steel

Exact Fit
Precision
Machined
Tips



SAE

Black Finish L-keys

Metric

Black Finish L-keys



Ideal for fastening screws in
difficult-to-access spots and fastening
into horizontal, inclined or deep tapped
blind holes



**6 Piece | Ball End Black
Finish Metric L-key Set**

Model #36992

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm



**13 Piece | Ball End Black
Finish SAE L-key Set**

Model #36991

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8,
9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



**9 Piece | Ball End Black
Finish Metric L-key Set**

Model #36990

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0,
8.0, 10.0mm



**22 Piece | MagicRing®
Screw Holding L-key Sets**

Model #36995

SAE Hex | .050, 1/16, 5/64, 3/32, 7/64, 1/8,
9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Metric Hex | 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0,
8.0, 10.0mm


L-key Sets Short Arm Hex



5 Pc. | Short Arm SAE L-keys

Model #35393

SAE Hex | .028, .035, .050, 1/16, 5/64"



5 Pc. | Short Arm MM L-keys

Model #35392

Metric Hex | 0.7, 0.9, 1.3, 1.5, 2.0mm

► Dual Drive T-handles

Hex



25°
angle for
improved
access

Premium
Quality
Tool Steel



SAE

Chrome &
Black Finish

Metric

Chrome &
Black Finish



10 Piece | SoftGrip Dual Drive T-handle Set

Model #54097 * Standard Hex - No Ball

Ball End SAE Hex | 3/32*, 7/64*, 1/8*, 9/64*,
5/32, 3/16, 7/32, 1/4, 5/16, 3/8" - Chrome Finish



11 Piece | SoftGrip Dual Drive Black Finish T-handle Set

Model #33494 * Standard Hex - No Ball

Ball End SAE Hex | 5/64*, 3/32*, 7/64*, 1/8*,
9/64*, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8" - Black Finish



8 Piece | SoftGrip Dual Drive T-handle Set

Model #54095 * Standard Hex - No Ball

Ball End Metric Hex | 2.0*, 2.5*, 3.0*, 4.0,
5.0, 6.0, 8.0, 10.0mm - Chrome Finish



8 Piece | SoftGrip Dual Drive Black Finish T-handle Set

Model #33496 * Standard Hex - No Ball

Ball End Metric Hex | 2.0*, 2.5*, 3.0*, 4.0, 5.0,
6.0, 8.0, 10.0mm - Black Finish



15.5" x 11" x 1.25"
Modular laminated foam storage tray



8 Piece | Dual Drive Metric T-handle Foam Tray Set

Model #54079 - Chrome Finish

METRIC | 2, 2.5, 3, 4, 5, 6, 8, 10mm



10 Piece | Dual Drive SAE T-handle Foam Tray Set

Model #54081 - Chrome Finish

SAE | 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 3/32,
7/64, 1/8, 9/64"



8 Piece SoftGrip Dual Drive T-handle Set in Stand

Model #33489 * Standard Hex - No Ball

Metric Hex | 2.0*, 2.5*, 3.0*, 4.0, 5.0,
6.0, 8.0, 10.0mm - Black Finish

8 Piece SoftGrip Dual Drive T-handle Set in Stand

Model #33489 * Standard Hex - No Ball

SAE Hex | 1/8*, 9/64*, 5/32, 3/16, 7/32, 1/4,
5/16, 3/8" - Black Finish

8 Piece | SoftGrip Dual Drive Ball End T-handle Set in Stand

Model #54094 * Standard Hex - No Ball

SAE Hex | 1/8*, 9/64*, 5/32, 3/16, 7/32, 1/4,
5/16, 3/8" - Chrome Finish

8 Piece | SoftGrip Dual Drive Ball End T-handle Set in Stand

Model #54092 * Standard Hex - No Ball

Metric Hex | 2.0*, 2.5*, 3.0*, 4.0, 5.0,
6.0, 8.0, 10.0mm - Chrome Finish

ErgoStar® TORX®




**TORX®
Ball End**



**Premium
Quality
Tool Steel**



**Exact Fit
Precision
Machined
Tips**



Ball End TORX®

Black Finish L-keys



TORX®

Rust-free Chrome-plated L-keys



Wiha exclusive ErgoStar holder works by turning the largest L-Key to turn all keys 90° for clear and unimpeded selection and includes the size marked on the holder for easy identification



- ◆ 20% Longer keys for hard to reach fasteners
- ◆ Ball End for fastener interlock of up to 25°
- ◆ Exact fit precision machined tip for reduced cam-out
- ◆ Chrome-plated satin L-keys delivers extreme durability and long-lasting corrosion protection



**13 Piece | ErgoStar®
Black Finish L-key Set**

Model #36689

Ball End TORX® | T5, T6, T7, T8, T9,
T10, T15, T20, T25, T27, T30, T40, T45



Rust-free

**13 Piece | ErgoStar®
Chrome-plated Satin L-key Set**

Model #36693

TORX® | T5, T6, T7, T8, T9, T10, T15, T20, T25,
T27, T30, T40, T45



**NO HASSLE
GUARANTEE**



► L-key Sets TORX® Long Arm Black Finish



**Exact Fit
Precision
Machined
Tips**

**Premium
Quality
Tool Steel**




**MagicSpring®
Holds Screws tight**



TORX® | TORXPlus® | MagicSpring®

Black Finish L-keys



**10 Piece | Long Arm
Black Finish L-key Set**

Model #36698

TORX® | T6, T7, T8, T9, T10, T15, T20,
T25, T27, T30



**7 Piece | Long Arm
Black Finish L-key Set**

Model #36690

TORXPlus® | IP6, IP7, IP8, IP9, IP10, IP15, IP20



**7 Piece | Long Arm
Black Finish L-key Set**

Model #37190

MagicRing® | T6, T7, T8, T9, T10, T15, T20



**13 Piece | Long Arm
Black Finish L-key Set**

Model #36699


TORX® | T5, T6, T7, T8, T9, T10, T15, T20, T25,
T27, T30, T40, T50



**9 Piece | Long Arm
Black Finish L-key Set**

Model #36691

TORXPlus® | IP8, IP9, IP10, IP15, IP20, IP25,
IP27, IP30, IP40



**10 Piece | Long Arm
Black Finish L-key Set**

Model #37192

MagicRing® | T6, T7, T8, T9, T10, T15, T20,
T25, T27, T30

► L-key Sets TORX® Short Arm Black Finish



Exact Fit
Precision
Machined
Tips

Premium
Quality
Tool Steel



TORX® | TORXPlus® | Security

Black Finish L-keys

- ◆ Short arm for easy access
- ◆ Exact fit precision machined tip for reduced cam-out
- ◆ Black oxide finish L-keys delivers extreme durability and long-lasting corrosion protection



7 Piece | Long Arm Black Finish L-key Set

Model #36392

TORX® | T6, T7, T8, T9, T10, T15, T20



9 Piece | Long Arm Black Finish L-key Set

Model #36394

TORX® | T8, T9, T10, T15, T20, T25, T27, T30, T40



9 Piece | Short Arm Black Finish L-key Set

Model #36199

TORXPlus® | IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40



9 Piece | Short Arm Black Finish L-key Set

Model #36393

Security TORX® | T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

► Dual Drive T-handles Soft Grip



Premium
Quality
Tool Steel

Exact Fit
Precision
Machined
Tips



TORX®

Chrome Finish T-handles



15.5" x 11" x 1.25"

Modular laminated
foam storage tray

Each tool finds its designated spot, enhancing efficiency
and reducing the time spent searching for specific items.

- ◆ Soft comfort grip for maximum torque
- ◆ Chrome finish gives best corrosion resistance
- ◆ Through hardened for extreme wear resistance



**7 Piece | Soft Grip
Dual Drive T-handle Set**

Model #36497

TORX® | T10, T15, T20, T25, T27, T30, T40



**7 Piece | Dual Drive TORX®
T-handle Foam Tray Set**

Model #36489

TORX® | T10, T15, T20, T25, T27, T30, T40



**NO HASSLE
GUARANTEE**



Quick Reference Guide

Insulated 1000V Hex L-keys

WIHA	Description	Order Multiples
13650	INS MM HEX L-KEY 1.5MM	1
13651	INS MM HEX L-KEY 2.0MM	1
13652	INS MM HEX L-KEY 2.5MM	1
13653	INS METRIC HEX L-KEY 3MM	1
13654	INS METRIC HEX L-KEY 4MM	1
13655	INS METRIC HEX L-KEY 5MM	1
13656	INS METRIC HEX L-KEY 6MM	1
13657	INS METRIC HEX L-KEY 12MM	1
13658	INS METRIC HEX L-KEY 8MM	1
13659	INS METRIC HEX L-KEY 10MM	1
13670	INS HEX L-KEY 1/16"	1
13671	INS HEX L-KEY 5/64"	1
13672	INS HEX L-KEY 3/32"	1
13673	INS HEX L-KEY 7/64"	1
13663	INS SAE HEX L-KEY 1/8"	1
13665	INS SAE HEX L-KEY 5/32"	1
13666	INS SAE HEX L-KEY 3/16"	1
13667	INS SAE HEX L-KEY 7/32"	1
13668	INS SAE HEX L-KEY 1/4"	1
13669	INS SAE HEX L-KEY 5/16"	1
13662	INS SAE HEX L-KEY 3/8"	1
13664	INS SAE HEX L-KEY 1/2"	1

Short Arm Nickel-Plated Hex L-keys

WIHA	Description	Order Multiples
35101	1.5MM HEX KEY NICKEL SHORT 10PK	3
35102	2MM HEX KEY NICKEL SHORT 10PK	3
35103	2.5MM HEX KEY NICKEL SHORT 10PK	3
35105	3MM HEX KEY NICKEL SHORT 10PK	3
35106	4MM HEX KEY NICKEL SHORT 10PK	3
35107	5MM HEX KEY NICKEL SHORT 10PK	3
35109	6MM HEX KEY NICKEL SHORT 10PK	3
35110	8MM HEX KEY NICKEL SHORT 10PK	3
35111	.050 HEX KEY NICKEL SHORT 10PK	3
35113	10MM HEX KEY NICKEL SHORT 10PK	3
35114	1/16 HEX KEY NICKEL SHORT 10PK	3
35115	5/64 HEX KEY NICKEL SHORT 10PK	3
35117	3/32 HEX KEY NICKEL SHORT 10PK	3
35118	7/64 HEX KEY NICKEL SHORT 10PK	3
35119	1/8 HEX KEY NICKEL SHORT 10PK	3
35121	9/64 HEX KEY NICKEL SHORT 10PK	3
35122	5/32 HEX KEY NICKEL SHORT 10PK	3
35123	3/16 HEX KEY NICKEL SHORT 10PK	3
35125	7/32 HEX KEY NICKEL SHORT 10PK	3
35126	1/4 HEX KEY NICKEL SHORT 10PK	3
35127	5/16 HEX KEY NICKEL SHORT 10PK	3
35129	3/8" HEX KEY NICKEL SHORT 10PK	3

Short Arm Black Finish Hex L-keys

WIHA	Description	Order Multiples
35303	1.3MM HEX LKEY SHORT BLACK	10
35304	1.5MM HEX LKEY SHORT BLACK	10
35305	2MM HEX L-KEY SHORT BLACK	10
35306	2.5MM HEX L-KEY SHORT BLACK	10
35307	3MM HEX L-KEY SHORT BLACK	10
35308	4MM HEX L-KEY SHORT BLACK	10
35309	5MM HEX L-KEY SHORT BLACK	10
35310	6MM HEX L-KEY SHORT BLACK	10
35312	8MM HEX L-KEY SHORT BLACK	10
35314	10MM HEX L-KEY SHORT BLACK	10

Long Arm Nickel-Plated Hex L-keys

WIHA	Description	Order Multiples
35423	1.5MM HEX KEY NICKEL LONG 10PK	3
35424	2MM HEX KEY NICKEL LONG 10PK	3
35425	2.5MM HEX KEY NICKEL LONG 10PK	3
35404	3MM HEX KEY NICKEL LONG 10PK	3
35405	4MM HEX KEY NICKEL LONG 10PK	3
35406	5MM HEX KEY NICKEL LONG 10PK	3
35407	6MM HEX KEY NICKEL LONG 10PK	3
35408	8MM HEX KEY NICKEL LONG 10PK	3
35409	10MM HEX KEY NICKEL LONG 10PK	3
35410	.050 HEX LKEY NICKEL LONG 10PK	3
35411	1/16 HEX L-KEY NICKEL LONG 10PK	3
35412	5/64 HEX L-KEY NICKEL LONG 10PK	3
35413	3/32 HEX L-KEY NICKEL LONG 10PK	3
35414	7/64 HEX LKEY NICKEL LONG 10PK	3
35415	1/8 HEX L-KEY NICKEL LONG 10PK	3
35416	9/64 HEX LKEY NICKEL LONG 10PK	3
35417	5/32 HEX LKEY NICKEL LONG 10PK	3
35418	3/16 HEX LKEY NICKEL LONG 10PK	3
35419	7/32 HEX LKEY NICKEL LONG 10PK	3
35420	1/4 HEX L-KEY NICKEL LONG 10PK	3
35421	5/16 HEX LKEY NICKEL LONG 10PK	3
35422	3/8 HEX L-KEY NICKEL LONG 10PK	3

Short Arm TORXPlus® L-keys

WIHA	Description	Order Multiples
36108	TORXPLUS LKEY IP8X44MM	10
36109	TORXPLUS LKEY IP9X48MM	10
36110	TORXPLUS LKEY IP10X51MM	10
36115	TORXPLUS LKEY IP15X54MM	10
36120	TORXPLUS LKEY IP20X57MM	10
36125	TORXPLUS LKEY IP25X60MM	10
36127	TORXPLUS LKEY IP27X63MM	10
36130	TORXPLUS LKEY IP30X70MM	10
36140	TORXPLUS LKEY IP40X76MM	10

Short Arm TORX® L-keys

WIHA	Description	Order Multiples
36306	TORX L-KEY T6X38MM	10
36307	TORX L-KEY T7X42MM	10
36308	TORX L-KEY T8X44MM	10
36309	TORX L-KEY T9X48MM	10
36303	TORX L-KEY T10X51MM	10
36315	TORX L-KEY T15X54MM	10
36304	TORX L-KEY T20X57MM	10
36325	TORX L-KEY T25X60MM	10
36327	TORX L-KEY T27X67MM	10
36312	TORX L-KEY T30X70MM	10
36340	TORX L-KEY T40X76MM	10
36345	TORX L-KEY T45X82MM	10
36355	TORX L-KEY T55X108MM	10
36360	TORX L-KEY T60X120MM	10

Sort Arm Security TORX® L-keys

WIHA	Description	Order Multiples
36323	TORX SECURITY L-KEY T8s	10
36326	TORX SECURITY L-KEY T9s	10
36328	TORX SECURITY L-KEY T10s	10
36311	TORX SECURITY L-KEY T15s	10
36332	TORX SECURITY L-KEY T20s	10
36335	TORX SECURITY L-KEY T25s	10
36337	TORX SECURITY L-KEY T27s	10
36339	TORX SECURITY L-KEY T30s	10
36342	TORX SECURITY L-KEY T40s	10
36346	TORX SECURITY L-KEY T45s	10

Long Arm TORXPlus® L-keys

WIHA	Description	Order Multiples
36606	TORXPLUS L-KEY IP6X66MM	10
36607	TORXPLUS L-KEY IP7X71MM	10
36608	TORXPLUS L-KEY IP8X75MM	10
36609	TORXPLUS L-KEY IP9X80MM	10
36610	TORXPLUS L-KEY IP10X85MM	10
36615	TORXPLUS L-KEY IP15X90MM	10
36620	TORXPLUS L-KEY IP20X96MM	10
36625	TORXPLUS L-KEY IP25X102MM	10
36627	TORXPLUS L-KEY IP27X108MM	10
36630	TORXPLUS L-KEY IP30X116MM	10
36640	TORXPLUS L-KEY IP40X124MM	10

Long Arm Ball End TORX® L-keys

WIHA	Description	Order Multiples
36656	T9 BALL END TORX L-KEY	10
36632	T10 BALL END TORX L-KEY	10
36633	T15 BALL END TORX L-KEY	10
36634	T20 BALL END TORX L-KEY	10
36657	T25 BALL END TORX L-KEY	10
36658	T27 BALL END TORX L-KEY	10
36637	T30 BALL END TORX L-KEY	10
36638	T40 BALL END TORX L-KEY	10
36639	T45 BALL END TORX L-KEY	10

Long Arm TORX® L-keys

WIHA	Description	Order Multiples
36645	T5 TORX LONG KEY	10
36646	T6 TORX LONG KEY	10
36647	T7 TORX LONG KEY	10
36648	T8 TORX LONG KEY	10
36649	T9 TORX LONG KEY	10
36650	T10 TORX LONG KEY	10
36651	T15 TORX LONG KEY	10
36652	T20 TORX LONG KEY	10
36653	T25 TORX LONG KEY	10
36654	T27 TORX LONG KEY	10
36655	T30 TORX LONG KEY	10
36659	T40 TORX LONG KEY	10
36661	T50 TORX LONG KEY	10

Long Arm Ball End Black Finish L-keys

WIHA	Description	Order Multiples
36904	1.5X89MM BALL HEX LKEY BLK	10
36908	2.0X99MM BALL HEX LKEY BLK	10
36912	2.5x111MM BALL HEX LKEY BLK	10
36916	3x125MM BALL HEX LKEY BLK	10
36920	4X138MM BALL HEX LKEY BLK	10
36924	5x158MM BALL HEX LKEY BLK	10
36928	6x178MM BALL HEX LKEY BLK	10
36936	8x198MM BALL HEX LKEY BLK	10
36944	10x221MM BALL HEX LKEY BLK	10
36945	.050x71MM BALL HEX LKEY BLK	10
36946	1/16x78MM BALL HEX LKEY BLK	10
36947	5/64x86MM BALL HEX LKEY BLK	10
36950	3/32x98MM BALL HEX LKEY BLK	10
36952	7/64x108MM BALL HEX LKEY BLK	10
36953	1/8x118MM BALL HEX LKEY BLK	10
36955	9/64x132MM BALL HEX LKEY BLK	10
36956	5/32x144MM BALL HEX LKEY BLK	10
36959	3/16x158MM BALL HEX LKEY BLK	10
36962	7/32x164MM BALL HEX LKEY BLK	10
36965	1/4x172MM BALL HEX LKEY BLK	10
36968	5/16x181MM BALL HEX LKEY BLK	10
36971	3/8x191MM BALL HEX LKEY BLK	10

Long Arm Ball End Chrome Finish L-keys

WIHA	Description	Order Multiples
66904	1.5MM BALL HEX LKEY CHROME	10
66908	2MM BALL HEX LKEY CHROME	10
66912	2.5MM BALL HEX LKEY CHROME	10
66918	3MM BALL HEX LKEY CHROME	10
66922	4MM BALL HEX LKEY CHROME	10
66926	5MM BALL HEX LKEY CHROME	10
66930	6MM BALL HEX LKEY CHROME	10
66937	8MM BALL HEX LKEY CHROME	10
66938	10MM BALL HEX LKEY CHROME	10
66945	.050 BALL HEX LKEY CHROME	10
66946	1/16 BALL HEX LKEY CHROME	10
66947	5/64 BALL HEX LKEY CHROME	10
66950	3/32 BALL HEX LKEY CHROME	10
66952	7/64 BALL HEX LKEY CHROME	10
36949	1/8 BALL HEX LKEY CHROME	10
36954	5/32 BALL HEX LKEY CHROME	10
36957	3/16 BALL HEX LKEY CHROME	10
36958	7/32 BALL HEX LKEY CHROME	10
36960	1/4 BALL HEX LKEY CHROME	10
36961	5/16 BALL HEX LKEY CHROME	10
36963	3/8 BALL HEX LKEY CHROME	10
36964	9/64 BALL HEX LKEY CHROME	10

Long Arm MagicSpring TORX® L-keys

WIHA	Description	Order Multiples
37101	TORX MAGICSPRING L-KEY T6	3
37102	TORX MAGICSPRING L-KEY T7	3
37103	TORX MAGICSPRING L-KEY T8	3
37109	TORX MAGICSPRING L-KEY T9	3
37110	TORX MAGICSPRING L-KEY T10	3
37115	TORX MAGICSPRING L-KEY T15	3
37120	TORX MAGICSPRING L-KEY T20	3
37125	TORX MAGICSPRING L-KEY T25	3
37127	TORX MAGICSPRING L-KEY T27	3
37130	TORX MAGICSPRING L-KEY T30	3

Screw Holding

Long Arm MagicRing Hex L-keys

WIHA	Description	Order Multiples
66916	MAGICRING 3MM HEX LKEY	10
66920	MAGICRING 4MM HEX LKEY	10
66924	MAGICRING 5MM HEX LKEY	10
66928	MAGICRING 6MM HEX LKEY	10
66936	MAGICRING 8MM HEX LKEY	10
66944	MAGICRING 10MM HEX LKEY	10
66953	MAGICRING 1/8 HEX LKEY	10
66955	MAGICRING 9/64 HEX LKEY	10
66956	MAGICRING 5/32 HEX LKEY	10
66959	MAGICRING 3/16 HEX LKEY	10
66962	MAGICRING 7/32 HEX LKEY	10
66965	MAGICRING 1/4 HEX LKEY	10
66968	MAGICRING 5/16 HEX LKEY	10
66971	MAGICRING 3/8 HEX LKEY	10

Screw Holding



No Hassle Guarantee

Wiha branded tools are regarded as the most durable, best designed and highly innovative products around. Our tools are used by demanding professional tradespeople and tool aficionados alike. They are meant to be used and utilized often. However, if you are not happy for any reason return them within 12 months of purchase with proof of purchase and we will **Repair or Replace**.

Rest assured, if for some reason there is a defect in material or workmanship we will replace your tool free of charge for as long as you own the tool.

Failures due to misuse, abuse or normal wear and tear are not covered by this guarantee. We stand by our products with what we believe is the best **No Hassle Guarantee** in the industry.

Exclusions

Wiha Tools has the right to exclude Bits, Tweezers and Ceramic Screwdrivers. These products are either consumable or wear easily.

All torque tools are designed for 5,000 cycles or 1 year (whichever comes first). If a tool becomes out of specification within that period Wiha Tools will **Repair or Replace**. Visit www.wihatools.com to learn more about our Torque Control Service Program.

Legal

Some areas do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This guarantee gives you specific rights, and you may also have other rights, which vary, from state to state, province to province, or country to country.

This **No Hassle Guarantee** is the sole and exclusive guarantee for the Willi Hahn Corporation dba Wiha Tools. No employee, agent, dealer, or other person is authorized to alter this guarantee or make any other guarantees on behalf of Wiha Tools.

Willi Hahn Corporation USA | Attn: No Hassle Guarantee
516 East 7th Street | Monticello, MN 55362



USA

516 East 7th Street
Monticello, MN 55362
(800) 494-6104 | (763) 295-6591
fax: (800) 494-7456 | (763) 295-6598
cservice@wihatools.com
www.wihatools.com

CANADA

(866) 494-0096 | (763) 295-6591
fax: (763) 295-6598
canada@wihatools.com
www.wihatools.com

#99937 L-key Catalog 2026
Subject to change without notice

©2026 Willi Hahn Corporation

®Torx is a registered trademark of
Acument Intellectual Properties LLC.



99002 Screwdrivers Catalog



99001 TorqueControl Catalog



99919 Insulated Catalog



99951 Bits Catalog



91327 Top Sellers Catalog

Distributed By:



Scan QR Code to see
our catalogs online!



99986 Best of Wiha