FILE NO.	BB-CD-805-03

NOTES:

1. MAT'L: COPPER, STOCK TKN .031 ±001
   PLATING: ELECTRO-TIN (.0003 MIN.)
2. TIN-PLATED BRASS FUNNEL FERRULE
3. NYLON INSULATION (BLUE)
4. "UL" LISTING #E32244
   "CSA" LISTING 18689



MWID = MAX. WIRE INSULATION DIA.

WIRE SIZE: 16-14. AWG.
1.0-2.5 MM²

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	"D" ±005			AVAILABLE STUD SIZES	
BB-8716	.310	.261	.886	.139			08 (.173 ±005)	
BB-8717	.330	.261	.934	.156			10 (.198 ±005)	

DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED			REFERENCE	SCALE: NTS	DATE	TITLE: SNAP SPADE SHORT TONGUE TERMINAL. AVIKRIMP-800 SERIES	ETC molex INCORPORATED
FRAC.	DEC.	ANG.		DRWN. BY: GZ	4-5-85		
±	±	±		CHKD. BY:			DWG. NO. A CUSTOMER DWG.
				APPRD. BY:			