REV.	DATE	DESCRIPTION	BY	C'K'D'
00	28/09/07	FIRST ISSUE	R Ch	
A	16/08/10	Reverse dimension E max	R Ch	

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.



Catalog Number	Dimensions				
	A±0.2	B±0.15	C±0.15	D±0.2	E max
UTG6103PN	21.6	12.2	10.9	19.1	31.6
UTG6103SN	21.6	12.2	10.9	19.1	26.8

MATERIAL :

BODY : GLASS-FILLED POLYAMIDE; COLOUR BLACK UL94-V0.
BAYONET RING : CUZN ALLOY NICKEL PLATED.

PERFORMANCE CHARACTERISTICS :

OPERATING TEMPERATURE : -55°C TO +125°C.
INSULATION RESISTANCE : 5000 M Ohm MIN.
TEST POTENTIAL : 2000 VAC EFF.
DESIGN : ACCORDING TO VDE 0110 GROUP C/220V.

NOTES :

1. CONNECTOR ACCEPTS SIZE 16 STRIP FORMED, MACHINED AND SUBMINIATURE COAXIAL PIN AND SOCKET CONTACTS.
2. CONTACTS TO BE ORDERED SEPARATELY - SEE DRAWINGS BSA 060291, BSA 060101, BSA 060152

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90
INT. ST.	10 11	12 13	14 18	20 31	32 33 34	38 39	40 42	43 44	45 46	48 56	70 72	73 75	76 81	82 83 84 88

1DEC ±0,2 1DEC
2DEC ±0,1 2DEC
ANGLES ±1' HOEKEN

WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.

ALL DIMENSIONS IN MM

ALLE AFMETINGEN IN MM

APPR.	DATE	SIGN.
DRAFT	28/09/07	ROUILLARD
CHECKED		
PROD. MGR.		
PR.ENG.MGR.		
PR.MGT.MGR.		

REFERENCES / REFERENTIES

PLUG UTG BANTAM SIZE 10-3

CAT. No. UTG6103*N

SOURIAU
Connection Technology

SOURIAU
Route Nationale 23
72470 CHAMPAGNE

SCALE

BS-A-202360-003

DRAWING NR. CUSTOMER DRAWING REVISION

BS,A ,202360,003