



A range of high quality UK manufactured phono plugs made from machined brass with various plating options.

- Spring centre contacts for good electrical contact with large solder bucket.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification
- Attractive body styling
- Maximum cable size 5.5mm

Rating -  
 Rated Current: 5A.  
 Rated Voltage: 50V  
 Insulation resistance – 100MΩ at 500 Vdc

### Dimensions



|                |                                      |
|----------------|--------------------------------------|
| Material       |                                      |
| Centre contact | Brass<br>flash gold plated           |
| Ground Contact | Brass,<br>flash gold plated          |
| Insulation     | Noryl SE1                            |
| Cable clamp    | Brass,<br>flash gold finish          |
| Spring         | Spring steel,<br>black chrome plated |
| Cap            | Brass,<br>black chrome plated        |

| Deltron Part No | Description   |
|-----------------|---|
| 342-0000        | FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING                  |
| 342-0100        | FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (BLACK ID RING)  |
| 342-0200        | FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (BLUE ID RING)   |
| 342-0500        | FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (RED ID RING)    |
| 342-0600        | FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (WHITE ID RING)  |
| 342-0700        | FLASH GOLD SOCKET ASSY/BLACK CHROME CAP & SPRING (YELLOW ID RING) |

Tel No. +44(0)1724 273200 Website www.dem-uk.com

PROPRIETARY AND CONFIDENTIAL  
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF  
 ALPHA 3 MANUFACTURING.  
 ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF  
 ALPHA 3 MANUFACTURING IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN MILLIMETRES  
 LINEAR TOLERANCE:  
 NO DECIMAL PLACES ±0.5mm  
 1 DECIMAL PLACE ±0.25mm  
 2 DECIMAL PLACES ±0.125mm  
 ANGULAR TOLERANCE: ±1°

FINISH PROFESSIONAL PHONO  
 LINE SOCKET

DEBURR AND BREAK  
 SHARP EDGES

DRAWN BY  
 APPROVED BY

SPB  
 WC

TITLE GENERAL SPECIFICATION  
 342 SERIES  
 SOCKET

THIRD ANGLE PROJECTION

SHEET 1 OF 1

DRAWING NO.  
 342 SERIES

ISSUE **03**  
 Release



DEM Manufacturing, Deltron Emcon House  
 Hargreaves Way, Sawcliffe Ind. Park,  
 Scunthorpe, North Lincolnshire, DN15 8RF, UK

IF IN DOUBT ASK  
 DO NOT SCALE DRAWING

MATERIAL SEE NOTE



SCALE 1:1  
 A4