THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| H | — |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | A | INITIAL RELEASE | 29NOV2013 | YC | BvH |
| | A1 | ECR-14-015049 | 13OCT2014 | GSK | BvH |

NOTES:
Tolerances cable lengths:

| | |
|---|---|
| 0m to 0.5m | +30mm |
| 0.5m to 1.0m | +50mm |
| 1.0m to 3.0m | +100mm |
| < 3.0m | +1.5% |




| TECHNICAL DATA | |
|---|---|
| Operating voltage | max. 30 V AC/DC |
| Operating current per contact | max. 4 A |
| Locking of ports | Screw thread M8/M12 x 1 mm (recommended torque 0.4/0.6 Nm), self-securing |
| Protection | IP65 and IP67 when plugged and screwed down (EN 60529) |

| PUR CABLE | |
|---|---|
| No./diameter of wires | 4 x 0.25 mm² |
| Wire isolation | PP (br, wh, bl, bk) |
| C-track properties | 5 million |
| Jacket | PUR (UL/CSA) |
| Outer diameter | approx. 4.4 mm |
| Bend radius (moving) | 10 x outer diameter |
| Temperature range (fixed) | -40...+80 °C |
| Temperature range (mobile) | -25...+80 °C |

| PVC CABLE | |
|---|---|
| No./diameter of wires | 4 x 0.25 mm² |
| Wire isolation | PVC (br, wh, bl, bk) |
| C-track properties | |
| Jacket | PVC (UL/CSA) |
| Outer diameter | approx. 4.8 mm |
| Bend radius (moving) | 10 x outer diameter |
| Temperature range (fixed) | -30...+80 °C |
| Temperature range (mobile) | -5...+80 °C |

Contact Layout




Schematic diagram




| | LENGTH"L" | MATERIAL | JACKET COLOR | TE PN | DESCRIPTION | ITEM |
|---|---|---|---|---|---|---|
| 4 pos | 2.0mtr | PVC | Black | 1-2273111-5 | 4x22AWG PVC 2.0m | 10 |
| | 1.5mtr | | | 1-2273111-4 | 4x22AWG PVC 1.5m | 9 |
| | 1.0mtr | | | 1-2273111-3 | 4x22AWG PVC 1.0m | 8 |
| | 0.6mtr | | | 1-2273111-2 | 4x22AWG PVC 0.6m | 7 |
| | 0.3mtr | | | 1-2273111-1 | 4x22AWG PVC 0.3m | 6 |
| 4 pos | 2.0mtr | PUR | Black | 2273111-5 | 4x22AWG PUR 2.0m | 5 |
| | 1.5mtr | | | 2273111-4 | 4x22AWG PUR 1.5m | 4 |
| | 1.0mtr | | | 2273111-3 | 4x22AWG PUR 1.0m | 3 |
| | 0.6mtr | | | 2273111-2 | 4x22AWG PUR 0.6m | 2 |
| | 0.3mtr | | | 2273111-1 | 4x22AWG PUR 0.3m | 1 |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL -
FINISH -

DWN YATHISH.C 29NOV2013
CHK B.VELDHOVEN 29NOV2013
APVD A.VAN ZANDVOORT 29NOV2013
PRODUCT SPEC 108-19483
APPLICATION SPEC 114-32127
WEIGHT -

TE Connectivity

NAME M8 STRGT SOCKET TO M12 STRGT PLUG AA

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | 00779 | C-2273111 | — |

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV A1