



注記 NOTES

- 材質 MATERIAL  
ハウジング : 液晶ポリマーガラス充填、黒色、UL 94V-0  
HOUSING : LIQUID CRYSTAL POLYMER GLASS FILLED  
COLOR BLACK, UL94V-0  
ターミナル : 燐青銅 (t=0.15)  
TERMINAL : PHOSPHOR BRONZE (t=0.15)
- メッキ仕様 PLATING  
金メッキ 0.25マイクロメートル以上。(コンタクト部)  
GOLD 0.25MICROMETER MINIMUM (CONTACT AREA)  
金メッキ 0.4マイクロメートル以下。(テール部)  
GOLD 0.4MICROMETER MAXIMUM (TAIL AREA)  
下地メッキ : ニッケルメッキ 2.5マイクロメートル以上。  
UNDER-PLATING : NICKEL 2.5MICROMETER MINIMUM

3. 嵌合相手 : 55559 シリーズ  
MATES WITH : 55559 SERIES
4. テール平坦度は 0.1以下。  
TAIL COPLANARITY TO BE 0.1 MAXIMUM
5. パターン書き込み禁止エリア  
NO FOOT PRINT AREA.

5.5	7.7	54729-0241	24
3.5	5.7	54729-0161	16
B	A	MATERIAL NO.	CKT. NO.

DO NOT SCALE DRAWING

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	RELEASED/REVISED '04/02/04 EC NO. J2004-0314 DRWN: R.SUMIYA CHK: S.AIHARA APPR: M.SASAO	PROPOSED '01/04/11 EC NO. JC2001-0282 DRWN: M.HAYASHI CHK: T.ITO APPR: T.YAMAGUCHI	MATERIAL 材料 注記参照 SEE NOTES	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE --/--	MODEL NO. 54729-***1	DESIGN UNITS <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	DIMENSIONS: <input type="checkbox"/> mm <input type="checkbox"/> INCH <input checked="" type="checkbox"/> mm ONLY	SHT REV
					注記参照 SEE NOTES	10 UNDER 未満 ±0.2	DRAWN BY & DATE M.HAYASHI '01/04/11	TITLE: 0.5 B-To-B Rec Hsg Assy (Hg+=2mm)	MOLEX MOLEX INCORPORATED		
						10 OVER 以上 ±0.25	CHECKED BY & DATE T.ITO '01/04/11				
						30 OVER 以上 ±0.3	APPROVED BY & DATE T.YAMAGUCHI '01/04/11				
						ANGLE 角度 ±3°	CAD FILENAME 54729009.S01	MATERIAL NO. SEE CHART	DRAWING NO. SD-54729-009	SHEET NO. 1 OF 1	SIZE B
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.											EN-02J(097) MXJ-54