





EMA112-10
G3 MANAGED

FUNCTIONALITY	INPUT	OUTPUT	OPERATING TEMPERATURE
CURRENT, POWER, AND ENERGY METERING FOR INPUT AND OUTLET; OUTLET SWITCHING	NEMA 5-15P 10FT 14AWG / 3C POWERCORD	(16) NEMA 5-15R	32° TO 140° F 0° TO 60° C
MECHANICAL	**INPUT RATING**	**OUTPUT RATING**	**CERTIFICATIONS**
63.15" (1604mm) LENGTH 2.05" (52mm) WIDTH 2.56" (65mm) DEPTH ALUMINUM CHASSIS, BLACK	100-127V~ W+N+PE 12 A 50/60 Hz	100-127V~ 12A MAX PER OUTLET 12A MAX TOTAL	c UL us LISTED
CIRCUIT BREAKERS	**FILTER AND SPIKE/SURGE**	**ACCESSORIES**	**CONFIGURATION**
NONE	NONE	INCLUDED SPK012 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EMA6MA15ALC87AC

TITLE	ePDU G3 SPECIFICATION EMA112-10	DRAW	Deng Dai	2014-08-05
		DESIGN	Deng Dai	2014-08-11
DWG NO.	B9001-221420-00P	CHECKED	Deng Dai	2014-08-11
MATERIAL		SAFETY	Merry Sun	2014-08-11
COATING		APPROVED	VICKY SHEN	2014-08-11
UNITS	in[mm]	A3	SCALE 1:2	EATON ELECTRICAL SECTOR
SHEET	1/1			