DATE	ECO NO	DESCRIPTION	BY
Mar 31 1993	CDN 93015	———	A.K
	DCN 93025	Revise	A.K







IC TO BE SEATED



SECTION A–A





RECOMMENDED IC (REF)



FOOTPRINT

FOOTPRINT AS VIEWED LOOKING DOWN
FROM TOP OF SOCKET

Performance.

1. Insulation Resistance : 1000 MΩ min. at 500V.D.C
2. Dielectric Withstanding Voltage : 600 V.A.C (RMS)
3. Contact Resistance : 30 mΩ max. at 20 mV max.
4. Temperature Range : −40°C ～+150°C

P.NO	PART DESCRIPTION	MATERIAL	QTY	NOTE
④	CONTACT−(2)	Be Cu	10	PLATING : Au
③	CONTACT−(1)	Be Cu	10	PLATING : Au
②	BASE−20P	PEI	1	COLOR : BLACK
①	COVER−20P	PEI	1	COLOR : BLACK

GENERAL TOLERANCES
±0.3 (±.012)

UNIT	SCALE	ANGLE
mm (in.)	2/1	3rd.

DRAWN	/ /
CHECKED	/ /
APPROVED	/ /

WELLS JAPAN LIMITED
ウエルズ・ジャパン株式会社

TITLE
SOP 20P SOCKET

DWG NO.
652D0202211