RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	12/27'21	First release	PansLee
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				





SECTION VIEW:A-A





VIEW:D SC 3:1

ZTC 060 03 0 000 G

- 060: 60A
- 03: 3P
- 000: Any special item by customer request; @Mark
- G: RoHS compliant (lead<4%) In copper Alloy

序号/NO	名称/NAME	规格型号/SPECIFICATIONS	数量/Q.TY	材料/MATERIALS	备注/REMARK
5	导电片/BUS BAR	———	3	黄铜/BRASS (H59)	镀镍/NICKEL PLATING
4	M6 组合螺丝/SCREW	M6*12	6	钢/STEEL	镀环保彩锌/ZINC PLATING
3	ZTC 60 本体BODY	———	1	PC BLACK	UL94-V0
2	标记条/MARKER BAR	0.5*9*81.5	1	PVC WHITE	———
1	ZTC 60 透明盖/COVER	———	1	PC TRANSPARENT BLUE	UL94-V2

標準 / IEC STANDARD:	IEC60947-7-1
額定電壓 / RATED VOLTAGE :	660 V
額定電流 / CURRENT RATING:	60A
耐高壓 / WITHSTAND VOLTAGE:	2.5KV/Min
絶緣電阻 / INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 1000 V
工作溫度 / OPERATING TEMPERATURE RANG:	-20 °C ~+105°C
螺絲型號 / SCREW TYPE/扭力值 / TORQUE VALUE:	M6 /6.5 N.m Max.
線徑範圍 / WIRE RANGE:	2.5-10mm²
重點尺寸 / Critical dimension: ▲	

一般公差/TOLERANCES

尺寸/DIM(mm)	公差/TOL(mm)
0--10	±0.2
>10--20	±0.3
>20--30	±0.4
>30--40	±0.52
>40--50	±0.56
角度/ANGLE	±1°

Amphenol ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	ZTC 60-3P				
PART NO.	ZTC060030000G			DWG NO.	8ZTC0001-60
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		PansLee 2021.12.27	PansLee 2021.12.27	UNIT: mm	
				SCALE: NONE	
				SHEET: 01/01	REV.: B