1	2	3	3		4 5		
	5±0.2 A 04.2±0.15 A±0.05 A±0.05 A±0.05 A±0.05 A±0.05 A±0.05	PCB L	6 8.3 10.9 AYOUT - COMPONE TOLERANCE ± 0.0		MATERIAL INSULATOR: F FLAMABILITY COLOR: BLAC CONTACT MA CONTACT TYF PLATING: - CENTER PIN - CENTER PIN - SHUNT TERI - TIP SPRING: QUALITY CLA: ENVIRONMEN OPERATING T	RATING: UL94-V0 K TERIAL: COPPER ALLOY PE: STAMPED : GOLD TERMINAL: TIN MINAL: TIN TIN SS: 5000 MATING CYLCES	P
(0.4) 6.1 (0.4) 6.1 (0.4) 6.1 (0.4) SECTION A-A	-	Ø A XX PLUG INNER Ø PLUG OUTER Ø	1.0 02 1.05 ^{+0.10} 3.5±0.05	1.3 03 1.35 $^{+0.10}_{-0.00}$ 3.5±0.05	INSULATION F DIELECTRIC V CONTACT RE SOLDERING	TING: 2A LTAGE: 30 VDC RESISTANCE: >100 MΩ VITHSTANDING VOLTAGE: 500 VAC/ SISTANCE: 50 mΩ max FREE WAVE SOLDERING PROCESS	
DUNCE LA L	6	CIRCUIT DIAGRAM CIRCUIT DIAGRAM					C
RoHS Compliant G F E D C B A 08-SEP-14 PDF REV DATE	APPROVAL: RJ	<u>Ө</u> -	DLERANCE = ⁺ /_ 0.50 = ⁺ /_ 0.30 = ⁺ /_ 0.20	WÜRTH ELEKTR DESCRIPTION: DO WERI PART NO: 6	C POWER JACK - RIGHT AN		^{IZE} [

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	toHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE]
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONIK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	Ъ
В]	SCALE:			۲
A	10-SEP-14	PDF	QL]	SHEET: 1/1	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			

	1		2		3	4	5		F
			190 00 Bag (x5)		235 Box (x4)				A
				AR CONTRACT	× × × × Waterproo	1000 pcs/ba 5 bags/bc 5000 pcs/bc 4 boxes/car 20000 pcs/ca	ox ox rton		В
R	oHS Compliant			OEE 250	340				с
G F E D					GENERAL TOLERANCE .X = ⁺ /_ 0.2 .XX = ⁺ /_ 0.15				
C B A REV	23-JUL-14 DATE	PDF FILE	AS BY	APPROVAL: RJ	UNIT: MM SCALE: SHEET: 1/1 DRAW: AS	DESCRIPTION: DC POWER JACK - RIGHT AN WERI PART NO: 694 1xx 303 002	IGLED - THT - 1.0 & 1.3Ø	SIZE	D