TENMA®

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC–F005.DWG

REVISIONS

DOC. NO. SPC–F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1939	A	RELEASED	DCM	6/2/06	JWM	9/5/06	HO	9/5/06



Set of 8 Mini Clips: 2 Black, 2 Red, 1 Yellow, 1 Green, 1 Blue, 1 White



CE

SPECIFICATIONS:

- Contacts: BeCu, Gold Plated
- Snap-Locking Caps for Safety
- IEC Rating: 33 VAC / 70 VDC
- Voltage: 150 V (non-handheld)
- Current: 6 A
- Jacket Material: PVC
- Conductor Area: 0.40mm^2
- Wire Gauge, Approx.: 21 AWG
- Stranding, (# x mm): 104 x 0.07mm
- Wire OD: 0.079 [2.0]
- Working temperature: -20° to +80°C

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Dan McVicker	6/2/06
CHECKED BY:	DATE:
Jeff McVicker	9/5/06
APPROVED BY:	DATE:
Hisham Odish	9/5/06

DRAWING TITLE: 8 Piece Test Clip Lead Kit

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	76–004A	12M5887.dwg	A

SCALE: NTS | U.O.M.: Inches [mm] | SHEET: 1 OF 1