SYLVANIA Motto LED Light Fittings

- Indoor decorative LED lighting
- Low energy consumption
- Extremely long life
- Shock and vibration resistant
- No UV or IR radiation
- High colour saturation
- IP20 rated
- 2m cord on each unit

Lamp unit, ceiling plate, lumidriver and lumisplitter all sold separately.

Ceiling Plates

- Mono, duo and trio face plates available
- Mono (LxW):- 70x70mm
- Duo (LxW):- 140x70mm
- Trio (LxW):- 210x70mm
- Quad (LxW):- 140x140mm
- Lamp spacing (between centres): 70mm
- All in a brushed aluminium finish

Lumidriver

- Electronic constant current source
- Overload, short circuit and thermal protection
- Supplied with 1.5m cord and 3 pin mains plug
- IP44 rated
- 350MA, 1 to 6 x 1W LED or
- 700MA, 1 to 3 x 3W LED
- Passes 850°C glow wire test

Lumisplitter

- Plug and play system
- For easy connection of LED units to lumidrivers
- IP44 rated
- Passes 850°C glow wire test

Technical Data

Voltage	240V
Wattage	1W or 3W
Panel Cut-out Diameter	55mm
External Diameter	70mm
Depth	36mm

555491

Description	*Order Code*	*price each* 1+	+
1W LED Fittings			
Cool White	**LA03607**	~~15.99~~	— —
Warm White	**LA03609**	~~15.50~~	— —
Blue	**LA03611**	~~14.50~~	— —
3W LED Fittings			
Cool White	**LA03608**	~~29.11~~	— —
Warm White	**LA03610**	~~27.88~~	— —
Blue	**LA03612**	~~29.11~~	— —
Ceiling Plates - Square			
Mono	**LA03613**	~~8.17~~	~~7.75~~
Duo	**LA03614**	~~46.50~~	— —
Trio	**LA03615**	~~67.44~~	— —
Quad	**LA03616**	~~88.50~~	— —
Ceiling Plates - Round			
Mono	**LA03617**	~~23.50~~	— —
Duo	**LA03618**	~~46.50~~	— —
Lumidrivers			
350MA	**LA03619**	~~18.01~~	— —
700MA	**LA03620**	~~31.04~~	— —
Lumisplitters			
1 to 6 x 1W LED	**LA03621**	~~5.84~~	~~5.53~~
1 to 3 x 3W LED	**LA03622**	~~4.79~~	— —