DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE PROJECTION



NOTES

1. SNAP-IN POLARIZERS PN. 927636-2 OR 927637-2 CAN BE APPLIED.
2. THERE IS NO WINDOW FOR SNAP-IN POLARIZERS AT THIS END IN 10 AND 14 POS. HEADERS.
3. INDICATION OF FIRST POSITION.
4. THERE IS NO CENTER STAND-OFF IN 10-26 POS. HEADERS.
5. PARTNUMBER AND PROD.-DATE ON SUITABLE SURFACE X-828 588-X DD.MM.YY



RECOMMENDED PCB-HOLE PATTERN



(2) PIN-CONTACT	BRASS	MATING SIDE: 0,8µm AU OR 0,8µm AMP DURAGOLD® / OVER 1,27µm NI SOLDER SIDE: MIN. 3,0µm SN OVER 1,27µm NI
(1) HOUSING	GLASSFILLED POLYESTER	GREY
	COMPONENT NAME	MATERIAL	PLATING/COLOUR

VARIABLE CONNECTOR DIMENSIONS					NR. OF POSITIONS	PARTNUMBER
DIM. "E"	DIM. "D"	DIM. "C"	DIM. "B"	DIM. "A"		
100,6	90,4	96,5	86,4	78,7	64	6-828588-4
95,5	85,3	91,4	81,3	73,7	60	6-828588-0
82,8	72,6	78,7	68,6	61,0	50	5-828588-0
70,1	59,9	66,0	55,9	48,3	40	4-828588-0
62,5	52,3	58,4	48,3	40,6	34	3-828588-4
52,3	42,2	48,3	38,1	30,5	26	2-828588-6
44,7	34,5	40,6	30,5	22,9	20	2-828588-0
39,6	29,5	35,6	25,4	17,8	16	1-828588-6
37,1	26,9	33,0	22,9	15,2	14	1-828588-4
32,0	21,8	27,9	17,8	10,2	10	1-828588-0

LTR.	REVISION RECORD	DR.	CHK.	DATE
–	–	–	–	–
–	–	–	–	–
–	–	–	–	–
–	–	–	–	–
A1	PLATING DURAGOLD OR GOLD ALTERNATIVELY USABLE	MAH.	STRE.	02-JUL-03
A	BEMERKUNG (5) ERGAENZT	BLU	LAU	11.05.95
0	EH-0839-93	JvL	RV	29-11-93

DR.: J.v.LIEMPT DATE: 29-11-93
CHK.: R.VERSTIJNEN. DATE: –
APP.: L.V.SOEST. DATE: –

CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED
© COPYRIGHT 19– BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.
~~THIS DRAWING IS UNPUBLISHED~~
RELEASED FOR PUBLICATION – ,19 –

AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME
AMP-LATCH HEADER 180° VERSION WITH LATCHES.

DWG.No.	LOC.		SHEET	REV.LTR.
C-828588	A1	A3	1 OF 1	A1

F E D C B A

8 7 6 5 4 3 2 1