

DWG. NO.
SD-88732-9*00

F

D

A

C

B

DO NOT SCALE DRAWING

8 7 6 5 4 3 2 1

F

E

D


C

B

887329*00.S02.DGN

注記)
NOTES.

1. ケーブル構造
CABLE CONSTITUTION



WIRE COLOR (SIGNAL NAME)	接点 CONTACT NUMBER	
	USB-A	USB-B
RED (V)	#1	#1
WHITE (-DATA)	#2	#2
GREEN (+DATA)	#3	#3
BLACK (GND)	#4	#4
DRAIN WIRE	SHEEL	SHEEL

2. 部品構成
PART CONSTRUCTION

	部品名 PARTS NAME	材質 MATERIALS	処理 FINISH
①	TERMINAL	銅合金 COPPER ALLOY	接点部 : 金メッキ + パラジウムニッケル CONTACT AREA : GOLD + PALLADIUM-NICKEL
②	HOUSING	GLASS FILLED HEAT RESISTANT PLASTIC + GOLD FLASH COLOR : WHITE	—— # ——
③	USB-A FRONT SHELL	鋼 STEEL	下地 : 銅めっき、光沢 半田めっき UNDER PLATING : COPPER, LIGHT TIN PLATING
④	USB-A REAR SHELL	鋼 STEEL	下地 : 銅めっき、光沢 半田めっき UNDER PLATING : COPPER, LIGHT TIN PLATING
⑤	USB-B FRONT SHELL	鋼 STEEL	下地 : 銅めっき、光沢 半田めっき UNDER PLATING : COPPER, LIGHT TIN PLATING
⑥	USB-B REAR SHELL	鋼 STEEL	下地 : 銅めっき、光沢 半田めっき UNDER PLATING : COPPER, LIGHT TIN PLATING
⑦	CRIMP HOUSING	GLASS FILLED HEAT RESISTANT PLASTIC + GOLD FLASH COLOR : WHITE	—— # ——
⑧	OVER MOLD HOUSING	POLYVINYL CHLORIDE COLOR : FROST WHITE	—— # ——

EC NO.
DRWN:
CHK:
APPR:

EC NO.
DRWN:
CHK:
APPR:

EC NO.
DRWN:
CHK:
APPR:

EC NO.
DRWN:
CHK:
APPR:

RELEASED
EC NO. JD2000-0857
DRWN: YUKOJIMA '00/02/17
CHK: M.SASAO '00/02/17
APPR: HIKESUGI '00/02/17

DESCRIPTION
MATERIAL
材料
部品構成表参照
SEE PART CONSTRUCTION
FINISH
仕上
部品構成表参照
SEE PART CONSTRUCTION
WIRE RANGE
適用電線範囲
——
INS. RANGE
被覆外径
——

REV

GENERAL TOLERANCES:
(UNLESS SPECIFIED)
一般公差

10 UNDER
未満

±0.2

10 OVER 30 UNDER
以上 未満

±0.25

30 OVER
以上

±0.3

ANGLE 角度

±3°

SCALE
2-1

DESIGN UNITS
☒mm ☐INCH

DRAWN BY & DATE
Yu.Kojima '00/02/17

CHECKED BY & DATE
H. Sasaki '00/02/17

APPROVED BY & DATE
H. Sasaki '00/02/17

CAD FILENAME
887329*00.S02

☒THIRD ANGLE
PROJECTION

TITLE:
USB A-B I/O CABLE

MOLEX INCORPORATED

MATERIAL NO.
SEE CHART

DRAWING NO.
SD-88732-9*00

SHEET NO.
2 OF 2

DIMENSIONS:
☐mm ☐INCH ☒mm ONLY

SHT
REV

REVISE ON
CAD ONLY

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

SIZE
B

8 7 6 5 4 3 2