Model Name/Number	A3(E11K)	Color Available	Black/Silver
Weight	92 g	Dimensions	91.2 mm×56 mm×13 mm
Audio Input	3.5 mm stereo Jack	Headphone output	3.5 mm stereo Jack
Volume Control	ALPS Potentiometer	Bass Boost	1 Level
Drive ability	16~150 Ω (recommend)	Power input	recommend DC5V 1A
Battery Capacity	1400 mAh	Battery Life	> 16 h
Output Power	270 mW (32 Ω/THD+N < 1%) 450 mW (16 Ω/THD+N < 1%)	Charging Time	< 4 h
THD	0.004% (1 kHz)	Output Impedance	< 0.2 Ω
Frequency Response	20 Hz~20 kHz	SNR	> 108 dB
Input Sensitivity	2.4 V (GAIN=L) 0.8 V (GAIN=H)	Channel imbalance	< 0.3 dB
Crosstalk	≥72 dB (Gain=H)	MAX output current	92.6 mA
Gain	-3.8 dB (GAIN=L) 11.7 dB (GAIN=H)	Overload Level	> 8 Vrms