Part Number: 0334720602

Status: Active

Overview: MX150™ Sealed and Unsealed Connector System

Description: MX150™ Sealed Female Connector, Dual Row, 6 Circuits, Polarization B, without Connector Position Assurance, Light Gray

Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Packaging Specification PK-31300-903 (PDF)
Packaging Specification PK-33472-001 (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150™ Sealed and Unsealed Connector System
Product Name	MX150™
UPC	800756537450
Physical	
Circuits (maximum)	6
Color - Resin	Gray (Light), Natural
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	9.330/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-31300-903, PK-33472-001
Sales Drawing	150-S-006-2-Z02, SD-33472-0001

EU ELV
Compliant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per -ED/79/2015 (17 December 2015)

Halogen-Free Status
Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant

Search Parts in this Series
33472 Series

Mates With
33482 Male Dual Row Sealed Connector

Use With
33012 MX150™ Female Terminal,
34345-0001 MX150™ Cavity Plug Sealed