Part Number: 0009507051
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® 3.96mm Crimp Terminal Housing, 5 Circuits



Series image - Reference only

Documents:
3D Model
Drawing (PDF)
Packaging Specification PK-2139-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	2139
Application	Power, Wire-to-Board
MolexKits	Yes
Overview	KK® Interconnect System - Molex
Product Name	KK® 396
UPC	800753531512

Physical

Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	1.280/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Engineering Number	2139-5C

Reference - Drawing Numbers

Packaging Specification	PK-2139-001
Sales Drawing	SD-2139

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
2139 Series

Mates With
KK® 396 Headers: 41771 , 41772 , 41791 , 41792 , 42491 , 42492 , KK® 396 Breakaway Headers: 41661 , 41662 , 41671 , 41672

Use With
2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG