Brand Name:	Acer
DVI:	Yes
Environmentally Friendly:	Yes
Number of USB 2.0 Ports:	4
Number of USB 3.0 Ports:	2
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 7 Professional
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i5-6400
Processor Speed:	2.70 GHz
Processor Type:	Core i5
Product Family:	Extensa M2710
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	1 TB
Total Number of USB Ports:	6
VGA:	Yes

Display & Graphics

TV Card:	No

General Information

Brand Name:	Acer
Manufacturer Part Number:	DT.X0TEK.002
Manufacturer Website Address:	http://www.acer.co.uk
Manufacturer:	Acer, Inc
Product Line:	Extensa
Product Name:	Extensa M2710 Desktop Computer
Product Series:	M2710
Product Type:	Desktop Computer

I/O Expansions

Number of M.2 Interfaces:	1
Number of PCI Express x1 Slots:	1
Number of PCI Express x16 Slots:	1
Number of Total Expansion Slots:	2

Input Devices

Keyboard Type:	Physical Keyboard
Keyboard:	Yes
Pointing Device Type:	Mouse

Interfaces/Ports

Audio Line In:	Yes
Audio Line Out:	Yes
DVI:	Yes
Modem (RJ-11):	No
Network (RJ-45):	Yes
Number of USB 2.0 Ports:	4
Number of USB 3.0 Ports:	2
Number of USB 3.1 Gen 1 Ports:	2
Total Number of USB Ports:	6
VGA:	Yes

Memory

Maximum Memory:	16 GB
Memory Card Reader:	No
Memory Standard:	DDR4-2133/PC4-17000
Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

Miscellaneous

Certifications & Standards:
- DMI
- PC2001
- BSMI
- CB
- CE
- FCC

Environmental Certification: RoHS

Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	• Extensa M2710 Desktop Computer • USB Keyboard • USB Mouse

Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

Physical Characteristics

Depth:	372 mm
Height:	365 mm
Width:	175 mm

Power Description

Maximum Power Supply Wattage:	220 W

Processor & Chipset

64-bit Processing:	Yes
Cache:	6 MB
Chipset Manufacturer:	Intel
Chipset Model:	H110 Express
Direct Media Interface:	8 GT/s
Maximum Turbo Speed:	3.30 GHz
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Quad-core (4 Core)
Processor Manufacturer:	Intel
Processor Model:	i5-6400
Processor Speed:	2.70 GHz
Processor Type:	Core i5

Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 7 Professional
Software Included:	• Microsoft® Office Starter: reduced-functionality Word and Excel® only, with advertising. No PowerPoint® or Outlook®. Buy Office 2010 to use the full-featured software. • Bing™ Bar • Windows Live™ Essentials

Storage

Hard Drive Configuration:	1 x 1 TB
Hard Drive Interface:	Serial ATA/300
Hard Drive RPM:	7200
Number of Hard Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	1 TB