Product information

MULTI TOOL

Satisfying the professional's needs

TM3000C

Oscillation Angle	3.2 °
Oscillations per Minute	6000 - 20000
Input Wattage	320 w
Vibration K factor	1.5 m/sec²
Vibration: Cutting Metal	3 m/sec²
Vibration: Cutting Wood	6.5 m/sec²
Vibration: Chiselling	5.5 m/sec²
Vibration: Sanding	2.5 m/sec²
Net weight	1.4 - 1.5 kg

3 YEAR WARRANTY

240V

110V

STANDARD EQUIPMENT: Hex wrench

- Thumb On/Off switch, positioned for ease of use when holding body of machine.
- Hex wrench holder on body.
- Variable speed control dial.
- Optional dust extraction attachment (Not included)
- Accessories can be installed at 30º increments, across 360º
- Uses OIS interface.

Details correct as of: 9-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.