KA0

Model Name: KA270H
Part Number: UM.HX3EE.A01

The KA0 series is optimised for a comfortable viewing experience. The display is easy on the eyes with low response times and special technology to reduce glare and harsh blue light. Easy adjustments and a wide viewing angle help you find the perfect position.

Screen Size	27"
Resolution	Full HD (1920 x 1080)
Aspect Ratio	16:9
Response Time	4ms GTG
Refresh Rate	60Hz
Colour Support	16.7 million
Brightness	300cd/m²
Backlight	LED
Viewing Angles	178° Horizontal 178° Vertical
Panel Type	Vertical Alignment (VA)
Stand	Tiltable (-5° to 15°)
Ports & Connectors	DVI-in HDMI® VGA
Features	Wide Viewing Angle, Flicker-free, Blue Light, ComfyView

Power	26.60 W (ENERGY STAR® rating) 32 W (EEL) 430 mW (standby) 240 mW (off)
Environmental Certification	MPR II
Colours	Black
Weight (Approximate)	5 kg (without stand) 5.40 kg (with stand)
Package Contents	• KA270H Widescreen LCD Monitor • UK Power Cord • 1 x VGA Cable
Warranty	Standard Warranty