Heavy Duty Connector Housings

multicomp PRO

Specifications

Surface	: Powder-Coated
Material	: Zinc Die-Cast
Colour	: Grey
Temperature Range	: -40°C to +125°C
Locking Type	: Single Locking latch
Locking Material	: Stainless Steel
Hoods/Housing Sealing	: NBR
IP Rating	: IP65

RoHS Compliant

Housing, Bulkhead Mount, Metal

Diagram

**MP009340**

**MP009341**

**MP009342**

panel cut out

Dimensions : Millimetres

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Page <1>   14/05/22   V1.0

Heavy Duty Connector Housings

MP009343

Housing, Bulkhead Mount, Plastic

Specifications

Material	: Polycarbonate
Colour	: Grey
Lever Material	: Polyamide
Hoods & Housings Seal	: NBR
Temperature Range	: -40°C to +125°C
IP Rating	: IP65

MP009348

MP009349

Part Number	Description
MP009340	1 Locking Lever
MP009343	Side Entry 1 Locking Lever
MP009341	1 Locking Lever Locking Cover for Female Insert
MP009342	1 Locking Lever Locking Cover for Male Insert
MP009348	Plastic, 1 Locking Lever
MP009349	Plastic, Side Entry 1 Locking Lever

Dimensions : Millimetres

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Page <2>   14/05/22   V1.0

multicomp PRO

Housing, Cable to Cable, Plastic

MP009351

Specifications

Material	: Polycarbonate
Colour	: Grey
Lever Material	: Polyamide
Hoods & Housings Seal	: NBR
Temperature Range	: -40°C to +125°C
IP Rating	: IP65

Housing, Cable to Cable, Metal

MP009345

Specifications

Material	: Zinc Die-Cast
Colour	: Grey
Surface	: Power
Temperature Range	: -40°C to +125°C
IP Rating	: IP65

| Part Number	Description
MP009351	Plastic, 1 Locking Lever, M20
MP009345	Metal, 1 Locking Lever, M20

Housing, Surface Mount, Metal

MP009344

Dimensions : Millimetres

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Page <3>   14/05/22   V1.0

Housing, Surface Mount, Plastic

MP009350

Specifications

Material	: Polycarbonate
Colour	: Grey
Lever Material	: Polyamide
Hoods & Housings Seal	: NBR
Temperature Range	: -40°C to +125°C
IP Rating	: IP65

Dimensions : Millimetres

Part Number	Description
MP009350	Plastic, 1 Locking Lever, M20
MP009344	Metal, 1 Locking Lever, M20

Part Number Table

Description	Part Number
Housing, H3A, Metal, Bulkhead Mount, 1 Locking Lever	MP009340
Housing, H3A, Metal, Bulkhead Mount, 1 Locking Lever Locking Cover for Female Insert	MP009341
Housing, H3A, Metal, Bulkhead Mount, 1 Locking Lever Locking Cover for Male Insert	MP009342
Housing, H3A, Metal, Bulkhead Mount, Side Entry 1 Locking Lever	MP009343
Housing, H3A, Metal, Surface Mount, 1 Locking Lever, M20	MP009344
Housing, H3A, Metal, Cable to Cable, 1 Locking Lever, M20	MP009345
Housing, H3A, Plastic, Bulkhead Mount, 1 Locking Lever	MP009348
Housing, H3A, Plastic, Bulkhead Mount, Side Entry 1 Locking Lever	MP009349
Housing, H3A, Plastic, Surface Mount, 1 Locking Lever, M20	MP009350
Housing, H3A, Plastic, Cable to Cable, 1 Locking Lever, M20	MP009351

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Page <4>   14/05/22   V1.0