

REV.	CNN	CNN DESCRIPTION	Date	Check in
03	2753	SHOW PIN AS SOLID	09/02/2010	Shaun Barron
04	2753	SHOW PIN AS SOLID	29/09/2010	Shaun Barron

A range of high quality UK manufactured phono plugs made from machined brass with various plating options.

- Centre contact available in hollow tube.
- Ground contact with unique 'T' shape slot for maximum contact area.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification.
- Attractive body styling.
- Maximum cable size 5.5mm

Rating -

Rated Current: 5A .

Rated Voltage: 50V

Insulation resistance - 100M  $\Omega$  at 500 Vdc

Material

Centre contact :Brass, silver plated



Ground contact :Brass, nickel plated

Insulation :Noryl SE1

Cable clamp :Brass, silver plated

Spring :Spring steel, nickel plated

Cap :Brass, nickel plated



Deltron Part No.	Description
333-0000	NICKEL PLATED
333-0100	NICKEL PLATED (BLACK ID RING)
333-0200	NICKEL PLATED (BLUE ID RING)
333-0500	NICKEL PLATED (BLUE ID RING)
333-0600	NICKEL PLATED (RED ID RING)
333-0700	NICKEL PLATED (YELLOW ID RING)

Tel No. +44(0)1724 273200 Website www.dem-uk.com

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ALPHA 3 MANUFACTURING. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ALPHA 3 MANUFACTURING IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETRES LINEAR TOLERANCE: NO DECIMAL PLACES  $\pm 0.5\text{mm}$  1 DECIMAL PLACE  $\pm 0.25\text{mm}$  2 DECIMAL PLACES  $\pm 0.125\text{mm}$  ANGULAR TOLERANCE:  $\pm 1^\circ$

FINISH

SEE NOTE

DEBURR AND BREAK SHARP EDGES

DRAWN BY

SPB

TITLE GENERAL SPECIFICATION

333 SERIES

PROFESSIONAL PHONO PLUG

APPROVED BY

WC

THIRD ANGLE PROJECTION

SHEET 1 OF 1

DRAWING NO.

333 SERIES

ISSUE

04

Release



DEM Manufacturing, Deltron Emcon House Hargreaves Way, Sawcliffe Ind. Park, Scunthorpe, North Lincolnshire, DN15 8RF, UK