D-shape metal housing

USB type B

Push Pull locking

USB type B

USB Receptacle

NAUSB-W

- USB 2.0 gender changer type A-B (B-A)
- Ideal for audio networking and integration of computerbased equipment into audio systems
- Lockable connection and water protection if mated with Neutrik USB cable NKUSB-*
- Optional screen to chassis grounding
- Reversible insert offering type A or B on front or rear end
- Universally accepted standard D-shape housing

NAUSB-W

31 (1.220")

26 [1.024"]

36 [1.42"]

41 [1.61"]

2 [0.079"]

USB Patch Cable

NEW

NKUSB-*

- USB 2.0 compliant - data rate up to 480 MBit/s
- Dust and water resistant sealing in combination with NAUSB-W*
- Push Pull mating design provides secure locking system if mated with NAUSB-W*
- Shielded connection - high noise immunity and EMI protection
- Ready made patch cables (1m, 3m and 5m) with removable rugged diecast cable carrier
- Mates with conventional USB receptacles if cable carrier is removed

NKUSB

Ø23.3 [.917"]

53.0 [2.10"]

Availability: commencing November 2009

Technical Data

Mechanical and Electrical

			Receptacle	Patch Cable
Conform with USB 2.0 Standard			●	●

Material

			Receptacle	Patch Cable
Shell	Zinc diecast (ZnAl4Cu1)	Nickel or black Chrome	●	Nickel
Insert		PBTP 15% GR	●	-
		PVC	-	●
Contacts		Brass (CuZn39Pb3)	●	●
Contact finish		Gold	●	●

Environmental

		Receptacle	Patch Cable
Operating temperature	-25°C to +85°C	●	●
Flammability	UL94 V-0	●	●

Ordering Information

Chassis

NAUSB-W	USB A – USB B Adapter (reversible), sealing ring, optional grounding, nickel housing
NAUSB-W-B	USB A – USB B Adapter (reversible), sealing ring, optional grounding, black housing

Patch Cable

NKUSB-*	USB 2.0 cable with overmolded flex relief and metal cable carrier, standard lengths: 1, 3, 5 m

Accessories

DSS-*

SCM

SCDX

SCDP-*

DSS-*	Lettering plate for D series, coloured plastic
SCM	Plastic sealing cover to protect the Firewire connectors against dust and moisture.
SCDP-*	D-Size sealing gaskets, colour coding (*: 0- black, 2- red, 4- yellow, 5- green, 6- blue, 9- white)
SCDX	Hinged cover seals D-size chassis connectors, IP42 rated
NZP1RU	Panel1RU D-shape housing

*:   0 - Black, 1- Brown, 2 - Red, 3 - Orange, 4 - Yellow, 5 - Green, 6 - Blue, 7 - Violet, 8 - Grey, 9 - White