Downloaded By: Edmonson,Stephanie - 11/22/2019 GOV: ESO1.0
THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL KOREA. THE DRAWING IS TO BE SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.
Honeywell proprietary & Confidential
Released
SZL-WL-K-N

SHEET 1/1

DRAWING NO. SZL-WL-K-N(EXP)

REV.NO.	REVISED	DATE	DRAWN	CHECKED	APPROVED
B	0024772	13SEP06	BNA	DVM	



1. CHARACTERISTICS

TYPE	
OPERATING FORCE	150g Max.
PRE-TRAVEL	20.0±1.0 mm

2. ELECTRICAL RATING

1 10A 125,250,300V AC
6A 24V DC

3. CONTACT ARRANEMENT



FIG 1. BLADE OF COM

-> IN CASE OF USING FOR SPDT : CONNECT No.1 WITH No. 4 OR No.2 WITH No. 3 BY BLADE OF COM(FIG 1)

NOTE

1. UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMALS ±0.4

ITEM	PART NO.	DESCRIPTION	Q'TY	REMARKS

APPROVED	JJ,RAH	MATERIAL	-	USED ON WL-K	PROJECTION
CHECKED		FINISH	-	YH/HONG NO. –	
DRAWN	KB,LEE	TREATMENT	-		
TOLERANCE	±0.4	Honeywell		DRAWING NO. SZL-WL-K-N(EXP)	REV. B
SCALE	1/1			DESCRIPTION OUTLINE DRAWING	SHEET 1/1

The HEC and TEC codes identified in this watermark supersede any conflicting HEC or TEC codes displayed in the drawing.