




Connector Location A

Connector Location B



NOTE:
For lengths < 1.0m:
- relative positioning of the connectors to each other will be as presented in the drawing, however with an admissible angular deviation around cable axis of $\pm 30^\circ$
For lengths ≥ 1.0 m:
- relative positioning of the connectors to each other not obligatory

Temperature range:
- Fixed installation: $-30^\circ\text{C} \dots +75^\circ\text{C}$
- Dynamic installation: $-5^\circ\text{C} \dots +50^\circ\text{C}$

	All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved		Created by	Inspected by	Standardisation	Date	State	
	Department HCS - RO		MUNTEANV	COSTEA	AVRAM	2017-06-07	Final Release	
	HARTING Customised Solutions		Title RJ Industrial Cable Assembly				Doc-Key / ECM-Nr.	
D-32427 Minden		Type	TB	Number	094747471XX		Rev.	Page
						L		1/2

1		2	3	4	5	6	7	8																																																									
A	54	09474747135	4x2xAWG27/7, S/FTP, PUR, Cat.7, yellow	35	±1%																																																												
	53	09474747136		31																																																													
	52	09474747125		30																																																													
	51	09474747182		28																																																													
	50	09474747126		25																																																													
	49	09474747181		22																																																													
	48	09474747123		20																																																													
	47	09474747179		19																																																													
B	46	09474747178		18																																																													
	45	09474747177		17																																																													
	44	09474747124		16																																																													
	43	09474747122		15																																																													
	42	09474747134		14																																																													
	41	09474747133		13.5																																																													
	40	09474747176		13																																																													
	39	09474747132		12.5																																																													
C	38	09474747131		12																																																													
	37	09474747130		11.5																																																													
	36	09474747129		11																																																													
	35	09474747121		10																																																													
	34	09474747128		9.5																																																													
	33	09474747120		9																																																													
	32	09474747127		8.5																																																													
	31	09474747119		8																																																													
D	30	09474747118		7.5																																																													
	29	09474747117		7																																																													
	28	09474747174		6.5																																																													
	27	09474747116		6																																																													
	26	09474747173		5.5																																																													
	25	09474747115		5																																																													
	24	09474747172		4.75																																																													
	23	09474747171		4.5																																																													
E	22	09474747170		4.25																																																													
	21	09474747114		4																																																													
	20	09474747169		3.75																																																													
	19	09474747168		3.5																																																													
	18	09474747167		3.25																																																													
	17	09474747113		3																																																													
	16	09474747140		2.75																																																													
	15	09474747112		2.5																																																													
F	14	09474747139		2.25																																																													
	13	09474747111		2																																																													
	12	09474747138		1.75																																																													
	11	09474747110		1.5																																																													
	10	09474747137		1.25																																																													
	9	09474747109		1																																																													
	8	09474747108		0.9																																																													
	7	09474747107		0.8																																																													
	6	09474747106		0.7	+0.020	<table><tr><td>57</td><td>09474747199</td><td rowspan="3">4x2xAWG27/7, S/FTP, PUR, Cat.7, yellow</td><td>100</td><td rowspan="3">±1%</td></tr><tr><td>56</td><td>09474747180</td><td>50</td></tr><tr><td>55</td><td>09474747175</td><td>40</td></tr><tr><td>Cont. no.</td><td>Part no.</td><td colspan="2">Type of cable</td><td>Dim. a[m]</td></tr><tr><td colspan="2"> All Dimensions in mm</td><td colspan="2">Tech. Character.</td><td colspan="2">Free size tol.</td><td colspan="2">According to production drawing</td></tr><tr><td colspan="2"> All rights reserved</td><td>Created by</td><td>Inspected by</td><td>Standardisation</td><td>Date</td><td colspan="2">State</td></tr><tr><td colspan="2">Department HCS - RO</td><td>MUNTEANV</td><td>COSTEA</td><td>AVRAM</td><td>2017-06-07</td><td colspan="2">Final Release</td></tr><tr><td colspan="2">HARTING Customised Solutions</td><td colspan="4">Title RJ Industrial Cable Assembly</td><td colspan="2">Doc-Key / ECM-Nr.</td></tr><tr><td colspan="2">D-32427 Minden</td><td colspan="4">Type TB</td><td>Number</td><td>094747471XX</td><td>Rev. L</td><td>Page 2/2</td></tr></table>			57	09474747199	4x2xAWG27/7, S/FTP, PUR, Cat.7, yellow	100	±1%	56	09474747180	50	55	09474747175	40	Cont. no.	Part no.	Type of cable		Dim. a[m]	 All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing		 All rights reserved		Created by	Inspected by	Standardisation	Date	State		Department HCS - RO		MUNTEANV	COSTEA	AVRAM	2017-06-07	Final Release		HARTING Customised Solutions		Title RJ Industrial Cable Assembly				Doc-Key / ECM-Nr.		D-32427 Minden		Type TB				Number	094747471XX	Rev. L
	57	09474747199	4x2xAWG27/7, S/FTP, PUR, Cat.7, yellow	100					±1%																																																								
	56	09474747180		50																																																													
	55	09474747175		40																																																													
	Cont. no.	Part no.	Type of cable						Dim. a[m]																																																								
	 All Dimensions in mm		Tech. Character.						Free size tol.		According to production drawing																																																						
	 All rights reserved		Created by	Inspected by					Standardisation	Date	State																																																						
	Department HCS - RO		MUNTEANV	COSTEA					AVRAM	2017-06-07	Final Release																																																						
HARTING Customised Solutions		Title RJ Industrial Cable Assembly				Doc-Key / ECM-Nr.																																																											
D-32427 Minden		Type TB				Number	094747471XX	Rev. L	Page 2/2																																																								
5	09474747105	0.6																																																															
4	09474747104	0.5																																																															
3	09474747103	0.4																																																															
2	09474747102	0.3																																																															
1	09474747101	0.2																																																															
Cont. no.	Part no.	Type of cable	Dim. a[m]																																																														
1				5	6	7	8																																																										