



SPECIFICATION

MATERIALS:

HOUSING & INSERT: PBT

COUPLING: BRASS-NICKEL PLATED

O-RING: VITON

ELECTRICAL:

VOLTAGE: 10-30VDC

CURRENT RATING: 4A PER PORT, 12 AMPS MAX.

PROTECTION CLASS: IP68

NOTES:

THREADED PLUG FITTED TO PORTS 1 & 2 ONLY

PROTECTION CAP FITTED TO ALL M12 PORTS

FIXING HOLES TO SUIT M4 SCREWS

SAP-Nummer	alte Artikel-Nr.	Beschreibung	Farbe
SAP-NUMBER	OLD ENGINEERING-No.	DESCRIPTION	COLOR
1201190027	BKY400P-FBP-03	ULTRA-LOCK MPIS 4 WAY - 4 I/O 3M	gelb/YELLOW
1201190001	BKY400P-FBP-05	ULTRA-LOCK MPIS 4 WAY - 4 I/O 5M	gelb/YELLOW
1200550891	BKY400P-FBP-10	ULTRA-LOCK MPIS 4 WAY - 4 I/O 10M	gelb/YELLOW

REV	DESCRIPTION
A	NEW RELEASE EC NO: WEU2010-0220 2009/12/07 DRWN:SBH 2009/12/17 CH'KD: 2009/12/18 APPR:FPACHER

QUALITY SYMBOLS: ▼=0, (C)=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.05	± ---
1 PLACE	± 0.10	± ---
ANGULAR ±---°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM ONLY

SCALE

DESIGN UNITS: METRIC

THIRD ANGLE PROJECTION

DRAWN BY: SBH DATE: 2009/12/10

CHECKED BY: APOHL_WEU DATE: 2009/12/10

APPROVED BY: FPACHER DATE: 2009/12/17

TITLE: ULTRA-LOCK MPIS 4 WAY - 4 I/O XM-PUR

MOLEX INCORPORATED

MATERIAL NO.: SEE TABLE

DOCUMENT NO.: SD-120119-017

SHEET NO.: 1 OF 1

SIZE: A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION