REVISION RECORD MODIFICATIONS	DATE	REV.
NEW	2012/05/07	A/0



PIN OUT



VIEW:



NOTE:

1. Electrical test:
   (1). 100% open short & miss wire test;
   (2). Insulation resistance:DC 300V 3MΩ;
   (3). Contactor resistance:3Ω;
2. RoHS compliant
3. MARKING: CAT6A S-STP 500MHz 4PAIRS STRANDED AWG26 100 ohm Halogenfree

MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT'Y	REMARK
③	CABLE	Cat.6A (7/0.16BC*1P+A)*4 SSTP B=0.12mm/5*16 AL-MG JACKET:HF/Color:GREY OD:6.5mm	1	
②	OUTER MOLD	PVC,COLOR: GREY	2	
①	8P8C PLUG	RJ45 8P8CS,Double stent,CAT.6A Pin PLATED GOLD 3U", ALL SHELL PLATED NICKEL,transparent Circle Type.	2	

DRAW NO.	KK0182	PRODUCT NAME	CAT.6A SSTP 8P8CS - 8P8CS		
CUSTOMER			VIEW	Tolerance	
ITEM NO.				X. ±1.00 X.X ±0.50	
APPOBY		CHECKBY	DRAWNBY	UNTT	MM
			Nancy.tang	Page	1 of 1