DX-200 Solenoid Bolt

* **High Security**
* **Fail Safe Device**
* **12VDC**
* **1.1A In-Rush**
* **140mA Maintained**
* **Stainless Steel**
* **Retry Circuit**
* **Relay Output (Locked)**
* **Door Status Output**
* **Excellent Value**
* **12 Month Warranty**

DX-200-H

Specification

Voltage:	12vdc
Current:	SB262 - Pull In 1.1A, Run 140mA
Dimensions:	200 x 27 x 42 (l x w x d)
Output:	Changeover relay for "locked"
	Door Position Switch
Delay:	Adjustable 0-7 seconds by jumper

Product Code

DX-200	Solenoid Bolt, Fail Safe
DX-200-H	Surface Housing for DX-200

*Making your security
a permanent asset...*

C.D.V. (UK) LTD

www.cdvuk.com