

Classic filament LED candles and lusters

Classic LEDLuster DT4.5-40W E14 CRI90P45 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	E14 [E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4.5-40W

Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	270 °
Luminous Flux (Nom)	470 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	104.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4.5 W
Lamp Current (Nom)	30 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]

Approval and Application	
Energy Efficiency Label (EEL)	A++

Classic filament LED candles and lusters

Energy Consumption kWh/1000 h	5 kWh

Product Data

Full product code	871869978023400
Order product name	Classic LEDLuster DT4.5-40W E14 CRI90P45 CL
EAN/UPC - Product	8718699780234

Order code	929002393602
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002393602
Net Weight (Piece)	0.014 kg

Dimensional drawing



P45 230V 6-40W 470lm 2700-2200K E14 D CL

Product	D	C
Classic LEDLuster DT4.5-40W E14 CRI90P45 CL	45 mm	82 mm

Photometric data



LEDbulb CLA 4,5W P45 E14 927 922 CL



LEDbulb CLA 4,5W P45 E14 927 922 CL



LEDbulb CLA WGD CRI90

Classic filament LED candles and lusters

Lifetime



15K LED



15K LMP

© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.