JOB SITE SPEAKER/ STEREO

DMR301

12Vmax-18V CXT LXT Li-Ion Cordless Bluetooth Job Site DAB / DAB+ Charger Radio

TECHNICAL SPECIFICATIONS

Battery Type	Lithium=ion
Body only machine	✓
Frequency Range FM	87.5 - 108 Mhz
Frequency Range AM	522 - 1710 kHz
Speakers	2x 89mmØ
Practical Output (12v)	1.2W x 2
Practical Output (14.4v)	2.2W x 2
Practical Output (18v)	3.5W x 2
Frequency Range DAB	Band III 5A - 13F
Net weight	5.9 - 6.6 kg

USER BENEFITS

- Battery Charging: Able to charge LXT/CXT batteries when powered by mains with AC adaptor
- Compatible with LXT and CXT batteries only
- AC adaptor jack
- IP64 rated dust and shower-proof construction
- 2X speaker stereo system
- Runs up to 24.7 hours with an 18V LXT Li-ion 6Ah battery
- Elastomer bumpers and metal pipes protect against rough handling
- AUX-IN jack for connecting to external audio source (Connecting cable is not included.)
- Digital tuner
- Illuminated control buttons and dial for improved visibility
- Swivel mount, soft bend antenna minimises breakage and/or loss
- LCD screen indicates battery charging status; Charging, Charging completed, Standing-by for charging, Charging error; indicates battery reach at

Link to product - makitauk.com

RELATED PRODUCTS

(Recor

OTHER