V-TAC
Meaningful Innovation.

PRODUCT SPEC SHEET

SKU 240796 Model:VT-91202 EAN:3800170253407

VT-91202 200W LED UFO HIGHBAY CREE CHIP 4000K 155LM/W 6 YEARS WARRANTY

A↑G D | IP65 STANDARD | 6 YEAR WARRANTY | CREE LED POWERED

- Powerful LED light source with a unique design
- High quality SMD-CREE Chip with power driver
- Strong and Sturdy Aluminium built
- Product designed with high lumen efficency 155 LM/W
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums

TECHNICAL INFORMATION

Color Temperature:	4000K
Model:	VT-91202
On/Off Cycles:	>25000
Dimmable:	No
CRI:	>70
Watts:	200
Lumens:	31000
Useful Lumens:	27000
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	326x326x105mm
Operation Temperature:	-20°C to +40°C
PF:	>0.9

LISTING DETAILS

SKU:	240796
Model:	VT-91202
EAN:	3800170253407
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	2.04
Unit CBM:	0.01751
Dimension:	326x326x105mm

MASTER BOX PACKAGING

Box Qty:	1
Qty Per Pallet:	80
Length (Box) mm:	330
Width (Box) mm:	330

LED Chip Type:	SMD-CREE Chip
Beam Angle:	90°
Energy Rating Label:	D (2021)
IP Rating:	IP65
IK Rating:	IK06
Long Life:	50,000 Hours
lumens per watt:	155

Height (Box) mm:	110