HellermannTyton

Technical data sheet

Article number:
170-03014 BSPSC100



Product Group	Fray Resistant
Material	Polyester (PET)
Colour	Black (BK)

Bundle Ø max.	30.2 mm
Bundle Ø min.	19.1 mm
Melting Point	+250 °C
Operating Temperature	-70 °C to +125 °C
Package Content	15.24 m
Package Content packed in	pack
UL-File Number	E147924

HF RoHS

created on 24. April 2026, 4:50 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.