

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW

NOTES:

- TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 830V  
RATED CURRENT: 40A  
INSULATION RESISTANCE:  $\geq 400M\Omega$   
RATED IMPULSE VOLTAGE: 8KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
MATING CYCLES: 500 CYCLES  
WIRE RANGE:  $1.0mm^2 \sim 6.0mm^2$   
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.  
(ORDER No. REFER TO DRAWING: T20400X20XX000)

注释:

- 技术参数:  
绝缘材料: PC  
额定电压: 830V  
额定电流: 40A  
绝缘电阻:  $\geq 400M\Omega$   
脉冲电压: 8KV  
污染等级: 3  
阻燃等级: UL94V-0  
插拔次数: 500次  
接线范围:  $1.0mm^2 \sim 6.0mm^2$   
接线类型: 冷压接
- 端子需要单独订购。  
(订货号参考图面: T20400X20XX000)

T2111042201-007	HMN-004-F	HMN-004 FEMALE MODULE INSERT HMN-004 模块母插																																													
PART NUMBER 料号	PART DESCRIPTION 描述																																														
<table border="1"> <tr> <td>DWN</td> <td>19SEP2017</td> <td rowspan="4"> </td> <td rowspan="4">TE Connectivity</td> </tr> <tr> <td>CHK</td> <td>YORK CHEN</td> </tr> <tr> <td>CHK</td> <td>GINO YAO</td> </tr> <tr> <td>APVD</td> <td>19SEP2017</td> </tr> <tr> <td colspan="2">APVD</td> <td>CHRIS WANG</td> <td>NAME</td> <td>HMN-004-F</td> </tr> <tr> <td colspan="2">PRODUCT SPEC</td> <td>108-137060</td> <td colspan="2">RESTRICTED TO</td> </tr> <tr> <td colspan="2">APPLICATION SPEC</td> <td>114-137060</td> <td>SIZE</td> <td>CAGE CODE</td> </tr> <tr> <td colspan="2">WEIGHT</td> <td>-</td> <td>A3</td> <td>00779</td> </tr> <tr> <td colspan="2">CUSTOMER DRAWING</td> <td colspan="2">SCALE</td> <td>3:2</td> </tr> <tr> <td colspan="2"></td> <td colspan="2">SHEET</td> <td>1 OF 1</td> </tr> <tr> <td colspan="2"></td> <td colspan="2">REV</td> <td>B</td> </tr> </table>			DWN	19SEP2017		TE Connectivity	CHK	YORK CHEN	CHK	GINO YAO	APVD	19SEP2017	APVD		CHRIS WANG	NAME	HMN-004-F	PRODUCT SPEC		108-137060	RESTRICTED TO		APPLICATION SPEC		114-137060	SIZE	CAGE CODE	WEIGHT		-	A3	00779	CUSTOMER DRAWING		SCALE		3:2			SHEET		1 OF 1			REV		B
DWN	19SEP2017		TE Connectivity																																												
CHK	YORK CHEN																																														
CHK	GINO YAO																																														
APVD	19SEP2017																																														
APVD		CHRIS WANG	NAME	HMN-004-F																																											
PRODUCT SPEC		108-137060	RESTRICTED TO																																												
APPLICATION SPEC		114-137060	SIZE	CAGE CODE																																											
WEIGHT		-	A3	00779																																											
CUSTOMER DRAWING		SCALE		3:2																																											
		SHEET		1 OF 1																																											
		REV		B																																											

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC $\pm$
	1 PLC $\pm$
	2 PLC $\pm$
	3 PLC $\pm$
	4 PLC $\pm$
	ANGLES $\pm$
MATERIAL	FINISH
-	-
-	-

1470-19 (3/13)