2 Port USB A Female Low Profile Slot Plate Adapter

Product ID: USBPLATELP



The USBPLATELP 2 Port Low Profile USB Bracket converts the USB pins on a USB 2.0 motherboard header to 2 standard USB A ports.

An ideal solution for small form factor computer cases, the slot plate can be mounted on the rear panel of your low profile or thin client computer case - adding two USB female ports for simple connection to USB peripheral devices.

The USB motherboard adapter cable is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility

Applications

• Add two USB 2.0 female ports to the back of a small form factor computer case

Features

• 2x USB 'A' female ports

• 2x IDC-5 female connectors

• Supports 4 or 5 pin motherboard connections

• Supports high-speed USB data transfer rates of up to 480 Mbps

• Offers 11.25" in cable length

General		
	UPC	065030831772
	Package Quantity	1
	Warranty	Lifetime
Physical & Environmental		
	Color	Gray
	Cable Length	11.2 in [28.5 cm]
	Product Length	12.6 in [32.0 cm]
	Product Width	3.2 in [81.2 mm]
	Product Height	0.7 in [18.6 mm]
	Weight of Product	1.6 oz [44.0 g]
	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Performance		
	Type and Rate	USB 2.0 (480Mbps)
Packaging & In-the-Box		
	Included in Package	1 - 2 Port USB A Female Low Profile Slot Plate Adapter
	Package Width	7.2 in [18.2 cm]
	Package Depth	5.0 in [12.7 cm]
	Package Height	0.8 in [21 mm]
	Shipping (Package) Weight	1.7 oz [48 g]
Connector(s)		
	Connector 1 (Quantity)	2

Connector 1	USB-A (480Mbps, 2.5W)
Connector 2 (Quantity)	2
Connector 2	IDC (5-Pin)

Product appearance and specifications are subject to change without notice.