


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/28/19	PHOSPODAR

WIRING MAP TYPE A		
J1	COLOR	J2
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5	GRAY	5
6	WHITE	6
7	RED	7
8	BLACK	8
9	YELLOW	9
10	PURPLE	10
11	ROSE	11
12	AQUA	12
13	BLUE/BLACK	13
14	ORANGE/BLACK	14
15	GREEN/BLACK	15
16	BROWN/BLACK	16
17	GRAY/BLACK	17
18	WHITE/BLACK	18
19	RED/BLACK	19
20	BLACK / WHITE	20
21	YELLOW/BLACK	21
22	PURPLE/BLACK	22
23	ROSE/BLACK	23
24	AQUA/BLACK	24



PART NUMBER	METERS [FEET]
MPFF24OM5AZ-1	1.0 [3.28]
MPFF24OM5AZ-3	3.0 [9.84]
MPFF24OM5AZ-5	5.0 [16.40]
MPFF24OM5AZ-10	10.0 [32.81]
MPFF24OM5AZ-25	25.0 [82.02]
MPFF24OM5AZ-50	50.0 [164.04]
MPFF24OM5AZ-100	100.0 [328.08]

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X±.2 [5.08]	FRACTIONS
.XX±.01 [.25]	± 1/32
.XXX±.005 [.13]	ANGLES ± 1°

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

an INFINITO brand
50 High Street, West Mill, 3rd Floor, Suite #30
North Andover, MA 01845 USA.
Phone: 1.800.341.5266 | 1.978.682.6936
Fax: 1.978.689.9484
www.L-com.com | e-mail: CustomerService@L-com.com

SIZE	CAGE	DRAWN BY	PART NUMBER	REV
A	43321	DZINN	MPFF24OM5AZ	A

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
L-COM GLOBAL CONNECTIVITY.
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.