


DESCRIPTION		QUALITY SYSTEM NO:	
DRAWING OF COMPRESSION TERMINALS AS SUPPLIED TO FARNELL		DAV 1134	
DISTRIBUTION	MANAGING DIRECTOR	SHEET 3 of	
SALES DIRECTOR	INSPECTION REPRESENTATIVE	ISSUE DATE. 15/10/90	
TEST. STORES		SIGNED. <i>[Signature]</i>	



FORK TERMINALS

1. Easy entry guides cable strands into position
2. Eliminates cable strand frays when inserted
3. Ensures fast positive and corrosion insulation

NEW EASY ENTRY DESIGN

BASIC TOLERANCE BAND

L.F.B. ± 1.0

ALL OTHER DIMENSIONS ± 0.25

TEMPERATURE RATING: -30 to 75 °C

DAVICO REF;	FARNELL PART NO.	A	B	C	D	F	F1	L	P	W	W1
DVF 1-3	150-283	3.2	10.0	1.7	3.4	6.5	-	21.2	-	5.7	-
DVF 1-3 N	150-284	3.7	10.0	1.7	3.4	6.5	-	21.2	-	5.7	-
DVF 1-4 N	150-285	4.3	10.0	1.7	3.4	6.5	-	21.2	-	6.4	-
DVF 1-5	150-286	5.3	10.0	1.7	3.4	6.5	-	21.2	-	9.5	-
DVF 1-6	150-287	6.4	10.0	1.7	3.4	11.0	-	27.2	-	12.0	-
DVF 2-3	150-288	3.2	10.0	2.3	4.1	6.5	-	21.2	-	5.7	-
DVF 2-3N	150-289	3.7	10.0	2.3	4.1	6.5	-	21.2	-	5.7	-
DVF 2-4 N	150-290	4.3	10.0	2.3	4.1	6.5	-	21.2	-	6.4	-
DVF 2-5	150-291	5.3	10.0	2.3	4.1	6.5	-	21.2	-	9.5	-
DVF 2-6	150-292	6.4	10.0	2.3	4.1	11.0	-	27.2	-	12.0	-

DAVICO RESERVE THE RIGHT TO ALTER DIMENSIONS WITHOUT PRIOR NOTICE.

DAVICO
Keeping electricity firmly in its place

Davico Industrial Limited, Charles Street, West Bromwich,
 West Midlands B70 0A2 U.K. Tel: 021-520 7101.
 Tel: 021-520 7100

REV 1	DATE	NEW EASY ENTRY ADDED	<i>[Signature]</i>
	2-1-92		
REV 2	DATE		SIG
REV 3	DATE		SIG