


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL. CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	18/JAN/2007	
A1	Add wiring color	16/JAN/2012	
A2	Add length 50FT	20/NOV/2014	



LENGTH & P/N Table

LENGTH	P/N	Cable Color
2.5FT ±1 inch	CS-DSDMDB50MM-002.5	GREY
5FT ±2 inch	CS-DSDMDB50MM-005	GREY
10FT ±3 inch	CS-DSDMDB50MM-010	GREY
15FT ±3 inch	CS-DSDMDB50MM-015	GREY
25FT ±4 inch	CS-DSDMDB50MM-025	GREY
50FT ±8 inch	CS-DSDMDB50MM-050	GREY

PIN OUT:		Inner Layer Code	Outer Layer Code	
Male	Male	Color	Color	
PIN1	PIN1	Black	PIN26	Black
PIN2	PIN2	Brown	PIN27	Brown
PIN3	PIN3	Red	PIN28	Red
PIN4	PIN4	Orange	PIN29	Orange
PIN5	PIN5	Yellow	PIN30	Yellow
PIN6	PIN6	Green	PIN31	Green
PIN7	PIN7	Blue	PIN32	Blue
PIN8	PIN8	Purple	PIN33	Purple
PIN9	PIN9	Gray	PIN34	Gray
PIN10	PIN10	White	PIN35	White
PIN11	PIN11	Pink	PIN36	Pink
PIN12	PIN12	Light Green	PIN37	Light Green
PIN13	PIN13	Brown/White	PIN38	Black/White
PIN14	PIN14	Black/White	PIN39	Brown/White
PIN15	PIN15	Red/White	PIN40	Red/White
PIN16	PIN16	Orange/White	PIN41	Orange/White
PIN17	PIN17	Green/White	PIN42	Green/White
PIN18	PIN18	Blue/White	PIN43	Blue/White
PIN19	PIN19	Purple/White	PIN44	Purple/White
PIN20	PIN20	Red/Black	PIN45	Red/Black
PIN21	PIN21	Orange/Black	PIN46	Orange/Black
PIN22	PIN22	Yellow/Black	PIN47	Yellow/Black
PIN23	PIN23	Green/Black	PIN48	Green/Black
PIN24	PIN24	Grey/Black	PIN49	Grey/Black
PIN25	PIN25	Pink/Black	PIN50	Pink/Black
			SHIELD	SHIELD

NOTES: UNLESS OTHERWISE SPECIFIED



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:

DECIMALS	±.XX	ANGLES	±.X°
X	±.XX		
XXX	±.XXX		

THIRD ANGLE PROJECTION

APPROVALS	DATE	EAR NO.
DRAWN	20/NOV/2014	
CHECKED		
BA	20/NOV/2014	
RESP ENG		
MFG ENG		

ASSEMBLY NO. CS-DSDMDB50MM-XXX

ASSEMBLY NO. CS-DSDMDB50MM-XXX

SCALE SHEET OF