


6		5		4		3		2		1	
PART NUMBER		TITLE		CABLE DESCRIPTION		LENGTH 'L'		CABLE COLOR			
2175011101		Micro-lock plus 2.0 F-S 75mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		75±3		BLACK			
2175011102		Micro-lock plus 2.0 F-S 150mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		150±5		BLACK			
2175011103		Micro-lock plus 2.0 F-S 225mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		225±5		BLACK			
2175011104		Micro-lock plus 2.0 F-S 300mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		300±5		BLACK			
2175011105		Micro-lock plus 2.0 F-S 450mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		450±5		BLACK			
2175012101		Micro-lock plus 2.0 F-S 75mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		75±3		RED			
2175012102		Micro-lock plus 2.0 F-S 150mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		150±5		RED			
2175012103		Micro-lock plus 2.0 F-S 225mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		225±5		RED			
2175012104		Micro-lock plus 2.0 F-S 300mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		300±5		RED			
2175012105		Micro-lock plus 2.0 F-S 450mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		450±5		RED			



ITEM	PART#	DESCRIPTION	QTY	UOM
A	5055721000	2.0W/B REC CRIMP TERM CHAIN H>F	1	PC

- NOTES:
1. Crimping to be done as per Molex standards.
 2. The product specification relies on the terminals & wire spec.
 3. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 0.65mm Max.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2021/06/01	A	INITIAL RELEASE	AS20
DOCUMENT STATUS	P1	RELEASE DATE	2021/08/30 06:17:48

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{E} = 0$ $\frac{F}{P} = 0$ DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex									
	mm		NTS																
	GENERAL TOLERANCES (UNLESS SPECIFIED)									EC NO: 675273 DRWN: AS20 2021/06/01 CHK'D: MNARAYAN01 2021/08/30 APPR: MNARAYAN01 2021/08/30					SEE TABLE				
	ANGULAR TOL ± °																		
	4 PLACES		±																
	3 PLACES		±		PRODUCT CUSTOMER DRAWING														
	2 PLACES		±																
	1 PLACE		±																
0 PLACES		±																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION		
							A4-SIZE		217501		2175011101		PSD		000		A		