


6		5		4		3		2		1	
PART NUMBER		TITLE		CABLE DESCRIPTION		LENGTH 'L'		CABLE COLOR			
2175011111		Micro-lock plus 2.0 F-S 75mm 24 AWG BK Sn		1X24AWG DISC SR-PVC BK UL10002		75±3		BLACK			
2175011112		Micro-lock plus 2.0 F-S 150mm 24 AWG BK Sn		1X24AWG DISC SR-PVC BK UL10002		150±5		BLACK			
2175011113		Micro-lock plus 2.0 F-S 225mm 24 AWG BK Sn		1X24AWG DISC SR-PVC BK UL10002		225±5		BLACK			
2175011114		Micro-lock plus 2.0 F-S 300mm 24 AWG BK Sn		1X24AWG DISC SR-PVC BK UL10002		300±5		BLACK			
2175011115		Micro-lock plus 2.0 F-S 450mm 24 AWG BK Sn		1X24AWG DISC SR-PVC BK UL10002		450±5		BLACK			
2175012111		Micro-lock plus 2.0 F-S 75mm 24 AWG RD Sn		1X24AWG DISC SR-PVC RD UL10002		75±3		RED			
2175012112		Micro-lock plus 2.0 F-S 150mm 24 AWG RD Sn		1X24AWG DISC SR-PVC RD UL10002		150±5		RED			
2175012113		Micro-lock plus 2.0 F-S 225mm 24 AWG RD Sn		1X24AWG DISC SR-PVC RD UL10002		225±5		RED			
2175012114		Micro-lock plus 2.0 F-S 300mm 24 AWG RD Sn		1X24AWG DISC SR-PVC RD UL10002		300±5		RED			
2175012115		Micro-lock plus 2.0 F-S 450mm 24 AWG RD Sn		1X24AWG DISC SR-PVC RD UL10002		450±5		RED			




ITEM	PART#	DESCRIPTION	QTY	UOM
A	5055721000	2.0W/B REC CRIMP TERM CHAIN H>F	1	PC

- NOTES:
1. Crimping to be done as per Molex standards.
 2. The product specification relies on the terminals & wire spec.
 3. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 0.75mm Max.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2021/06/01	A	INITIAL RELEASE	AS20
DOCUMENT STATUS	P1	RELEASE DATE	2021/08/30 06:17:49

6		5		4		3		2		1	
FORMAT: master-ib-prod-A4		REVISION: J		DATE: 2020/01/14							

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex				
	mm		NTS										
	GENERAL TOLERANCES (UNLESS SPECIFIED)								SEE TABLE				
	ANGULAR TOL ± °												
	4 PLACES		±										PRODUCT CUSTOMER DRAWING
	3 PLACES		±										
	2 PLACES		±										
	1 PLACE		±										
	0 PLACES		±		INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
	DRWN: AS20 2021/06/01				2175011111				PSD	000	A		
APPR: MNARAYAN01 2021/08/30													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A4-SIZE	217501	SEE TABLE		GENERAL MARKET		1 OF 1			