



RoHS compliant
by exemption

*) Cavity 7, 8, 14 and 15 are unfiltered

4	15	Signal contact	P36 / Brass / AWG 20	G1 / C-Filter 1nF -20/+80% *)
3	1	Shell	Steel	tin plated
2	1	Sealing compound	Epoxy resin (-55°C - +85°C)	black
1	1	Insulator	Plastic	black
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

SYMBOLS					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0	DIMENSION UNITS	SCALE	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m		
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0	mm	2:1	CURRENT REVISION		
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0			DRWN: DRAWN BY	MTeubel	03-02-2020
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0			APPR: APPR BY	tschneider01	05-02-2020
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0	2	24130	INITIAL REVISION		
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0	1		DRWN: DRAWN BY	MTeubel	11-11-2015
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0	REV.	CH.-NO.	APPR: APPR BY	aschiekofer	17-11-2015
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0	REPLACEMENT FOR:		THIRD ANGLE PROJECTION	DRAWING	DOCUMENT NUMBER
▽ = 0	▽ = 0	▽ = 0	▽ = 0	▽ = 0				A3-SIZE	FC15POG1-5837
								PRODUCT CUSTOMER DRAWING	
								MATERIAL NUMBER	REVISION
								1731140430	2
								CUSTOMER	SHEET NUMBER
								GENERAL MARKET	1 OF 1

COMMENT: ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT, IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY. AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.