




ELV & RoHS COMPLIANT

NOTES

1.適用メスハウジング
APPLICABLE FEMALE HOUSING

PART NAME	PART NO.
FEMALE ASSY 44P	503137-44*1
FEMALE ASSY R 60P	503136-60*1
COMPACTUS 66WAY ASSY	560152-66*1
	560152-66*2
COMPACTUS 80WAY ASSY	560154-80*1
	560154-80*2
COMPACTUS 114WAY ASSY	560155-14*1
	560155-14*2

2.材質：PBT 色：グレー
MATERIAL：PBT COLOR：GRAY
3.使用する際は、適用メスハウジングの指定箇所に確実に装着されているか確認の事。
本製品の取扱いに関しては、適用メスハウジングに対応する取扱説明書を参照ください。
THE SPECIFIED POSITION IS ASSEMBLY.
ABOUT THE HANDLING OF THIS PRODUCT,PLEASE REFER TO
AN HANDLING MANUAL FOR THE APPLICABLE FEMALE HOUSING.
4.防水面に傷等無き事。
SEALING AREA：NO SCRATCHES AND NO CRACK.

0.12g
NET WEIGHT

molex

040 DUMMY PLUG HOUSING

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-503131-001	PSD	001	A1

THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	A3-SIZE	503131	503131-0151	GENERAL MARKET	1 OF 1

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	± 0.3
10 OVER 30 UNDER	± 0.4
30 OVER	± 0.5
ANGULAR	$\pm 5^\circ$



PACKAGING SPECIFICATION

LANGUAGE

JAPANESE
ENGLISH

CONFIDENTIAL


【1. 製品名称及び型番 PRODUCT NAME AND PART NUMBER】

- 製品名称 (Product Name) 025 DUMMY PLUG HOUSING
040 DUMMY PLUG HOUSING
- 型番 (Part Number) / 色 (Color) 025 : 503130-0101 / 白 (WHITE)
040 : 503131-0151 / 灰 (GRAY)

【2. 標準梱包内容 GENERAL PACKAGING INFORMATION】

- ポリ袋 (Poly bag) 025 : 20 PCS
040 : 10 PCS
- 製品数量 (Parts per carton box) 025 : 50,000 PCS (2,500 PCS×20)
040 : 30,000 PCS (3,000 PCS×10)
- 総重量 (Total weight) 025 : 4.2 KG
040 : 4.1 KG

【3. 参考寸法 REFERENCE DIMENSIONS】




<ラベル内容 / LABEL>

製品型番、数量、ロット No.
Part number , Quantity , Lot number

025



040



REVISION:

0

ECR/ECN INFORMATION:

EC No: JTR2009-0087

DATE: 2009 / 04 / 01

TITLE:

PACKAGING SPECIFICATION
025/040 DUMMY PLUG HOUSING

SHEET No.

1 of 1

DOCUMENT NUMBER:

SPK-503130-001

CREATED / REVISED BY:

K.KATO

CHECKED BY:

MA.YAMAMOTO

APPROVED BY:

A.KANESHIGE