


6		5		4		3		2		1	
PART NUMBER		TITLE		CABLE DESCRIPTION		LENGTH 'L'		CABLE COLOR			
2175011101		Micro-lock plus 2.0 F-S 75mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		75±3		BLACK			
2175011102		Micro-lock plus 2.0 F-S 150mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		150±5		BLACK			
2175011103		Micro-lock plus 2.0 F-S 225mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		225±5		BLACK			
2175011104		Micro-lock plus 2.0 F-S 300mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		300±5		BLACK			
2175011105		Micro-lock plus 2.0 F-S 450mm 26 AWG BK Sn		1X26AWG DISC SR-PVC BK UL10002		450±5		BLACK			
2175012101		Micro-lock plus 2.0 F-S 75mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		75±3		RED			
2175012102		Micro-lock plus 2.0 F-S 150mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		150±5		RED			
2175012103		Micro-lock plus 2.0 F-S 225mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		225±5		RED			
2175012104		Micro-lock plus 2.0 F-S 300mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		300±5		RED			
2175012105		Micro-lock plus 2.0 F-S 450mm 26 AWG RD Sn		1X26AWG DISC SR-PVC RD UL10002		450±5		RED			



ITEM	PART#	DESCRIPTION	QTY	UOM
A	5055721000	2.0W/B REC CRIMP TERM CHAIN H>F	1	PC

- NOTES:
- 1. Crimping to be done as per Molex standards.
 - 2. The product specification relies on the terminals & wire spec.
 - 3. Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 0.65mm Max.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2021/06/01	A	INITIAL RELEASE	AS20
DOCUMENT STATUS	P1	RELEASE DATE	2021/08/30 06:17:48

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				
FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{E} = 0$ $\frac{F}{P} = 0$ DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 675273 DRWN: AS20 2021/06/01 CHK'D: MNARAYAN01 2021/08/30 APPR: MNARAYAN01 2021/08/30					molex SEE TABLE										
	mm		NTS																	
	GENERAL TOLERANCES (UNLESS SPECIFIED)									PRODUCT CUSTOMER DRAWING										
	ANGULAR TOL ± °																			
	4 PLACES		±		DOCUMENT NUMBER 2175011101 DOC TYPE PSD DOC PART 000 REVISION A															
	3 PLACES		±																	
	2 PLACES		±																	
	1 PLACE		±																	
	0 PLACES		±		INITIAL REVISION: DRWN: AS20 2021/06/01 APPR: MNARAYAN01 2021/08/30															
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
										A4-SIZE		217501		SEE TABLE		GENERAL MARKET		1 OF 1		