


6			5		4		3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM						
A,B	348033212	CTX64 RCPT TERM ST SN L DWIND MS GEN			2	PC						



PART NUMBER	TITLE	CABLE DESCRIPTION	LENGTH 'L'	CABLE COLOR
2244511111	Stac64 F-F 75mm 0.75sq.mm Lead BK Sn	1CX0.75SQMM DISC PVC BK FLRYW125-B	75±3	BLACK
2244511112	Stac64 F-F 150mm 0.75sq.mm Lead BK Sn	1CX0.75SQMM DISC PVC BK FLRYW125-B	150±4	BLACK
2244511113	Stac64 F-F 225mm 0.75sq.mm Lead BK Sn	1CX0.75SQMM DISC PVC BK FLRYW125-B	225±4	BLACK
2244511114	Stac64 F-F 300mm 0.75sq.mm Lead BK Sn	1CX0.75SQMM DISC PVC BK FLRYW125-B	300±4	BLACK
2244511115	Stac64 F-F 450mm 0.75sq.mm Lead BK Sn	1CX0.75SQMM DISC PVC BK FLRYW125-B	450±4	BLACK

NOTES:
1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
02/20/2023	A	INITIAL RELEASE	MARUTG
DOCUMENT STATUS	P1	RELEASE DATE	2023/03/16 02:43:54

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
FUNCTIONAL SYMBOLS F A = 0 F E = 0 F P = 0 DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 742440 DRWN: MARUTG 2023/02/20 CHK'D: SKUMAR07 2023/03/16 APPR: SKUMAR07 2023/03/16 INITIAL REVISION: DRWN: MARUTG 2023/02/20 APPR: SKUMAR07 2023/03/16				molex SEE TABLE						
	mm		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	ANGULAR TOL ± °														
	4 PLACES		±												
3 PLACES		±						PRODUCT CUSTOMER DRAWING							
2 PLACES		±													
1 PLACE		±													
0 PLACES		±						DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION		
								2244511111		PSD		000	A		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A4-SIZE		224451		SEE TABLE		GENERAL MARKET		1 OF 1	