

CUSTOMER PRINT

PART NUMBER: CA6280XPPXXX90


- NOTES:
1. FINISHED PRODUCT TO BE COILED
 2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
 3. ELECTRICAL TEST: 100% CONTINUITY
 4. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	NO. OF CONTACTS
CA62802PPXXX90	2
CA62803PPXXX90	3
CA62804PPXXX90	4
CA62805PPXXX90	5
CA62806PPXXX90	6
CA6280XPPXXX90	


CABLE LENGTH IN "INCHES"
NO. OF CONTACTS

ASS'Y P/N	"X" DIM
CA6280XPP03990	3 FT. 3 1/2 IN. ±2 IN. [1M ±50.8mm]
CA6280XPP07990	6 FT. 7 IN. ±2 IN. [2M ±50.8mm]
CA6280XPP19790	16 FT. 5 IN. ±4 IN. [5M ±101.6mm]
CA6280XPP39490	32 FT. 9 3/4 IN. ±8 IN. [10M ±203.2mm]
CA6280XPPXXX90	


CABLE LENGTH IN "INCHES"
NO. OF CONTACTS




END "A"
FACE VIEW
CA62802PPXXX90




END "A"
FACE VIEW
CA62803PPXXX90



END "A"
FACE VIEW
CA62804PPXXX90




END "A"
FACE VIEW
CA62805PPXXX90





END "A"
FACE VIEW
CA62806PPXXX90

STRAIGHT OVERMOLDED
CABLE CONNECTOR, MALE
MAT'L: UV PBT, BLACK
(2-6) #20 PIN CONTACTS
MAT'L: GOLD PLATED COPPER ALLOY



END "A"
FACE VIEW
CA62806PPXXX90



O-RING
MAT'L: SILICONE, RED

COUPLING RING
MAT'L: UV PBT, BLACK
SPRING
MAT'L: STAINLESS STEEL

CABLE
20 AWG CONDUCTORS
JACKET: PVC, BLACK
300 VOLTS

DIMENSIONS IN BRACKETS [] ARE IN
MILLIMETERS UNLESS INDICATED

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY: _____	DATE: _____

RoHS COMPLIANT

A	MA	06-04-21	DRAWING CREATED PER DOR 21-109359DS
REV.	INIT.	DATE	DESCRIPTION
	MA	06-04-21	ORIG. DRAWN BY: DATE: MA 06-04-21
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			conxall 601 E. WILDWOOD VILLA PARK, IL 60181
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			
APPROVED BY: _____			TITLE: CABLE ASSEMBLY (2-6) #20 PIN CONTACTS INSTA-CLICK™ MINI-CON-X STANDARD PRODUCT
SCALE NTS	SIZE B	SHEET 1 OF 1	CUSTOMER: CA6280XPPXXX90
FILE: CA6280XPPXXX90	DIRECTORY: SLW	PART NUMBER: CA6280XPPXXX90	REV A