



P	LTR	DESCRIPTION	DATE	DWN	APVD
	BA	INITIAL DRAWING RELEASE	21OCT2022	LG	AP


FOR FURTHER INFORMATION SEE DATA SHEET FOR
RLW73 SERIES WIDE TERMIAL CURRENT SENSING RESISTOR




RoHS Compliant



RECOMMANDED LAND PATTERN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LALITH G	21OCT2022	 TE Connectivity							
		CHK ALLAN P	21OCT2022								
DIMENSIONS: mm		APVD ALLAN P	21OCT2022	NAME WIDE TERMINAL CURRENT SENSING RESISTOR TYPE RLW73 SERIES							
		PRODUCT SPEC -		- SIZE CAGE CODE DRAWING NO RESTRICTED TO							
		APPLICATION SPEC -									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT -		A3		00779		C=2176539-CD		-	
0 PLC ±0.2		CUSTOMER DRAWING				SCALE		SHEET		REV	
1 PLC ±0.1						50:1		1 OF		BA	
2 PLC ±								2			
3 PLC ±											
4 PLC ±											
ANGLES ±											
FINISH											
-											
-											


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
2176539-1	RLW 73B2FR010TD	RLW 73 B2 1% R010 600ppm 5k RL	PRODUCTION
2176539-2	RLW 73B2FR012TD	RLW 73 B2 1% R012 600ppm 5k RL	PRODUCTION
2176539-3	RLW 73B2FR015TD	RLW 73 B2 1% R015 600ppm 5k RL	PRODUCTION
2176539-4	RLW 73B2FR018TD	RLW 73 B2 1% R018 600ppm 5k RL	PRODUCTION
2176539-5	RLW 73B2FR022TD	RLW 73 B2 1% R022 600ppm 5k RL	PRODUCTION
2176539-6	RLW 73B2FR027TD	RLW 73 B2 1% R027 600ppm 5k RL	PRODUCTION
2176539-7	RLW 73B2FR033TD	RLW 73 B2 1% R033 200ppm 5k RL	PRODUCTION
2176539-8	RLW 73B2FR039TD	RLW 73 B2 1% R039 200ppm 5k RL	PRODUCTION
2176539-9	RLW 73B2FR047TD	RLW 73 B2 1% R047 200ppm 5k RL	PRODUCTION
1-2176539-0	RLW 73B2FR056TD	RLW 73 B2 1% R056 200ppm 5k RL	PRODUCTION
1-2176539-1	RLW 73B2FR068TD	RLW 73 B2 1% R068 200ppm 5k RL	PRODUCTION
1-2176539-2	RLW 73B2FR082TD	RLW 73 B2 1% R082 200ppm 5k RL	PRODUCTION
1-2176539-3	RLW 73B2FR10TD	RLW 73 B2 1% R10 200ppm 5k RL	PRODUCTION
1-2176539-4	RLW 73B2FR12TD	RLW 73 B2 1% R12 200ppm 5k RL	PRODUCTION
1-2176539-5	RLW 73B2FR15TD	RLW 73 B2 1% R15 200ppm 5k RL	PRODUCTION
1-2176539-6	RLW 73B2FR18TD	RLW 73 B2 1% R18 200ppm 5k RL	PRODUCTION
1-2176539-7	RLW 73B2FR22TD	RLW 73 B2 1% R22 200ppm 5k RL	PRODUCTION
1-2176539-8	RLW 73B2FR27TD	RLW 73 B2 1% R27 200ppm 5k RL	PRODUCTION
1-2176539-9	RLW 73B2FR33TD	RLW 73 B2 1% R33 200ppm 5k RL	PRODUCTION
2-2176539-0	RLW 73B2FR39TD	RLW 73 B2 1% R39 200ppm 5k RL	PRODUCTION
2-2176539-1	RLW 73B2FR47TD	RLW 73 B2 1% R47 200ppm 5k RL	PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2

1 PLC ±0.1

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

MATERIAL -

-

DWN LALITH G 21OCT2022

CHK ALLAN P 21OCT2022

APVD ALLAN P 21OCT2022

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

NAME

WIDE TERMINAL CURRENT SENSING RESISTOR TYPE RLW73 SERIES

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©=2176539-CD

-

CUSTOMER DRAWING

SCALE 50:1

SHEET 2 OF 2

REV BA

TE Connectivity